

WT24-2B420 W24

COMPACT PHOTOELECTRIC SENSORS





Ordering information

Туре	Part no.
WT24-2B420	1017885

Other models and accessories → www.sick.com/W24

Illustration may differ



Detailed technical data

Features

Functional principle	Photoelectric proximity sensor
Functional principle detail	Background suppression
Dimensions (W x H x D)	27 mm x 87.5 mm x 65 mm
Housing design (light emission)	Rectangular
Sensing range max.	100 mm 2,500 mm ¹⁾
Sensing range	100 mm 2,500 mm ¹⁾
Type of light	Infrared light
Light source	LED ²⁾
Light spot size (distance)	Ø 80 mm (2,500 mm)
Adjustment	Potentiometer

 $^{^{1)}}$ Object with 90% remission (based on standard white, DIN 5033).

Mechanics/electronics

Supply voltage U _B	10 V DC 30 V DC ¹⁾
Ripple	< 5 V _{pp} ²⁾
Current consumption	50 mA ³⁾
Switching output	NPN, PNP

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

 $^{^{2)}}$ Average service life: 100,000 h at T_U = +25 °C.

 $^{^{2)}\,\}mbox{May}$ not exceed or fall below $\mbox{U}_{\mbox{\sc V}}$ tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = V_S connections reverse-polarity protected.

⁷⁾ C = interference suppression.

⁸⁾ D = outputs overcurrent and short-circuit protected.

⁹⁾ Reference voltage: 50 V DC.

 $^{^{10)}}$ Static, low heat output, use in +5 $^{\circ}$ C ... +15 $^{\circ}$ C.

Switching mode	Light/dark switching
Switching mode selector	Selectable via PNP/NPN selector, selectable via light/dark selector
Output current I _{max.}	≤ 100 mA
Response time	≤ 500 µs ⁴⁾
Switching frequency	1,000 Hz ⁵⁾
Time functions	On delayoff delay
Delay time	Adjustable via time delay selector switch, 0.5 s 10 s
Connection type	Male connector M12, 4-pin
Circuit protection	A ⁶⁾ C ⁷⁾ D ⁸⁾
Protection class	и ⁹⁾
Weight	330 g
Front screen heating	✓ ¹⁰⁾
Housing material	Metal, zinc diecast
Optics material	Plastic, PMMA
Enclosure rating	IP69K
Test input sender off	TE to 0 V
Ambient operating temperature	-40 °C +60 °C
Ambient temperature, storage	-40 °C +75 °C

 $^{^{1)}\,\}mathrm{Limit}$ values when operated in short-circuit protected network: max. 8 A.

Safety-related parameters

MTTF _D	621 years
DC _{avg}	0 %

Classifications

ECLASS 5.0	27270904
ECLASS 5.1.4	27270904
ECLASS 6.0	27270904
ECLASS 6.2	27270904
ECLASS 7.0	27270904
ECLASS 8.0	27270904
ECLASS 8.1	27270904
ECLASS 9.0	27270904
ECLASS 10.0	27270904

 $^{^{2)}}$ May not exceed or fall below U_{V} tolerances.

³⁾ Without load.

⁴⁾ Signal transit time with resistive load.

⁵⁾ With light/dark ratio 1:1.

 $^{^{6)}}$ A = V_S connections reverse-polarity protected.

⁷⁾ C = interference suppression.


⁸⁾ D = outputs overcurrent and short-circuit protected.

⁹⁾ Reference voltage: 50 V DC.

 $^{^{10)}}$ Static, low heat output, use in +5 $^{\circ}$ C ... +15 $^{\circ}$ C.

ECLASS 11.0	27270904
ECLASS 12.0	27270904
ETIM 5.0	EC002719
ETIM 6.0	EC002719
ETIM 7.0	EC002719
ETIM 8.0	EC002719
UNSPSC 16.0901	39121528

Adjustments



- ② LED signal strength indicator
- Adjustment of sensing range
- ① Light/dark selector
- ② NPN/PNP changeover switch
- Time control t₂ = OFF delay
- Time control t₁= ON delay
- (5) Time delay selector switch

Connection type




Connection diagram

Cd-117

Characteristic curve

WT24-2, infrared light



- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor

Sensing range diagram

WT24-2, infrared light




0 400 800 1,200 1,600 2,000 2,400 2,800 (15.75) (31.5) (47.24) (62.99) (78.74) (94.49)(110.24)

Distance in mm (inch)

- Sensing range
- ① Sensing range on black, 6% remission factor
- ② Sensing range on gray, 18% remission factor
- 3 Sensing range on white, 90% remission factor

Dimensional drawing (Dimensions in mm (inch))

WT24-2



- ① Alignment sight
- ② LED signal strength indicator
- 3 Standard direction of the material being detected
- 4 Center of optical axis, sender
- (5) Center of optical axis, receiver (close range)
- 6 Center of optical axis, receiver (far range)
- M5 threaded mounting hole, 6 mm deep
- M5 threaded mounting hole, through-hole

Recommended accessories

Other models and accessories → www.sick.com/W24

	Brief description	Туре	Part no.
Mounting bra	ckets and plates		
	Mounting bracket, large, stainless steel, without mounting hardware for the sensor	BEF-WG-W24	4026324
Plug connectors and cables			
	 Connection type head A: Female connector, M12, 4-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 4-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals 	YF2A14- 050VB3XLEAX	2096235
	 Connection type head A: Male connector, M12, 4-pin, straight Description: Unshielded Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² 	STE-1204-G	6009932

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

