

ALPHA WIRE COMPANY

CUSTOMER PRODUCT SPECIFICATION

Part Number: FIT221B
Page 1 of 2 Pages

Issue: 2
Issue Date: 12/31/2008
Effective Date: 3/1/2009

A. Construction

- | | |
|--------------------|-------------------------|
| 1) Tubing Type | Heat Shrinkable Tubing |
| 2) Tubing Material | Cross Linked Polyolefin |
| 3) Color(s) | BLACK, CLEAR |

| Part Number | Minimum Supplied ID (In) | Maximum Recovered ID (In) | Nominal Recovered Wall Thickness (In) |
|--------------|--------------------------|---------------------------|---------------------------------------|
| FIT221B-3/64 | 0.046 | 0.023 | 0.016 |
| FIT221B-1/16 | 0.063 | 0.031 | 0.017 |
| FIT221B-3/32 | 0.093 | 0.046 | 0.020 |
| FIT221B-1/8 | 0.125 | 0.062 | 0.020 |
| FIT221B-3/16 | 0.187 | 0.093 | 0.020 |
| FIT221B-1/4 | 0.250 | 0.125 | 0.025 |
| FIT221B-3/8 | 0.375 | 0.187 | 0.025 |
| FIT221B-1/2 | 0.500 | 0.250 | 0.025 |
| FIT221B-3/4 | 0.750 | 0.375 | 0.030 |
| FIT221B-1IN | 1.000 | 0.500 | 0.035 |

B. Industry Approvals

- | | |
|-----------------------------------|--|
| 1) UL | Standard 224 |
| 2) Other | REACH Regulation (EC 1907/2006) AMS-DTL-23053/5 Class 1 (Except Clear) AMS-DTL-23053/5 Class 2 (Clear Only) |
| 3) EU Directive 2002/95/EC(RoHS): | All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture. |
| 4) California Proposition 65: | The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65. |

C. Physical & Mechanical Properties

- | | | |
|--------------------------------|------------------------------|---------------|
| 1) Temperature Range | -55 to 135°C | |
| 2) Shrink Ratio | Approximately 2:1 | |
| 3) Full Recovery Temperature | 121 °C | |
| 4) Minimum Shrink Temperature | 90°C | |
| 5) Tensile Strength | 1500psi, Min | ASTM D638 |
| 6) Elongation | 200%, Min | ASTM D638 |
| 7) Low Temperature Flex(-55°C) | no cracking | AMS-DTL-23053 |
| 8) Heat Shock(250°C,4hrs) | no cracking | AMS-DTL-23053 |
| 9) Secant Modulus | 2.5x10 ⁴ psi, Min | ASTM D882 |
| 10) Longitudinal Change | +/-5% | AMS-DTL-23053 |
| 11) Specific Gravity(Colors) | 1.35, Max | ASTM D792 |
| Specific Gravity(Clear) | 1.00, Max | |
| 12) Shelf Life | 5 Years @ 0 to 35°C | |

D. Electrical Properties

- | | | |
|------------------------|--------------------------------|-----------|
| 1) Dielectric Strength | 500 V/mil, Min | ASTM D876 |
| 2) Volume Resistivity | 1x10 ¹⁴ ohm-cm, Min | ASTM D876 |

E. Chemical Properties

- | | | |
|----------------------------------|------------------|---------------|
| 1) Water Absorption | 0.50%, Max | ASTM D570 |
| 2) Fluid Resistance(23°C,24 Hrs) | 1000 PSI, Min | AMS-DTL-23053 |
| 3) Vacuum Outgassing - CVCM | 0.1%, Max | ASTM E595 |
| 4) Halogen Free | Yes – Clear Only | |

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: FIT221B
Page 2 of 2 Pages

Issue: 2
Issue Date: 12/31/2008
Effective Date: 3/1/2009

5) Lead Free Yes – Clear Only

F. Other

- 1) Packaging
 - a) FIT221B-3/64
3X1000 FT, 250X4 FT
 - b) FIT221B-1/16
3X1000 FT, 250X4 FT
 - c) FIT221B-3/32
3X500 FT, 250X4 FT
 - d) FIT221B-1/8
3X500 FT, 250X4 FT
 - e) FIT221B-3/16
250X4 FT, 2X500 FT
 - f) FIT221B-1/4
250X4 FT, 2X250 FT
 - g) FIT221B-3/8
250X4 FT, 2X200 FT
 - h) FIT221B-1/2
200X4 FT, 2X150 FT
 - i) FIT221B-3/4
125X4 FT, 2X250 FT
 - j) FIT221B-1IN
2X250 FT, 75X4 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.