

ENTRELEC TERMINAL BLOCKS

COMPACT POWER BLOCKS - CBS185-2P

Screw Clamp Technology


185 mm² (350 Kcmil) , Single pole 1000 VAC/DC (IEC/UL), 353 A

INTRODUCTION

The compact terminal blocks cover a wide variety of applications from mechanical engineering, industrial equipment, automation to wind turbines, solar energy or switchgears. They offer cost, weight and space savings from enhanced aluminum body and compact design. The range offers connection capacity from 50 mm² to 300 mm² and TS35 rail or panel mount.

FEATURES

- Screw-clamp technology
- 185 mm² (350 Kcmil)
- 1000V AC/DC - IEC/UL rated
- Current rating 353 A (IEC/UL)
- Single pole
- 6 colors (grey, blue, green, black, brown, red)
- Aluminum tin plated body
- Panel and Din-rail mounting
- One extra measurement connection 10 mm² (8 AWG)



Approvals

IEC 60947-7-1
IEC 61238-1 (Class A)
UL-1059
UL 486E
CSA C22.2 No.158-10



























Conformity










COMPACT POWER BLOCKS - CBS185-2P

MAIN TECHNICAL DATA

Remarks:	The product is compliant with the EC ROHS directives																																									
Standards:	IEC 60947-7-1, IEC 61238-1		UL 1059, CSA-C22.2 No. 158																																							
																																										
Nominal Voltage:	1.000 V AC / 1.000 V DC		1.000 V AC																																							
Nominal current:	Cu 353 A		Cu 310 A, Al 250 A																																							
Rated cross-section:	185 mm ²		350 Kcmil																																							
Impulse withstand voltage:	8 kV																																									
Pollution degree:	3																																									
Surge voltage category:	III																																									
CTI value:	550		550																																							
Terminal cross section:	<table><tr><td rowspan="4"></td><td colspan="3">no. of connections: 2 x 185 mm² (all conductor types)</td></tr><tr><td colspan="2">IEC 60947-7-1</td><td>IEC 61238-1</td></tr><tr><td colspan="2">Cu</td><td>Al</td></tr><tr><td></td><td></td><td></td></tr><tr><td>185 mm²</td><td rowspan="4">25 Nm</td><td>-</td><td rowspan="4"></td></tr><tr><td>150 mm²</td><td colspan="2" rowspan="3">25 Nm</td></tr><tr><td>120 mm²</td></tr><tr><td>95 mm²</td></tr><tr><td>70 mm²</td><td rowspan="4">-</td><td rowspan="9">20 Nm</td><td rowspan="7"></td></tr><tr><td>50 mm²</td></tr><tr><td>35 mm²</td></tr><tr><td>25 mm²</td></tr><tr><td>stripping length</td><td colspan="3">29 mm</td></tr><tr><td>allen screw</td><td colspan="3">M18 (SW 10 mm)</td></tr></table>					no. of connections: 2 x 185 mm ² (all conductor types)			IEC 60947-7-1		IEC 61238-1	Cu		Al				185 mm ²	25 Nm	-		150 mm ²	25 Nm		120 mm ²	95 mm ²	70 mm ²	-	20 Nm		50 mm ²	35 mm ²	25 mm ²	stripping length	29 mm			allen screw	M18 (SW 10 mm)			
	no. of connections: 2 x 185 mm ² (all conductor types)																																									
	IEC 60947-7-1		IEC 61238-1																																							
	Cu		Al																																							
																																										
185 mm ²	25 Nm	-																																								
150 mm ²		25 Nm																																								
120 mm ²																																										
95 mm ²																																										
70 mm ²	-	20 Nm																																								
50 mm ²																																										
35 mm ²																																										
25 mm ²																																										
stripping length	29 mm																																									
allen screw	M18 (SW 10 mm)																																									
	<table><tr><td rowspan="4"></td><td colspan="3">no. of connections: 2 x 350 Kcmil (all conductor types)</td></tr><tr><td colspan="2">UL 1059, CSA-C22.2 No. 158</td><td></td></tr><tr><td colspan="2">Cu</td><td>Al</td></tr><tr><td></td><td></td><td></td></tr><tr><td>350 kcmil</td><td rowspan="4">28.2 Nm</td><td>-</td><td rowspan="4"></td></tr><tr><td>300 kcmil</td><td colspan="2" rowspan="3">28.2 Nm</td></tr><tr><td>250 kcmil</td></tr><tr><td>AWG 3/0</td></tr><tr><td>AWG 2/0</td><td rowspan="4">-</td><td rowspan="8">-</td><td rowspan="8"></td></tr><tr><td>AWG 1/0</td></tr><tr><td>AWG 2</td></tr><tr><td>AWG 4</td></tr><tr><td>stripping length</td><td colspan="3">29 mm</td></tr><tr><td>allen screw</td><td colspan="3">M18 (SW 10 mm)</td></tr></table>					no. of connections: 2 x 350 Kcmil (all conductor types)			UL 1059, CSA-C22.2 No. 158			Cu		Al				350 kcmil	28.2 Nm	-		300 kcmil	28.2 Nm		250 kcmil	AWG 3/0	AWG 2/0	-	-		AWG 1/0	AWG 2	AWG 4	stripping length	29 mm			allen screw	M18 (SW 10 mm)			
	no. of connections: 2 x 350 Kcmil (all conductor types)																																									
	UL 1059, CSA-C22.2 No. 158																																									
	Cu		Al																																							
																																										
350 kcmil	28.2 Nm	-																																								
300 kcmil		28.2 Nm																																								
250 kcmil																																										
AWG 3/0																																										
AWG 2/0	-	-																																								
AWG 1/0																																										
AWG 2																																										
AWG 4																																										
stripping length	29 mm																																									
allen screw	M18 (SW 10 mm)																																									
Measurement connection:	<table><tr><td rowspan="4"></td><td colspan="3">no. of connections: 1 x 10 mm² (all conductor types)</td></tr><tr><td rowspan="4">1.2 Nm</td><td>-</td><td rowspan="4"></td></tr><tr><td colspan="2" rowspan="3">1.2 Nm</td></tr><tr><td>10 mm²</td></tr><tr><td>6 mm²</td></tr><tr><td>4 mm²</td><td rowspan="4">-</td><td rowspan="5"></td><td rowspan="5"></td></tr><tr><td>2.5 mm²</td></tr><tr><td>1.5 mm²</td></tr><tr><td>stripping length</td><td colspan="3">10 mm</td></tr><tr><td>screw</td><td colspan="3">M4 (+/- PZ2)</td></tr></table>					no. of connections: 1 x 10 mm ² (all conductor types)			1.2 Nm	-		1.2 Nm		10 mm ²	6 mm ²	4 mm ²	-			2.5 mm ²	1.5 mm ²	stripping length	10 mm			screw	M4 (+/- PZ2)															
	no. of connections: 1 x 10 mm ² (all conductor types)																																									
	1.2 Nm	-																																								
		1.2 Nm																																								
				10 mm ²																																						
6 mm ²																																										
4 mm ²	-																																									
2.5 mm ²																																										
1.5 mm ²																																										
stripping length				10 mm																																						
screw	M4 (+/- PZ2)																																									
	<table><tr><td rowspan="4"></td><td colspan="3">no. of connections: 1 x 8 AWG (all conductor types)</td></tr><tr><td rowspan="4">2.3 Nm</td><td>-</td><td rowspan="4"></td></tr><tr><td colspan="2" rowspan="3">2.3 Nm</td></tr><tr><td>8 AWG</td></tr><tr><td>10 AWG</td></tr><tr><td>12 AWG</td><td rowspan="4">-</td><td rowspan="8"></td><td rowspan="8"></td></tr><tr><td>14 AWG</td></tr><tr><td>16 AWG</td></tr><tr><td>stripping length</td><td colspan="3">10 mm</td></tr><tr><td>screw</td><td colspan="3">M4 (+/- PZ2)</td></tr></table>					no. of connections: 1 x 8 AWG (all conductor types)			2.3 Nm	-		2.3 Nm		8 AWG	10 AWG	12 AWG	-			14 AWG	16 AWG	stripping length	10 mm			screw	M4 (+/- PZ2)															
	no. of connections: 1 x 8 AWG (all conductor types)																																									
	2.3 Nm	-																																								
		2.3 Nm																																								
				8 AWG																																						
10 AWG																																										
12 AWG	-																																									
14 AWG																																										
16 AWG																																										
stripping length				10 mm																																						
screw	M4 (+/- PZ2)																																									
	<div> solid</div> <div> compact stranded</div> <div> fine stranded with ferrule</div>																																									
Materials:	Terminal body: Aluminium tin plated Housing: PA 6 (Halogen-free) Screws: Steel zinc plated																																									
Flame resistance:	Self-extinguishing																																									
Mechanical data:	Dimensions: width x height x depth (mm): 37,5 x 73,5 x 105																																									
Protection degree:	IP20																																									



ORDERING DETAILS

Description	Color	Type	Part Number	Pkg qty Std/box	Weight 1 Piece (g)	EAN/UPC codes
185 mm ² Single pole	Grey -RAL7035	 CBS185-2P	1SNF536011R0000	1/12	206	3472599057869
	Grey/Blue -RAL7035/5012	 CBS185-2P-BL	1SNF536021R0000			3472599057876
	Grey/Green -RAL7035/6018	 CBS185-2P-GR	1SNF536031R0000			3472598016591
	Grey/Brown -RAL7035/8003	 CBS185-2P-BR	1SNF536041R0000			3472598016607
	Grey/Black -RAL7035/9005	 CBS185-2P-BK	1SNF536051R0000			3472598016614
	Grey/Red -RAL7035/3020	 CBS185-2P-RD	1SNF536061R0000			3472598016621
CBS185 IP20 Cover	Grey -RAL7035	 CB185- Cover	1SNF936710R0000	12/216	8	3472599057982
Self-adhesive Rigid white label 17x9 mm 60 per card	White	TAA0917	1SNA235776R0000	18 cards/pack	16,7 (per card)	3472599021105

Connect With Us

Get Answers to Your Questions Now.

We make it easy to connect with our experts and are ready to provide the support you need, including:

- Product information
- Product comparisons for your project
- Discussions with TE engineers and product experts
- Project consultations
- TE design resources and tools

te.com

©2024 TE Connectivity. All Rights Reserved.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

INDUSTRIAL / ENTRELEC COMPACT POWER BLOCKS CBS95-2P/DATASHEET/ EN

07/24

TE Connectivity

EUROPARC - Bat. 9
9, rue Irène Joliot-Curie
69800 Saint-Priest
France