

# **Technical Data Sheet**

Rev. A (05/18) Page 1 of 2

# Economy Duster Product# 1673

### **Product Description**

Economical HFC152a based duster. Note: not for use on powered electrical equipment, on hot surfaces, and around open flames or sparks.

#### **Features / Benefits**

- Best value & 30% more volume
- Lower global warming potential / 10% of HFC-134a
- Non-ozone depleting
- Moisture free
- Zero residue
- Safe on plastics
- VOC exempt
- Velocity 11.4 m/s

#### **Applications**

- Audio/Video Equipment
- Computers and Other Electronic Equipment
- Fax Machines
- Laboratory Instruments
- Photo Equipment
- Printed Circuit Boards
- Printers
- Surface Mount Devices

## **Usage Instructions**

CAUTION: Can must be held in a upright position when spraying. Do not tilt can more than 40 degrees during spraying operation or shake during use. Do not use near flames. De-energize all equipment prior to use. Before use, press actuator to clear valve of any liquid product. Extension tube can be used to remove dust in tight areas. Use short burst to prevent cooling of can. CONSULT SDS BEFORE USE. Note: Do not use on photographic negatives without first clearing valve.



### **Typical Product Data and Physical Properties**

Physical state:	Gas
Auto-ignition temperature:	309.2ºF (154ºC)
Flammable limits:	Lower: 3.9%
	Upper: 16.9%
Color:	Colorless
Odor:	Ethereal. Faint odor.
Vapor pressure:	87 psia @ 25ºC
Vapor density:	2.4 [Air=1]
Volatility:	100%
Heat of combustion:	18.49 kJ/g
VOC – EPA:	0%
CARB:	Exempt
Shelf life:	5 years



## **Technical Data Sheet**

Rev. A (05/18) Page 2 of 2

# Economy Duster Product# 1673

### **Material Compatibility**

Buna-N: Excellent Graphite: Excellent HDPE: Excellent LDPE: Excellent Lexan: Excellent Excellent Neoprene: Cross-Linked PE: Excellent Polyacrylate: Excellent Polystyrene: Excellent PVC: Excellent Silicone Rubber: Excellent Teflon: Excellent Viton: Excellent

### **Packaging and Availability**

1673-10S 10 oz. Aerosol

### **Environmental Policy**

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

#### **Resources**

Techspray® products are supported by global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Techspray® 8125 Cobb Center Drive Kennesaw, GA 30152 800-858-4043 tsales@techspray.com

### Europe

ITW Contamination Control BV Saffierlaan 5, 2132 VZ Hoofddorp The Netherlands +31 88 1307 400 info@itw-cc.com

#### Countries outside the US

Call to locate a distributor in your country