



22mm LED Metal Pilot Lights



Certified for
NEMA Type 4X
12 environment.

Pilot Light

with bulb, bulb holder
and mounting bracket



Replacement bulbs
available.
See page 39.

Color 12V AC/DC

Voltage

Cat No.

☐	White	12V AC/DC	2PLB1LB-012
☒	Green	12V AC/DC	2PLB3LB-012
☒	Red	12V AC/DC	2PLB4LB-012
☒	Amber	12V AC/DC	2PLB5LB-012
☒	Blue	12V AC/DC	2PLB6LB-012
☐	Clear	12V AC/DC	2PLB7LB-012
☒	Yellow	12V AC/DC	2PLB8LB-012

24V AC/DC

☐	White	24V AC/DC	2PLB1LB-024
☒	Green	24V AC/DC	2PLB3LB-024
☒	Red	24V AC/DC	2PLB4LB-024
☒	Amber	24V AC/DC	2PLB5LB-024
☒	Blue	24V AC/DC	2PLB6LB-024
☐	Clear	24V AC/DC	2PLB7LB-024
☒	Yellow	24V AC/DC	2PLB8LB-024

48V AC/DC

☐	White	48V AC/DC	2PLB1LB-048
☒	Green	48V AC/DC	2PLB3LB-048
☒	Red	48V AC/DC	2PLB4LB-048
☒	Amber	48V AC/DC	2PLB5LB-048
☒	Blue	48V AC/DC	2PLB6LB-048
☐	Clear	48V AC/DC	2PLB7LB-048
☒	Yellow	48V AC/DC	2PLB8LB-048

110V AC

☐	White	110V AC	2PLB1LB-110
☒	Green	110V AC	2PLB3LB-110
☒	Red	110V AC	2PLB4LB-110
☒	Amber	110V AC	2PLB5LB-110
☒	Blue	110V AC	2PLB6LB-110
☐	Clear	110V AC	2PLB7LB-110
☒	Yellow	110V AC	2PLB8LB-110

110V DC

☐	White	110V DC	2PLB1LB-110D
☒	Green	110V DC	2PLB3LB-110D
☒	Red	110V DC	2PLB4LB-110D
☒	Amber	110V DC	2PLB5LB-110D
☒	Blue	110V DC	2PLB6LB-110D
☐	Clear	110V DC	2PLB7LB-110D
☒	Yellow	110V DC	2PLB8LB-110D

230V AC

☐	White	230V AC	2PLB1LB-230
☒	Green	230V AC	2PLB3LB-230
☒	Red	230V AC	2PLB4LB-230
☒	Amber	230V AC	2PLB5LB-230
☒	Blue	230V AC	2PLB6LB-230
☐	Clear	230V AC	2PLB7LB-230
☒	Yellow	230V AC	2PLB8LB-230

230V DC

☐	White	230V DC	2PLB1LB-230D
☒	Green	230V DC	2PLB3LB-230D
☒	Red	230V DC	2PLB4LB-230D
☒	Amber	230V DC	2PLB5LB-230D
☒	Blue	230V DC	2PLB6LB-230D
☐	Clear	230V DC	2PLB7LB-230D
☒	Yellow	230V DC	2PLB8LB-230D

22mm Specifications

Electrical and Mechanical Characteristics

Standard conformity:	IEC 60947-5-1
Approvals:	VDE0660 CSA - C22.2 No. 14-95 UL508 IEC 947 - 5 (1) 1990, IS 13947 ASTA UK certified as per IEC 947 - 5 - (1) 1990
Degree of protection:	IP 65 as per IEC 529 NEMA Type 4X, 12 as per UL50
Temperature Range:	- 25°C to + 70°C (-13°F to +158°F)

Contact Block

Rated voltage:	600V AC /DC
Rated current:	10A AC / 2.5A DC
Contact operation:	self-wiping, slow break NO or NC
UL508 rating (pilot duty):	
CSA - C22.2 No. 14-95:	A600: 10A; 600V AC Q600: 2.5A; 600V DC
Make and break capacity	
IEC 947 - 5 - (1) 1990:	AC 15 4A, 415V AC DC 13 0.5A, 110V DC
Terminal capacity:	minimum 20 AWG (0.5 mm ²) maximum 2x16 AWG (2 x 1.5 mm ²) or 14 AWG (2.5 mm ²)
Terminal marking:	1-2 for NC, 3-4 for NO
Short circuit protection:	10A cartridge fuse HRC type, rated for resistive loads
Mechanical life:	1 million operations

Modules for Pilot Lights & Illuminated Switches with LED Bulbs

Current consumption (applicable to all colors)	
24 VAC/DC, 100 VAC & 240 VAC:	max. 20 mA
110 VDC:	max. 15 mA
220 VDC:	max. 10 mA
Service life (at nominal voltage and at ambient temperature of 25°C):	100,000 hours
Voltage limits (nominal voltage):	<20% of rated voltage>
Short circuit protection:	on specific request
Terminal capacity:	min. 1 x 0.5 mm ² (20 AWG), max. 2 x 1.5 mm ² (2x16 AWG) or 1 x 2.5 mm ² (1x14 AWG)

Torque Specifications

Mounting bracket screws	1.2 Nm (10.8 lbs. in.)
Contact block to bracket screws	0.5 Nm (4.5 lbs. in.)
Terminal screws (wiring)	0.8 Nm (7.2 lbs. in.)