



BLOW MOLDED SHIPPERS

- Double wall construction
- ESD and physical protection
- Custom thermoformed and foam interiors are available
- Reusable

PN	L X W X H (D)	QTY/CASE
50014	8 15/16 X 6 5/8 X 1 1/4"	5
50015	11 7/8 X 8 3/16 X 1 1/4"	5
50016	12 3/4 X 10 1/2 X 1 3/4"	5
50019	5 1/16 X 2 3/4 X 1"	5
50021	18 7/16 X 17-11/16 X 1 15/16"	5
50023	17 1/2 X 13 1/2 X 1 5/16"	5



SPECIFICATIONS

These products meet and/or exceed ANSI/ESD S20.20-2021 and ANSI/ESD S541-2019.

BLOW MOLDED SHIPPERS		
PROPERTY	VALUE (U.S.)	TEST METHOD
Surface Resistivity	1 ³ -1 ⁴ Ohms	ASTM D4496
Tensile Strength	3300 psi	ASTM D638
Tensile Elongation	15.0%	ASTM D638
Flexural Modulus	14500 psi	ASTM D790
Flexural Strength	4700 psi	ASTM D790
Notched IZOD Impact	8.0 ft-lb/in	ASTM D256

All values are for pre-formed materials. Electrical values will vary with each individual design. All information, recommendations and suggestions appearing in this bulletin concerning the use of our products are based upon tests and data believed to be reliable; however, it is the user's responsibility to determine the suitability for their own use of the products described herein. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Conductive Containers, Inc. as to the effects of such use or the results to be obtained, nor does Conductive Containers, Inc. assume any liability arising out of use, by others, of the products referred to herein. Nor is the information herein to be construed as absolutely complete since additional information may be necessary or desirable, when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations. Nothing herein contained is to be construed as permission or as a recommendation to infringe any patent.

