



OLS20-BB1118142 ols

CONTRAST SENSORS





Ordering information

| Туре | Part no. |
|-----------------|----------|
| 0LS20-BB1118142 | 1100421 |

Other models and accessories → www.sick.com/OLS

Illustration may differ



Detailed technical data

Features

| Dimensions (W x H x D) | 31 mm x 62 mm x 52.5 mm |
|----------------------------|-----------------------------|
| Sensing distance | ≤ 100 mm |
| Sensing distance tolerance | ± 10 mm |
| Housing design | Rectangular |
| Working range | 90 mm 110 mm |
| Light source | LED, blue ¹⁾ |
| Wave length | 450 nm |
| Light spot size | 180 mm x 9 mm ²⁾ |
| Receiving filters | RG 610 |
| Bar code types | Interleaved 2 of 5 |
| Module width (min.) | ≥ 1.5 mm |
| Line radius (min.) | ≥ 0.5 m |
| Track color | Orange |

 $^{^{1)}}$ Average service life: 100,000 h at T_{U} = +25 °C.

Mechanics/electronics

| Supply voltage | 18 V DC 30 V DC ¹⁾ |
|----------------|-------------------------------|
| Ripple | \leq 5 $V_{pp}^{2)}$ |

 $^{^{1)}}$ Limit values when operated in short-circuit protected network: max. 8 A.

 $^{^{2)}}$ Field of view line +-90mm, field of view code +-50mm.

 $^{^{2)}\,\}mbox{May}$ not exceed or fall below $\mbox{U}_{\mbox{\scriptsize V}}$ tolerances.

³⁾ Without load.

| Power consumption | < 3 W ³⁾ |
|----------------------------------|--|
| Sampling rate | 5 ms |
| Accuracy optical center | ± 1 mm |
| Switching output | Push-pull: PNP/NPN |
| Switching output (voltage) | Push-pull: PNP/NPN HIGH = U_V - 3 V/LOW \leq 3 V |
| Output current I _{max.} | < 100 mA |
| Connection type | Male connector M12, 5-pin |
| Protection class | III |
| Circuit protection | U _V connections, reverse polarity protected Output Q short-circuit protected Interference pulse suppression |
| Enclosure rating | IP67 |
| LED risk group | 2 (IEC 62471) |
| Weight | 250 g |
| Housing material | Metal, zinc diecast |

 $^{^{1)}\,\}mathrm{Limit}$ values when operated in short-circuit protected network: max. 8 A.

Communication interface

| IO-Link | √ , COM3 (230,4 kBaud) |
|---------------------|-------------------------------|
| Cycle time | 5 ms |
| Process data length | 21 Byte Process Data In |
| Modbus | √ , RTU RS-485 |
| Digital output | Q_1 |
| Number | 1 |

Ambient data

| Ambient operating temperature | -10 °C +55 °C |
|-------------------------------|------------------------------|
| Ambient temperature, storage | -25 °C +75 °C |
| Ambient light immunity | 50,000 lx |
| Shock load | According to IEC 60068 |
| UL File No. | NRKH.E181493 & NRKH7.E181493 |

Classifications


| ECLASS 5.0 | 27270906 |
|--------------|----------|
| ECLASS 5.1.4 | 27270906 |
| ECLASS 6.0 | 27270906 |
| ECLASS 6.2 | 27270906 |
| ECLASS 7.0 | 27270906 |
| ECLASS 8.0 | 27270906 |
| ECLASS 8.1 | 27270906 |
| ECLASS 9.0 | 27270906 |
| ECLASS 10.0 | 27270906 |

 $^{^{(2)}}$ May not exceed or fall below U_{ν} tolerances.

³⁾ Without load.


| ECLASS 11.0 | 27270906 |
|----------------|----------|
| ECLASS 12.0 | 27270906 |
| ETIM 5.0 | EC001820 |
| ETIM 6.0 | EC001820 |
| ETIM 7.0 | EC001820 |
| ETIM 8.0 | EC001820 |
| UNSPSC 16.0901 | 39121528 |

Dimensional drawing (Dimensions in mm (inch))



- ① Optical axis
- ② Field of view
- 3 Mounting hole, Ø 4.1 mm
- Connector M12 (rotatable up to 180°)


Adjustments



① Indicator lamps

Connection diagram

Cd-424



Recommended accessories

Other models and accessories → www.sick.com/OLS

| | Brief description | Туре | Part no. | |
|--|--|-----------------------------------|----------|--|
| Connection m | Connection modules | | | |
| | IO-Link V1.1 Class A port, USB2.0 port, optional external power supply 24V $/$ 1A | IOLA2US-01101 (SiLink2 Master) | 1061790 | |
| Universal bar | clamp systems | | | |
| | Plate NO4 for universal clamp, steel, Zinc plated steel (sheet), Zinc die cast (clamping bracket), Universal clamp (5322626), mounting hardware | BEF-KHS-N04 | 2051610 | |
| | Mounting bar, straight, 200 mm, steel, steel, zinc coated, without mounting hardware | BEF-MS12G-A | 4056054 | |
| | Mounting bar, L-shaped, 250 x 250 mm, steel, steel, zinc coated, without mounting hardware | BEF-MS12L-B | 4056053 | |
| Codes | | | | |
| | Luminescent duct tape for easy application to all types of flooring, width 2.5 cm, length 25 m, neon orange | ADHESIVE TAPE, FABRIC | 5337868 | |
| | 1D bar codes in $2/5$ interleaved format, set of 108 bar codes, 9 A4 sheets of 12 bar codes each, luminescent PVC base material with protective film, codes 0001 0108, neon orange | BARCODE 7510- 038-0001-0108 | 5338408 | |
| ATTENNA OF THE PROPERTY OF THE | Scope of delivery: $1 \times 90^\circ$ arc, protective film for adhesive tape, slip resistance class R10, protection against abrasion and moisture, prepared as 90° arc with a radius of 1,000 mm | TAPE 250AS-100-35 | 5338390 | |
| 6 | Protective film for adhesive tape, slip resistance class R10, protection against abrasion and moisture, width 3,5 cm, length 50 m $$ | TAPE 250AS-35-50 | 5338386 | |
| | Scope of delivery: $1 \times 90^\circ$ arc, protective film for adhesive tape, slip resistance class R10, protection against abrasion and moisture, prepared as 90° arc with a radius of 500 mm | TAPE 250AS-500-35 | 5338389 | |
| | Scope of delivery: $1x90^\circ$ arc, luminescent rugged PVC adhesive tape, prepared as 90° arc with a radius of 1,000 mm, neon orange | TAPE 7510- 038-1000 | 5338388 | |

OLS20-BB1118142 | OLS

CONTRAST SENSORS

| | Brief description | Туре | Part no. |
|---------------|---|-------------------------|----------|
| Q | Luminescent rugged PVC adhesive tape for easy application to all types of flooring, width 2 cm, length 25 m, neon orange | TAPE 7510- 038-20-25 | 5338378 |
| | Scope of delivery: 1 x 90 $^{\circ}$ arc: luminescent rugged PVC adhesive tape, prepared as 90 $^{\circ}$ arc with a radius of 500 mm, neon orange | TAPE 7510-038-500 | 5338387 |
| Plug connecto | ors and cables | | |
| | Connection type head A: Female connector, M12, 5-pin, straight, A-coded Connection type head B: Flying leads Signal type: Sensor/actuator cable Cable: 5 m, 5-wire, PVC Description: Sensor/actuator cable, unshielded Application: Zones with chemicals | YF2A15- 050VB5XLEAX | 2096240 |
| | Connection type head A: Male connector, M12, 5-pin, straight Description: Unshielded, Head A: male connector, M12, 5-pin, straight, unshielded, for cable diameter 4 mm 6 mm Head B: - Connection systems: Screw-type terminals Permitted cross-section: ≤ 0.75 mm² Note: For field bus technology | STE-1205-G | 6022083 |

Recommended services

Additional services → www.sick.com/OLS

| | Туре | Part no. |
|--|-------------------------|----------|
| Pre-configuration | | |
| Product area: OLS Voraussetzungen: SOPAS ET file or sensor app which contains the necessary configuration and is coordinated to the customer application, Uploading of the configuration or the SOPAS ET file or sensor app Range of services: Production and delivery of one or several personalized SICK products with the configuration uploaded by the customer and selected in the web ordering process Documentation: Additional label on the SICK product and its packaging with the configuration name specified by the customer and a unique configuration ID Duration: The delivery time of the pre-configured and customer-specific SICK product is identical, or in the case of temporary storage, a few days longer than with a standard SICK product | Pre-configuration OLS20 | 1615148 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

