

## LCL Series



- Single Output Industrial Supplies
- High Efficiency
- Low Cost
- 150 W Convection Cooled
- 300 W & 500 W with Internal Fans
- Outputs from 12 V to 48 V
- 3 Year Warranty

## Specification

## Input

Input Voltage	• 85-264 VAC (127-370 VDC) see note 1
Input Frequency	• 47-63 Hz
Input Current	• 2.1 A max for LCL150, 4.5 A max for LCL300, 6.6 A max for LCL500
Inrush Current	• 40 A max for LCL150, 60 A max for LCL300 & 500 25 °C cold start
Power Factor	• Meets EN61000-3-2 class A
Earth Leakage Current	• <2mA at 264 VAC, 60 Hz
Input Protection	• LCL150: T3.15 A/250 V, LCL300: T6.3A/250 V, LCL500: T10A/250 V, internal fuse fitted in line

## Output

Output Voltage	• See tables
Output Voltage Trim	• See tables
Initial Set Accuracy	• $\pm 100$ mV at 50% load
Minimum Load	• None required
Start Up Delay	• 2 s max for LCL150, 1.5 s max for LCL300, 0.8 s max for LCL500
Start Up Rise Time	• 50 ms max for LCL150, 35 ms max for LCL300 & LCL500
Hold Up Time	• 10 ms min at 115 VAC and full load
Line Regulation	• $\pm 0.5\%$ max for LCL150, $\pm 0.3\%$ for LCL300 & LCL500
Load Regulation	• $\pm 1\%$ max
Transient Response	• 4% max deviation returning to within 1% within 500 $\mu$ s for a 50% load change
Ripple & Noise	• See tables
Overvoltage Protection	• 115-135%, recycle input to reset
Overtemperature Protection	• Output turns off when OTP triggered, measured internally, auto Recovery
Overload Protection	• 110-130% of rated output power
Short Circuit Protection	• Trip and restart (hiccup mode), auto recovery
Remote Sense	• Fitted to LCL500 only, compensates for 0.25 V max each line
Remote On/Off	• Fitted on LCL300 & 500 only, On = logic low or open circuit, Off = logic high

## General

Efficiency	• 85% min at full load & 230 VAC
Isolation	• 3000 VAC Input to Output 1500 VAC Input to Ground 500 VAC Output to Ground
Switching Frequency	• 90-110 kHz main switch & 45-190 kHz PFC for LCL150, 80-190 kHz main switch & 62-65 kHz PFC for LCL300 & 500
Power Density	• 2.7 W/in <sup>3</sup> LCL150, 4.4 W/in <sup>3</sup> LCL300, 4.9 W/in <sup>3</sup> LCL500
MTBF	• 200 kHrs according to MIL-HDBK-217F at 25 °C, GB

## Environmental

Operating Temperature	• -10 °C to +60 °C, derate from 100% load at 50 °C to 50% load at 60 °C for LCL150 -10 °C to +65 °C, derate from 100% load at 50 °C to 60% load at 65 °C for LCL300 -10 °C to +60 °C, derate from 100% load at 55 °C to 80% load at 60 °C for LCL500
Cooling	• LCL150 convection cooled, LCL300 & LCL500 have internal fans
Operating Humidity	• 5% to 90% non condensing
Storage Temperature	• -40 °C to +85 °C
Operating Altitude	• 3000 m
Vibration	• 10-500 Hz, 2g, 10 mins per cycle on 3 axes

## EMC &amp; Safety

Emissions	• EN55022 level B conducted, level A radiated
Harmonic Currents	• EN61000-3-2 class A
Voltage Flicker	• EN61000-3-3
ESD Immunity	• EN61000-4-2, $\pm 4$ kV contact, $\pm 8$ kV air discharge, Performance Criteria A
Radiated Immunity	• EN61000-4-3, level 2 Perf Criteria A
EFT/Burst	• EN61000-4-4, level 2 Perf Criteria A
Surge	• EN61000-4-5, level 2 Perf Criteria A
Conducted Immunity	• EN61000-4-6, level 2 Perf Criteria A
Magnetic Field	• EN61000-4-8, 1 A/m Perf Criteria A
Dips & Interruptions	• EN61000-4-11, 70% $U_T$ for 10 ms, 40% $U_T$ for 100 ms, <5% $U_T$ for 5000 ms, Perf Criteria ABB
Safety Approvals	• EN60950-1, UL60950-1, CSA60950 No 22.2


## Model and Ratings

Output Power <sup>(1)</sup>	Output Voltage	Trim Range	Output Current	Ripple & Noise <sup>(2)</sup>	Model Number
150 W	12.0 V	11.0-13.0 V	12.5 A	100 mV pk-pk	LCL150PS12
	13.5 V	12.5-14.5 V	11.1 A	100 mV pk-pk	LCL150PS13
	15.0 V	14.0-16.0 V	10.0 A	100 mV pk-pk	LCL150PS15
	24.0 V	23.0-25.0 V	6.3 A	150 mV pk-pk	LCL150PS24
	27.0 V	26.0-28.0 V	5.6 A	150 mV pk-pk	LCL150PS27
	48.0 V	47.0-49.0 V	3.1 A	250 mV pk-pk	LCL150PS48

### Notes

- Output power derates linearly from 100% at 90 VAC to 90% at 85 VAC.
- Measured with 20 MHz bandwidth.

## Mechanical Details





Pin	Function
1	+Vout
2	+Vout
3	-Vout
4	-Vout
5	Ground
6	AC Neutral
7	AC Live

### Notes

Weight: 1.39 lbs (630g) approx.  
Dimensions shown in inches (mm).

Tolerance is  $\pm 0.05$  ( $\pm 0.2$ ) maximum.

## Derating Curves




Output Power <sup>(1)</sup>	Output Voltage	Trim Range	Output Current	Ripple & Noise <sup>(2)</sup>	Model Number
300 W	12.0 V	11.0-13.0 V	25.0 A	150 mV pk-pk	LCL300PS12
	13.5 V	12.5-14.5 V	22.0 A	150 mV pk-pk	LCL300PS13
	15.0 V	14.0-16.0 V	20.0 A	150 mV pk-pk	LCL300PS15
310 W	24.0 V	23.0-25.0 V	13.0 A	150 mV pk-pk	LCL300PS24
315 W	27.0 V	26.0-28.0 V	11.7 A	200 mV pk-pk	LCL300PS27
320 W	48.0 V	47.0-49.0 V	6.70 A	240 mV pk-pk	LCL300PS48

Notes

1. Operation at 85 VAC is possible, but output power derates linearly from 100% at 90 VAC to 90% at 85 VAC.
2. Measured with 20 MHz bandwidth.

Mechanical Details



J1 Pin Connections	
Pin	Function
1	+Vout
2	+Vout
3	+Vout
4	-Vout
5	-Vout
6	-Vout
7	Ground
8	AC Neutral
9	AC Live

J2 Pin Connections	
Pin	Function
1	Remote Control -
2	Remote Control +



Applying >4.5 V to Pin 2 with respect to Pin 1 turns output off.  
Applying <0.8 V to Pin 2 with respect to Pin 1 or open circuit turns output on.

Mating Connectors (J2):  
Molex KK type 2695 housing  
Molex 2695-2759 contacts

Notes

Weight: 1.94 lbs (880g) approx. Tolerance is ±0.05 (±0.2) maximum.  
Dimensions shown in inches (mm).

Derating Curves







**Model and Ratings**

Output Power <sup>(1)</sup>	Output Voltage	Trim Range	Output Current	Ripple & Noise <sup>(2)</sup>	Model Number
500 W	12.0 V	11.0-13.0 V	42.0 A	120 mV pk-pk	LCL500PS12
	13.5 V	12.5-14.5 V	37.0 A	150 mV pk-pk	LCL500PS13
	15.0 V	14.0-16.0 V	34.0 A	150 mV pk-pk	LCL500PS15
	24.0 V	23.0-25.0 V	21.0 A	150 mV pk-pk	LCL500PS24
	27.0 V	26.0-28.0 V	18.5 A	150 mV pk-pk	LCL500PS27
	48.0 V	47.0-49.0 V	10.5 A	240 mV pk-pk	LCL500PS48

**Notes**

1. Output power derates linearly from 100% at 90 VAC to 90% at 85 VAC.
2. Measured with 20 MHz bandwidth.

**Mechanical Details**



J1 Pin Connections	
Pin	Function
1	+Vout
2	+Vout
3	+Vout
4	-Vout
5	-Vout
6	-Vout
7	Ground
8	AC Neutral
9	AC Live

J2 Pin Connections	
Pin	Function
1	Remote Control -
2	Remote Control +
3	Sense -
4	Sense +

Applying >4.5 V to Pin 2 with respect to Pin 1 turns output off.  
Applying <0.8 V to Pin 2 with respect to Pin 1 or open circuit turns output on.

Mating Connectors (J2):  
WST P4-I25002 housing  
WST I25002BS contacts

**Notes**

Weight: 3.2 lbs (1.45 kg) approx. Tolerance is ±0.05 (±0.2) maximum.  
Dimensions shown in inches (mm).

**Derating Curves**

