



1000-3500W

Model

DC-1000-KIT
DC-2000-KIT
DC-2500-KIT
DC-2500-KIT-XL
DC-3500-KIT



Samlex uses the highest quality of industrial grade, flexible cables suitable to be used as battery cables for automotive and renewable energy applications. Key features:

- 600V rating
- Very wide operating temperature of -50°C to 105°C
- High strand count, annealed, and tinned copper conductors for high flexibility
- Ethylene Propylene Rubber (EPR) jacket provides the high 600V insulation and resistance to abrasion, oils, acids and heat

Design Features of Fuses and Fuse Holders Provided with the Kits:

- 100A, 200A and 300A Marine Rated Battery Fuses are provided with DC-1000-KIT, DC-2000-KIT, DC-2500-KIT and DC-2500-KIT-XL respectively. The MRBF Fuse with high Ampere Interrupting Capacity (AIC) provides easy, weatherproof and safe short circuit protection
- 400A Class T Fuse is provided with DC-3500-KIT. Each Class T Fuse has a very high AIC, and is designed for protection against damage due to short circuit conditions in battery cables

2 YEAR LIMITED WARRANTY

[illegible]

NOTES:

- a) Specifications are subject to change without notice.
- b) Cable Specifications: (i) Red Positive, Black Negative, each 10 ft or 15 ft length, (ii) 600V, -50°C to 105°C, (iii) Stranded conductors with crimped Ring Terminals on either end: Hole diameter 0.41" for 3/8" stud.

12013-DC Install Kits-0322