


SANYO

Cadnica




Cell Type CP-1300SCR

Specifications


Nominal Capacity		1300mAh
Nominal Voltage		1.2V
Charging Current	Standard	130mA
	Fast	1950mA
Charging Time	Standard	14 to 16Hrs.
	Fast	about 1Hr.
Ambient Temperature	Charge	Standard 0°C to +45°C [+32°F to 113°F] Fast 5°C to +40°C [+41°F to 104°F]
		Discharge -20°C to +60°C [-4°F to 140°F]
	Storage	-30°C to +50°C [-22°F to 122°F]
Internal Impedance (Av.) (at 50% discharge)		6.5mΩ (at 1000Hz)
Weight		35g/1.23oz
Dimensions(D)×(H) (with tube)		22.9 $\begin{smallmatrix} 0 \\ -1 \end{smallmatrix}$ × 26.7 $\begin{smallmatrix} 0 \\ -0.9 \end{smallmatrix}$ mm 0.90 $\begin{smallmatrix} 0 \\ -0.04 \end{smallmatrix}$ × 1.05 $\begin{smallmatrix} 0 \\ -0.04 \end{smallmatrix}$ inch

Typical Characteristics


Charge




Discharge (at high rate)




Cell capacity (at various discharge rate)



Discharge (at high rate)



Discharge (at low rate)



Temperature (Charge & Discharge)

