



Connectors > Connector Accessories > Connector Caps & Covers > Bus Connector: Strain Relief, ATA



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Black**

Primary Product Material: **Thermoplastic**

[All Bus Connector: Strain Relief, ATA \(13\)](#)

Features

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Body Features

Primary Product Color	Black
Primary Product Material	Thermoplastic

Dimensions

Product Width	6.1 mm[.24 in]
Product Length	48.01 mm[1.89 in]
Product Height	14.76 mm[.581 in]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	CSA LR7189, UL E28476

Packaging Features

Packaging Quantity	500
Packaging Method	Bag & Box



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>









Compatible Parts

 <p>TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS</p>	 <p>TE Part # 3-1761607-1 IDC LOW PRO HDR 34P RA LG LAT BLUE</p>	 <p>TE Part # 1-1761606-1 IDC LOW PRO HDR 34P VERT LG LAT BLK</p>	 <p>TE Part # 5103311-7 A/L LOW PRO HDR 34P RA BLACK</p>
 <p>TE Part # 5103309-7 A/L LOW PRO HDR 34P VERT BLACK</p>	 <p>TE Part # 1658621-8 34 NOVO MIL/CTR 15DP, LEAD FREE</p>	 <p>TE Part # 3-1761603-1 IDC LOW PRO HDR 34P VERT BLUE</p>	 <p>TE Part # 3-1761606-1 IDC LOW PRO HDR 34P VERT LG LA</p>



 TE Part # 1658622-8 34 NOVO MIL/CTR 30DP,LEAD FREE	 TE Part # 1658620-8 34 NOVO MIL 15DP, LEAD FREE	 TE Part # 5103308-7 A/L LOW PRO HDR 34P VERT BLACK	 TE Part # 1-1761607-1 IDC LOW PRO HDR 34P RA LG LAT
 TE Part # 1658623-8 34 NOVO MIL 30DP, LEAD FREE	 TE Part # 2-111446-2 034 UNIV I/O 30DP NO EARS	 TE Part # 5103310-7 A/L LOW PRO HDR 34P RA BLACK	 TE Part # 5104338-7 A/L LOW PRO HDR 34P VERT HT
 TE Part # 1-1761681-1 IDC LOW PRO HDR 34P VERT HT BLACK	 TE Part # 3-1761605-1 IDC LOW PRO HDR 34P RA BLUE	 TE Part # 5111448-8 034 UNIV I/O 30DP SLOT	 TE Part # 1-1761686-1 IDC LOW PRO HDR 34P VERT LG LAT

Customers Also Bought

 TE Part #499252-5 010 STRAIN RELIEF A-L RCPT	 TE Part #66425-7 III+ PIN,30-26,15AU/FL,STRIP	 TE Part #1-770004-0 UMNL II SOK SN/AUNI/PHBZ	 TE Part #1-2176379-7 RQ 0805 158R 0.1% 10PPM 5K RL
 TE Part #9-2176389-7 RQ 1206 1K07 0.1% 10PPM 5K RL	 TE Part #9-2176389-0 RQ 1206 909R 0.1% 10PPM 5K RL	 TE Part #556135-1 CONT,AMPINNRGY WTW,STRIP,14-18	 TE Part #1SNA115201R2500 M6/9.EE



TE Part #ANT-916-CW-HD  
Antenna 1/4 Wave HD Whip 916MHz  
RPS

Documents

Product Drawings

034 STRAIN RELIEF A-L RCPT

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_499252-6\_AL.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_499252-6\_AL.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_499252-6\_AL.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Product Specifications

Application Specification

English