



FEATURES

- Push keyboard setting.
- External trigger input.
- RS232 computer interface output.
- Flash rate: 5 to 10,500 RPM/FPM. 0.083 to 175 Hz
- Display 14 mm LED, 6 digits.
- High resolution.
- Main function: Fine adjust, Coarse adjust, Multiply by 2, Divide by 2, Fast finder, Memory recall.
- Memorize 10 sets of measuring data.
- Crystal time base and microprocessor circuit, do not necessary require any calibration procedures.
- Power supply: AC 110V/220V/230V, 50/60 Hz.
- Application for inspecting and measuring the speed of moving gears, fans, centrifuges, pumps, motors, general industrial maintenance, production, quality control, laboratories, schools, and colleges...

CERTIFICATES

ISO-9001, CE, IEC1010

Digital Stroboscope



FEATURES

* DT-2269 is a microprocessor circuit design, high accuracy, digital readout STROBOSCOPE. Adjusting the "Flash Rate" by push button keyboard, unique design in the world, easy operating & with intelligent function. That is ideal for inspecting and measuring the speed of moving gears, fans, centrifuges, pumps, motors and other equipment used in general industrial maintenance, production, quality control, laboratories and as well as for schools and colleges for demonstrating strobe action.

* External trigger input.

* RS232 computer interface output.

SPECIFICATIONS

Display	14 mm (0.56") LED, 6 digits.	External trigger	Input signal : 5V to 30 V rms, 5 to 10,500 RPM.
Set up unit	Flash rate - RPM/FPM, Hz * <i>FPM - flash per minute.</i>		0.083 to 175 Hz.
Flash rate set up range	RPM 5 to 12,500 RPM. Hz 0.083 to 175 Hz.	Power supply	AC 110V 10%, 50/60 Hz. or AC 220V 10%, 50/60 Hz. or AC 230V 10%, 50/60 Hz.
Resolution (<i>internal trigger</i>)	RPM/ FPM 0.1 RPM <i>5 to 999.9 RPM</i> 1 RPM <i>1,000 to 9,999 RPM</i> 10 RPM <i>10,000 to 12,500 RPM</i> Hz 0.001 Hz <i>< 10 Hz</i> 0.01 Hz <i>10 Hz - 99.99 Hz</i> 0.1 Hz <i>100 - 208 Hz</i>	Circuit	This stroboscope/tachometer employs an custom one-chip of microcomputer LSI circuit & crystal control time base which results in extraordinary accuracy & high set up stability over a wide, dynamic range.
Accuracy	$\pm (0.15 \% + 0.2 \text{ RPM }) \text{ rdg.}$ <i>< 1,000 RPM</i> $\pm (0.5 \% + 1 \text{ RPM }) \text{ rdg.}$ <i>1,000 to 3,300 RPM</i> $\pm 1 \% \text{ FS.}$ <i>3,301, to 12,500 RPM</i> <i>rdg : reading, FS : full scale</i>	Power consumption	Less than 30 Watt.
Switch Select Function	RPM, Hz Fine adjust, Coarse adjust, Multiply by 2, Divide by 2, Fast finder, Memory recall.	Dimension	21 x 12 x 12 cm (8.3 x 4.8 x 4.8 inch).
Memory	Can memorize 10 sets of measuring data.	Weight	1Kg/2.2 LB.
Set up stability	1 digit within 10 minute.	Housing case	Compact and impact plastic injection case with plastic mirror type reflector.
Data output	RS 232 computer interface.	Calibration	Crystal time base and microprocessor circuit, not necessary take any external calibration procedure if the stroboscope working properly.
Operating temp.	0 to 50 °C (32 to 122 °F).	Accessories included	Operation manual. 1 PC. Power cord. 1 PC.
Operating humidity	Less than 80% R.H.	Optional Accessories	* RS232 cable. UPGB-02 * USB cable..... USB-01. * Data Acquisition software SW-U801-WIN.
Operating duty Cycle	For prolong life and safe operation, please adhere to the following duty cycle: < 2000 RPM - 2 hours, 2000 to 3600 RPM - one hour, 3601 to 8000 RPM - 30 minutes, > 8000 RPM - 10 minutes. * 10 min. cooling off period between cycles.		

Digital Stroboscope



FLASH TUBE SPECIFICATIONS			
Flash tube	Xenon lamp.	Flash tube replacement	It is required to change the flash tube when the instrument start to flash irregularly at speeds of 3600 RPM/FPM or more.
Flash Duration	Approximately 60 to 1,000 microseconds.		
Flash color	Xenon white 6,500 K degree		
Flash energy	4 Watts-seconds (joules).		
Beam Angle	80 degrees.		

OPERATIONS PROCEDURES	
Preparation	(a) Plug unit into a properly grounded 110V AC, 220V AC or 230V AC outlet. (b) Turn the power switch to " on " position. (c) Determine the range switch to " Low " or " High " position.
Checking Speed	When checking speed, care must be taken to insure that the strobe is flashing in unison (one to one) with the object being monitored. A Stroboscope will also stop motion at 2:1, 3:1, 4:1 et., this is normally referred to as harmonies. To be sure of unison, turn the dial until two images appear - this will double the actual speed. Then lower the flashing rate until a single and stationary image appears - this is the actual true speed.
Checking Motion	For motion analysis, simply locate the actual speed as mentioned above and then turn the dial slowly up or down. This will give a slow motion effect allowing complete inspection.

Remark	When order the stroboscope, should inform the power supply type is AC 110V, or 220 V or 230V.
--------	---

Part Number Table

Description	Part Number
Digital Stroboscope	72-7601

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016

