

CDF600-2200

Connection Device Fieldbus

4DPROCONNECTIVITY





Ordering information

Туре	Part no.
CDF600-2200	1062460

Please note that for installation of new hardware with firmware V2.01, new GSD files (min V2.00) are recommended and available under "Downloads". It is also possible to use old GSD files for installation of new hardware. Do not use new GSD files (min V2.00) for installations with old hardware. You can find information on the device and software releases in the SICK SupportPortal. You must register before logging in.

Other models and accessories → www.sick.com/Connection_Device_Fieldbus



Detailed technical data

Features

1 Catalog		
Brief description	Fieldbus proxy/gateway for connecting one identification sensor to PROFINET-IO networks (interface 2 x M12, female connector/female connector, 4-pin)	
Supported products	Lector® series CLV61x - CLV65x CLV69x RFID read/write device Mobile handheld scanners	
Cloning module support (CMC)	Integrated	
Supports display module (CMD)	No	
Supports power supply module (CMP)	No	
Supports fieldbus gateway (CMF)	No	

Mechanics/electronics

Connection type	1 x "DEVICE" connection, 15-pin D-sub HD female connector with seal 1 x "POWER" connection, 5-pin M12 plug, A-coded 1 x "EXT. IN 1" connection, 5-pin M12 female connector, A-coded 1 x "PROFINET P1" connection, 4-pin M12 female connector, D-coded 1 x "PROFINET P2" connection, 4-pin M12 socket, D-coded 1 x "USB" connection, 5-pin micro-B socket, for configuration/diagnostics, behind screw-mounted cover
Supply voltage	(10 V DC 30 V DC)
Power consumption	< 5 W, if no sensor is connected and the digital input is not connected
Housing	Aluminum (unpainted)
Housing color	Aluminum (unpainted)
Enclosure rating	IP65
Protection class	III
Weight	+ 361 g
Dimensions (L x W x H)	207 mm x 49.5 mm x 40.7 mm
Scanner connection	RS-232

Interfaces

Function		
Data transmission rate		
Serial √, RS-232		
Function	AUX	
Data transmission rate	57.6 kBaud	
CAN	√	
Remark	Depending on sensor connected	
Digital inputs	1	
Digital outputs	0	
Optical indicators	6 LEDs	
Configuration software	SOPAS ET	


Ambient data


Electromagnetic compatibility (EMC)	EN 61000-6-3/A1:2011-03 / EN 61000-6-2:2005-08
Vibration resistance	EN 60068-2-6:2008-02
Shock resistance	EN 60068-2-27:2009-05
Ambient operating temperature	-35 °C +50 °C
Storage temperature	-35 °C +70 °C
Permissible relative humidity	< 90 %, Non-condensing


Classifications

eCl@ss 5.0	27242208
eCl@ss 5.1.4	27242608
eCl@ss 6.0	27242608
eCl@ss 6.2	27242608
eCl@ss 7.0	27242608
eCl@ss 8.0	27242608
eCl@ss 8.1	27242608
eCl@ss 9.0	27242608
eCl@ss 10.0	27242608
eCl@ss 11.0	27242608
eCl@ss 12.0	27242608
ETIM 5.0	EC001604
ETIM 6.0	EC001604
ETIM 7.0	EC001604
ETIM 8.0	EC001604
UNSPSC 16.0901	32151705

Dimensional drawing (Dimensions in mm (inch))







- ① Elongated mounting hole (2 x), for mounting with M6 screw
- ② "PROFINET P2" connection, 4-pin M12 socket, D-coded
- ③ "PROFINET P1" connection, 4-pin M12 female connector, D-coded
- ④ "EXT. IN 1" connection, 5-pin M12 female connector, A-coded
- ⑤ "POWER" connection, 5-pin M12 plug, A-coded
- ⑥ "DEVICE" connection, 15-pin D-sub HD female connector with seal
- ① LED (6 x), status display (POWER, EXT. IN 1, SF, BF, P1 LNK/ACT, P2 LNK/ACT)
- ® Rotary encoding switch "Mode", for operating mode, behind screw-mounted cover
- (9) "USB" connection, 5-pin micro-B socket, for configuration/diagnostics, behind screw-mounted cover
- ® Screw (Torx T8), captive (2 x), for cover
- 1 Elongated mounting hole (2 x), for mounting with M6 screw

Recommended accessories

Other models and accessories → www.sick.com/Connection_Device_Fieldbus

	Brief description	Туре	Part no.
Plug connecto	ors and cables		
1	Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, shielded, 5 m	YF2A25- 050UB6XLEAX	2095733
100	Head A: male connector, USB-A Head B: male connector, Micro-B Cable: USB 2.0, unshielded, 2 m	USB cable	6036106
1	Head A: female connector, M12, 17-pin, straight Head B: male connector, D-Sub-HD, 15-pin, straight Cable: Power, serial, CAN, digital I/Os, shielded, 3 m	YF2Z1D- 030XXXMHDAC	2055420

CDF600-2200 | Connection Device Fieldbus

4DPROCONNECTIVITY

	Brief description	Туре	Part no.
6 6	Head A: male connector, M12, 4-pin, straight, D-coded Head B: male connector, M12, 4-pin, straight, D-coded Cable: Ethernet, PROFINET, PUR, halogen-free, shielded, 2 m	YM2D24- 020PN1M2D24	2106159

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com

