

ZCKL8H7

Limit switch body, Limit switches XC Standard,
ZCKL, 2 NO, slow break, 1/2"NPT



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch body
Device short name	ZCKL
Body type	Fixed
Product Compatibility	XCKL
Associated head	ZCKD029 ZCKD59 ZCKD02 ZCKD23 ZCKD21 ZCKD239 ZCKD10 ZCKD109 ZCKD81 ZCKD41 ZCKD06 ZCKD16 ZCKD91 ZCKD15 ZCKD08 ZCKD05 ZCKD17 ZCKD219
Body material	Metal
Cable entry	1 entry tapped for 1/2" NPT conduit
Number of poles	2
Contacts type and composition	2 NO
Contact operation	Slow-break, simultaneous
Number of steps	1 1 position
Contacts material	Silver plated contacts

Complementary

Local display	Without
Electrical connection	Screw-clamp terminals 1 x 0.5...2 x 2.5 mm ²
Positive opening	Without
Minimum actuation speed	6 m/min
[Ie] rated operational current	3 A 240 V, AC-15, A300 EN/IEC 60947-5-1 appendix A 0.27 A 250 V, DC-13, Q300 EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	500 V 3)IEC 60947-1 contact block 300 VCSA C22.2 No 14 contact block 300 VUL 508 contact block
Maximum resistance across terminals	0.25 mOhm IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	4 kV IEC 60664 4 kV IEC 60947-1
Short-circuit protection	6 A cartridge fuse gG
Electrical durability	5000000 Cycles, DC-13 120 V, 1 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13 24 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 2 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C
Width	2.05 in (52 mm)
Height	2.83 in (72 mm)
Depth	1.18 in (30 mm)

Net Weight	0.46 lb(US) (0.21 kg)
Terminals description ISO n°1	(21-22)NC (31-32)NC (13-14)NO

Environment

IP Degree of Protection	IP66
IK Degree of Protection	IK05
Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	US1000T22449
Discount Schedule	000T
GTIN	3389118130135
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	No need of specific recycling operations
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------