

CRIMPFOX CENTRUS 10S - Crimping pliers



1213154

<https://www.phoenixcontact.com/in/products/1213154>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² .. 10 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Your advantages

- Pressure lock ensures consistently high quality crimping results
- Ergonomic handle design ensures comfortable, fatigue-free handling
- With a particularly small handle width, the tool fits perfectly in your hand
- Up to 30 % lower actuation force, thanks to optimized leverage
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping

Commercial data

Item number	1213154
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH3
Product key	BH3131
Catalog page	Page 420 (C-3-2019)
GTIN	4055626212623
Weight per piece (including packing)	457 g
Weight per piece (excluding packing)	377.9 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX CENTRUS 10S - Crimping pliers



1213154

<https://www.phoenixcontact.com/in/products/1213154>

Technical data

Notes

General	DIN 46228-1, DIN 46228-4
Environmental Product Compliance	
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Square crimp

Crimping position 1

Min. cross section	0.14 mm ²
Max. cross section	10 mm ²
AWG min	26
AWG max	8

Connection data

Conductor connection

Cross section range, metric	0.14 mm ² ... 10 mm ² (2 x 0.5 mm ² ... 2 x 4 mm ²)
Cross section range AWG	26 ... 8 (2 x AWG 20 ... 12)

Dimensions

Width	70 mm
Height	21 mm
Length	180 mm

Material specifications

Color	black/green
-------	-------------

Mounting

Thread type	()
-------------	----

CRIMPFOX CENTRUS 10S - Crimping pliers



1213154

<https://www.phoenixcontact.com/in/products/1213154>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1213154>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX CENTRUS 10S - Crimping pliers



1213154

<https://www.phoenixcontact.com/in/products/1213154>

Classifications

ECLASS

ECLASS-11.0	21043811
ECLASS-12.0	21043811
ECLASS-13.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX CENTRUS 10S - Crimping pliers



1213154
<https://www.phoenixcontact.com/in/products/1213154>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in