



## Main

Device short name	F
Enclosure type	Standard environment enclosure indoor
Product Specific Application	Control electrically driven water pumps
Quantity per Set	Set of 20
Range of Product	Square D Pumptrol
Switch application	Standard
Type of Packing	Bulk

## Complementary

Adjustable range on rising pressure	20...65 psi (137.90...448.16 kPa)
Approximate adjustable differential	15...30 psi (103.42...206.84 kPa)
Depth	2.78 in (70.61 mm)
Electrical connection	Line screw clamp terminal Load slip-on terminal
Fixing Mode	By brackets
Fluid connection type	0.25 inch NPT external
Height	2.8 in (71.12 mm)
Material	Zinc plated steel: flange
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	220 psig
Maximum Horse Power Rating	2 Hp 115 V AC, 3 phase 1.5 Hp 115 V AC, 1 phase 3 Hp 230 V AC, 3 phase 2 Hp 230 V AC, 1 phase 1 hp 460/575 V AC, 3 phase
Number of poles	2
Permissible voltage	575 V AC
Pressure actuator	Diaphragm
Pressure setting range	30...50 psi (206.84...344.74 kPa)
Net Weight	1.13 lb(US) (0.51 kg)
Range on decreasing pressure	10...45 psi (68.95...310.26 kPa)
Scale type	Adjustable differential
Switch function	DPST
Width	3.76 in (95.50 mm)

## Environment

NEMA Degree of Protection	NEMA 1
Product Certifications	CSA file LR25490[RETURN]UL listed file E12158 CCN NKPZ

## Ordering and shipping details

Category	US10CP721532
Discount Schedule	OCP7
GTIN	785901166986
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 in (25.806 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Package 1 Weight	16.00 oz (453.592 g)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

## Contractual warranty

Warranty	18 months
----------	-----------