

Phase Sequence and Motor Rotation Meter



Specifications

Basic Functions	Range	Best Accuracy
AC Voltage (V)	40V to 690V	√
Frequency Range (Hz)	15Hz to 400Hz	
Test Current (A)	< 1mA	

Special Functions

Phase Sequence Indication		LCD
Missing Phase Indication		LCD
Motor Rotation Indication		

General Characteristics

Power	: No Battery Required
Product Colour	: Orange & Grey
Product Weight	: 180g
Product Size	: 70mm × 75mm × 30mm

Accessories	Qty.	Note
Operating Manual	1 piece	-
Test Leads	1 pair	Material: Double insulated wire, 102 cores Length: 1090mm Safety level: CAT III 600V/CAT IV 300V
Alligator Clip	3 pieces	Specifications: Length 75mm, opening 27mm Safety level: CAT III 1000V/CAT IV 600V 10A
Cloth bag	1 piece	-

Part Number Table

Description	Part Number
Phase Sequence and Motor Rotation Meter	72-3515

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

