



Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch base
Device short name	9007C
Body type	Compact plug-in
Product Compatibility	9007C
Electrical connection	Screw-clamp terminals AWG 22...AWG 12), 1...2
Cable entry	1 entry for 1/2" - 14 NPT ANSI B1.20.1
Ambient air temperature for operation	-20...185 °F (-29...85 °C) standard environment
Environmental characteristic	Standard environment
Sale per indivisible quantity	1

Complementary

Associated head	9007C
Associated connection component	9007CO52
Body material	Zinc
Function Available	-
Mechanical durability	10000000 cycles
Width	1.55 in (39.37 mm)
Height	2.26 in (57.40 mm)
Depth	0.9 in (22.86 mm)
Net Weight	0.75 lb(US) (0.34 kg)

Environment

Shock resistance	60 gn 9 ms IEC 60068-2-27
Vibration resistance	25 gn 10...150 Hz)IEC 60068-2-6
NEMA degree of protection	NEMA 1 Nema type 250 NEMA 2 Nema type 250 NEMA 4 Nema type 250 NEMA 6 Nema type 250 NEMA 6P Nema type 250 NEMA 12 Nema type 250 NEMA 13 Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Electrical shock protection class	Class 0 IEC 61140
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Protective treatment	Epoxy powder coat

Ordering and shipping details

Category	US10DS121499
Discount Schedule	0DS1
GTIN	785901812265
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.69 in (4.3 cm)
Package 1 Width	2.80 in (7.1 cm)
Package 1 Length	4.29 in (10.9 cm)
Package 1 Weight	5.76 oz (163.3 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------