

Description

MP780922 is a rugged and ergonomically designed thermal camera, powerful and user friendly with great performance and attractive price, with 120×90 pixels IR resolution which can automatically track the objective's temperature from -20°C to 400°C. It is an affordable professional troubleshooting tool, widely used in many applications.



Features

- Durable and user-friendly
- 8" TFT display screen (320×240 Pixels)
- IR resolution: 120×90
- Temperature measurement range: -20°C to 400°C / -4°F to 752°F
- Auto alarm for high/low temperature
- Auto tracking for hot spot/cold spot
- Image capture
- Image modess: Thermal, Visual image, Fusion
- Color palettes: 5(White hot, Black hot, Red hot, Ironbow, Rainbow)
- LED flashlight
- PC software analysis
- Rechargeable Li-ion battery
- 1/4" tripod mounting hole
- IP65
- 2m drop proof"

Specifications

IR resolution (Pixels)	120 × 90
Display	2.8" TFT LCD (320 × 240)
Field of view (FOV)	50° × 38°
Thermal sensitivity (NETD)	≤60mK
Spatial resolution (IFOV)	7.3mrad
Frame rate	≤25Hz
Focus	Focus Free
Temperature measurement range	-20°C to 400°C
Accuracy	±2°C or ±2% whichever is greater
Emissivity	0.01 to 1.00 adjustable

Functions	
Colour palettes	5 (White hot, Black hot, Red hot, Ironbow, Rainbow)
Image modes	Thermal, Visual image, Fusion
Digital camera resolution	640 × 480
Hi/Lo temperature alarm	Icon, LED flashlight, Buzzer
PC software analysis	√
General Characteristics	
Battery	Fixed Li-ion battery (3.6V 5000mAh)
Battery operation time	≥6 hours
USB	Type-C
IP rating	IP65
Drop proof	2m
Storage	Up to 32GB Micro SD card
Image/Video storage format	BMP
Product net weight	910g
Product size	236mm × 75.5mm × 86mm

Accessories	Qty.	Note
Operating Manual	1 piece	-
USB interface cable		Type-C UL2725 (#24+28)×4C Charging band Data Transfer Black L = 2m (RoHS) USB/AM+Type-C

Part Number Table

Description	Part Number
Thermal Imager, 120×90 Pixels, 50°×38°, -20°C to 400°C, 8" TFT	MP780922

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.