




Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Jumpers & Shunts



Shunt Type: **Novo**
Shunt Style: **Open Top**
Number of Positions: **2**
Centerline (Pitch): **2.54 mm [.1 in]**
Contact Current Rating (Max): **3 A**

Features

Product Type Features

Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Termination Resistance	15 mΩ
------------------------	-------

Body Features

Handle	With
Primary Product Color	Black

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Shunt Type	Novo
Shunt Style	Open Top
Contact Current Rating (Max)	3 A

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------



Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Product Height	5.8 mm[.228 in]
----------------	-----------------

Usage Conditions

Operating Temperature Range	-65 – 60 °C[-85 – 140 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Jumper & Shunt Packaging	Loose Piece
Packaging Quantity	14000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5-146282-2
02 MODII HDR SRST B/A .100CL

TE Part # 5-146274-2
02 MODII HDR SRST B/A .100CL

TE Part # 5-146278-2
02 MODII HDR SRST B/A .100CL

Also in the Series | Modu Connector System

Automotive Connector Caps & Covers
(3)

Board-to-Board Jumpers & Shunts(5)

Connector Caps & Covers(1)

Connector Hardware(4)

PCB Headers & Receptacles(1110)

Customers Also Bought

TE Part #1-2176231-7
3522 47R 1% 3W

TE Part #1276565-1
EXTRACTION TOOL FOR .025 REC

TE Part #5-1579007-3
EXTRACTION TOOL

TE Part #6-1625890-7
2W SM M/OX 5% 6K8



TE Part #1924678-1
26P SMT LAC HDR ASY, KEY AE, Hand Mate

TE Part #1891600-1
EXTRACTION TOOL

TE Part #2008625-2
Socket Micro MNL, GOLD 22-18

TE Part #2-2176422-3
TLRP 2512 3.0W R020 1% 25PPM 4K RL

TE Part #2047050-1
Extraction Tool, 0.5/1.0 Sealed Contact

TE Part #839010-E
IDCCS SRC 1,27 2 * SFX SFX 100 PVC

Documents

Product Drawings

AMP SHUNT ASS'Y

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-881545-4_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-881545-4_K.3d_igs.zip

English

Customer View Model

ENG_CVM_1-881545-4_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

Agency Approval Document

English