
5

Ouartz Plus Hour Meters — 85000 Series



Honeywell's 85000 Series Quartz Plus meters are direct current hour meters that provide legendary performance and reliability in a technically advanced quartz package. The Quartz Plus features a rugged drive mechanism inside a shock-proof, tamperproof, totally sealed case.

Fig. C

- Custom CMOS Integrated Circuit
- Totally Sealed Case
 Temperature Range: –40°F to +185°F
 (–40°C to +85°C)
- Shock and Vibration Resistant
- UL Recognized and CSA Certified Running Indicator 3 mm (0.12") Numeral Height Transient Votage and Reverse Polarity Protected Standard Terminals: ¹/₄* Male Blade

Direct Current Hour Meters

Stock No.	Mfr.'s Type	Fig.	Description	Voltage Range	Electrical Termination	EACH
70111629 70111605 70111606 70111630 70111607 70111608 70111598 70111609	85000-12 85094-12 85331-12 85127-12 85097-02 85093-03 85098-03 85342-03	A A A B C C C	2-Screw Mount 2-Screw Mount 2-Screw Mount 2-Screw Mount, 100K Hours 3-Screw Mount Round (2.27" Black Bezel) Round (2.50" Chrome Bezel) Round (2.27" Chrome Bezel)	10.0-32 VDC 10.0-80 VDC 6.5-16 VDC 10.0-80 VDC 10.0-80 VDC 10.0-80 VDC 10.0-80 VDC 10.0-80 VDC	1/4" Blade 1/4" Blade 1/4" Blade 1/4" Blade 1/4" Blade 1/4" Blade 1/4" Blade 1/4" Blade 1/4" Blade	34.57 30.80 52.04 45.79 30.13 47.11 37.53 33.13

AC Hour Meters — 20000 Series



HOURS Fig. A





Fig. C

Honeywell's 20000 Series AC hour meters provide an accurate means of tracking run time on all types of equipment, whether for testing purposes, leasing applications, maintenance records or warranty programs. The synchronous motor is integrated into the chassis as one substructure for maximum reliability, and the complete unit is installed in a totally sealed case.

- Single-Phase Synchronous, Permanently-Lubricated
- Motor
 Temperature Range: -65°F to +154°F
 (-54°C to +68°C)
- Shock and Vibration Resistant
 UL Recognized, CSA Certified, CE Mark
 3.0 Watts Power Rating
 3 mm (0.12") Numeral Height

Stock No.	Mfr.'s Type	Fig.	Description	Voltage Range	Freq. (Hz)	Electrical Termination	EACH
70111631 70111610 70111602 70111519 70111603 70111604 70111611 70111612 70111613	20001-17 20007-17 20028-17 20035-17 20017-14 20019-14 20116-23 20177-23 20182-23	A A A B B C C C	2-Screw Mount 2-Screw Mount 2-Screw Mount 2-Screw Mount 3-Screw Mount 3-Screw Mount Retainer Mount Retainer Mount	108-132 VAC 216-264 VAC 108-132 VAC 108-132 VAC 108-132 VAC 216-264 VAC 108-132 VAC 216-264 VAC 108-132 VAC	60 60 50 60 60 60 60 60	8-32 8-32 Wire Lead 8-32 8-32 8-32 8-32 1/4" Blade	30.20 27.42 45.70 28.63 28.34 37.29 25.60 49.49 32.71

LCD Hour Meters — LM Series







Round



Standard

Honeywell's MCU (microcontroller unit) LCD (liquid crystal display) Hour Meters, LM Series, are sealed digital instruments designed to monitor and record elapsed running time, normally displayed in hours and tenths of hours. These devices are used to log running time of equipment used in transportation applications to assure proper maintenance expensive machines or systems. This maintenance typically involves replacing, changing, or checking parts, belts, filters, oil, and lubrication of heavy duty equipment, or running condition of engines, motors, and blowers, to name a few. These devices feature a 40-year memory data retention (without power) to provide customers with a long data retention capability within their desired application. The large 7 mm display eases readability and offers backlight options and a running indicator. Sealing to IP67 provides enhanced durability. The hour meter also features a long reset time to offer customers the protection against malfunction of reset. The LM Series offers customization options including the customer's logo, Honeywell logo, or a black face as well as numerous customization options. a black face, as well as numerous customizable port options.

All meters below have V_4 -inch blade terminals and are marked with the Honeywell logo — for 3/16-inch terminals and custom logos, please contact your local Allied sales office.

- Backlight and Large 7 mm Display Ease Readability

- Digital, Microcontroller Unit LCD
 Durable Design of Mounting Assembly
 IP67 Environmental Sealing Provides Enhanced Durability
- 1P67 Environmental Sealing Provides Enhanced Durability
 Customizable with Customer's Logo, as Well as Numerous Customizable Port Options
 Function Types, Including Hour Meter (Measures Time) or Counter (Measures Number of Instances, Starts, etc.)
 Fast Delivery of Samples and Products Due to Honeywell's Integrated Supply Chain and Global Design Center
 Shock and Vibration Resistance Allow for Use in a Wide Variety of Tough Applications

Stock No.	Mfr.'s Type	Shape	chape Connector Definition		EACH
70378422 70378423 70378424 70378425 70378426 70378427 70378428	LM-HB4AS-H11 LM-HS2AS-H11 LM-HB2AS-H31 LM-HH2AS-H21 LM-HH4AS-H21 LM-HS4AS-H11 LM-HB4AS-H31	Round Diamond Round Diamond Diamond Standard Round	Positive/Negative/Reset/Enable Positive/Negative Positive/Negative Positive/Negative/Reset/Enable Positive/Negative/Reset/Enable Positive/Negative/Reset/Enable	Black Black Black Black Black — Black	24.43 24.00 24.00 26.68 27.14 24.43 24.43

Diochron Hour Meters



Fig. A





Fig. C

- Quartz Accuracy: ±0.02% (±200 ppm) Sealed, Shock-Resistant Case Run Indicator

- Voltage Range: 10-80 VDC
- Temperature Range: -40°F to +185°F



Fig. B



Fia. D

- Numeral Size: 0.12'
- UL Recognized CSA Certified
- Polycarbonate Case and Lens 1/4" Blade Terminals

Stock No.	Mfr.'s Type	Fig.	Description	Voltage Range	EACH
70111535 70111536 70111537 70111538	82450-83 82451-84 82452-82 82453-85	A B C	2-Screw Retainer, Round Black Bezel Retainer, Rectangular Bezel 3-Screw	10-80 VDC 10-80 VDC 10-80 VDC 10-80 VDC	27.32 28.91 25.19 25.19