




Part Number : [5018643091](#)
Product Description : 0.50mm Pitch Easy-On FFC/FPC-to-Board Connector, Receptacle Housing Assembly, Right-Angle, Surface Mount, with Grounding Terminals, Gold (Au) Plating, 30 Circuits
Series Number : 501864
Status : Active
Product Category : FFC / FPC Connectors



Documents & Resources

Drawings
[Drawing 5018643091_sd.pdf](#)

3D Models and Design Files
[2D Drawing DXF 5018643091.dxf](#)
[2D Drawing DXF \(PDF\) 5018643091.pdf](#)
[3D Model 5018643091_stp.zip](#)

Specifications
[Packaging Specification 5018649200-SPK-200.pdf](#)
[Product Specification PS-501864-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	501864
Description	0.50mm Pitch Easy-On FFC/FPC-to-Board Connector, Receptacle Housing Assembly, Right-Angle, Surface Mount, with Grounding Terminals, Gold (Au) Plating, 30 Circuits
Comments	Requires a custom FFC/FPC with notches
Product Family	Easy-On FFC FPC Connectors
Product Name	Easy-On
UPC	822350663427

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	Flexi-Latch
Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Contact Position	Bottom

Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	4.85mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	741.465/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Plating min - Mating	0.100µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FFC/FPC

Solder Process Data

Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	250

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.50mm Pitch Premo-Flex LVDS Jumpers, 100±10 Ohms Differential Impedance	<u>15022</u>
0.50mm Pitch Premo-Flex LVDS Jumpers, 90±10 Ohms Differential Impedance	<u>15922</u>

Use with Part(s)

Description	Part Number
0.50mm Pitch FFC-to-Board Plug Jacket, 30 Circuits	<u>5017833009</u>
0.50mm Pitch FFC-to-Board Plug Jacket Cover, 30 Circuits	<u>5017843008</u>