


CUI INC

a bel group


date 01/11/2024

page 1 of 5

SERIES: VOF-150 | DESCRIPTION: AC-DC POWER SUPPLY

FEATURES

- up to 150 W continuous power
- compact size
- universal input (90~277 Vac)
- single output from 5~48 Vdc
- active power factor correction
- user trimmable output voltage option
- no load power consumption <0.34W
- 3000 Vac isolation
- over current, over voltage, and short circuit protections
- UL/cUL and TUV 60950-1 safety approvals
- efficiency up to 90%



MODEL	output voltage (Vdc)	output current max (A)	output power max (W)	ripple and noise ¹ max (mVp-p)	efficiency typ (%)
VOF-150-5	5	18	90	120	83
VOF-150-12*	12	12.5	150	120	87
VOF-150-15	15	10	150	150	88
VOF-150-24	24	6.3	150	240	88
VOF-150-36	36	4.2	150	360	89
VOF-150-48*	48	3.2	150	480	90

Notes: 1. Ripple & noise are measured at 20 MHz BW with 0.1 μ F ceramic cap and a 10 μ F electrolytic capacitors on the output and the two earth ground pads are connected to input earth ground.
2. * Discontinued model.

PART NUMBER KEY

VOF-150 - XX

Base Number

Output Voltage

INPUT

parameter	conditions/description	min	typ	max	units
voltage		90		277	Vac
frequency		47		63	Hz
input current	at 115 Vac, full load at 230 Vac, full load		2.0 1.0		A A
inrush current	at 230 Vac, cold start		80		A
leakage current	at 277 Vac			3.5	mA
power factor		0.9			
no load power consumption	at 110 Vac at 230 Vac			0.34 0.35	W W
input fuse	6.3 A/250V time delay fuse (included)				

OUTPUT

parameter	conditions/description	min	typ	max	units
line regulation	low line to high line		±0.5		%
load regulation	full load to 10% load		±1		%
initial set point accuracy			±3		%
transient response	1 kHz, 10~100% load VOF-150-5 VOF-150-12 VOF-150-15 VOF-150-24 VOF-150-36 VOF-150-48		500 1200 1500 2400 3600 4800		mVp-p mVp-p mVp-p mVp-p mVp-p mVp-p
hold-up time	at 115 Vac, full load	8			ms
start-up time	at 115 Vac, full load		50		ms
start-up delay	at 115 Vac, full load		1000		ms
adjustability	built in trim pot		±5		%
temperature coefficient			±0.03		%/°C

PROTECTIONS

parameter	conditions/description	min	typ	max	units
short circuit protection	hiccup, auto recovery	105			%
over current protection	hiccup, auto recovery	105			%
over voltage protection	clamped by TVS				

SAFETY & COMPLIANCE



parameter	conditions/description	min	typ	max	units
isolation voltage	input to output input to ground output to ground	3,000 1,500 1,500			Vac Vac Vac
safety approvals	UL60950-1, EN60950-1				
EMI/EMC ¹	EN 55022: 2010 Class B, EN 61204-3:2000, EN 61000-6-3: 2007 +A1: 2011, EN 61000-3-2: 2006 +A2: 2009, EN 61000-3-3: 2008, EN 55024: 2010, EN 61000-6-1: 2007, ENV 50204: 1995, CE, FCC				
class	class II				
MTBF	as per MIL-HDBK-217F at 25 °C, full load	250,000			hours
RoHS	2011/65/EU				

Notes: 1. The power supply is considered a component which will be installed into final equipment. The final equipment still must be tested to meet the necessary EMC directives.

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature	see derating curves	-20		60	°C
storage temperature		-40		85	°C
operating humidity	non-condensing	20		90	%
storage humidity	non-condensing	20		90	%
operating altitude			5000		m
vibration & shock	10~3000Hz, 10 minutes per cycle, for 1 hour along each of the X, Y, and Z axes		2		G

DERATING CURVES



MECHANICAL


parameter	conditions/description	min	typ	max	units
dimensions	127 x 76.2 x 33.6 (5.00 x 3.00 x 1.32 inch)				mm
weight			368		g
cooling method	open frame (convection)				

MECHANICAL DRAWING

units: mm[inch]
tolerance: ± 0.30

CN1	
PIN	Function
1	L
2	NP
3	N

CN2	
PIN	Function
1	+Vo
2	+Vo
3	+Vo
4	+Vo
5	+Vo
6	-Vo
7	-Vo
8	-Vo
9	-Vo
10	-Vo



- Notes:
- CN1 mates with Molex housing 09-50-7031 with Molex 2478 series crimp contact or equivalent.
 - CN2 mates with Molex housing 09-50-7101 with Molex 2478 series crimp contact or equivalent.
 - All specifications are measured at $T_a=25^{\circ}\text{C}$, 230 Vac input voltage, and rated output load unless otherwise specified.

REVISION HISTORY

rev.	description	date
1.0	initial release	04/08/2014
1.01	updated datasheet	05/09/2014
1.02	company logo updated	11/30/2020
1.03	discontinued models VOF-150-12 & VOF-150-48	01/11/2024

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC
a bel group

Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.