GENERAL TECHNICAL DATA

Specifications, Directives and Standards



The Camden products listed in this catalogue are developed and manufactured according to the rules set out in IEC international publications and EN European standard.

Speci cations

· International Speci cations

The International Electrotechnical Commission, IEC, which is part of the International Standards Organization, ISO, publishes IEC publications which act as a basis for the world market.

· European Speci cations

The European Committee for Electrotechnical Standardisation (CENELEC), grouping 18 European countries, publishes EN standards for low voltage industrial apparatus.

These European standards di er very little from IEC international standards and use a similar numbering system. The same is true of national standards. Contradicting national standards are withdrawn.

Harmonised European Speci cations

The European Committees for Standardisation (CEN and CENELEC), grouping 18 European countries, publish EN standards relating to safety of machinery.

· Speci cations in Canada and the USA

These are equivalent, but di er markedly from IEC, UTE, VDE and BS speci cations.

UL Underwriters Laboratories (USA)

CSA Canadian Standards Association (Canada)

Remark concerning the label issued by the UL (USA). Two levels of acceptance between devices must be distinguished.

"Recognized" Authorised to be included in equipment, if the equipment in question has been entirely mounted and wired by quali ed personnel. They are not

valid for use as "General purpose products" as their possibilities are limited.

They bear the mark:

"Listed" Authorised to be included in equipment and for separate sale are "General purpose products" components in the USA.

They bear the mark: (4)

European Directives

The guarantee of free movement of goods within the European Community assumes elimination of any regulatory di erences between the member states. European Directives set up common rules that are included in the legislation of each state while contracditory regulations are cancelled.

There are three main directives:

- Low Voltage Directive 73/23/EEC, amended by Directive 93/68/EEC concerning electrical equipment from 50 to 1000 V a.c. and from 75 to 1500 V d.c.

 This speci es that compliance with the requirements that is sets out is acquired once the equipment conforms to the standards harmonised at European level:

 EN 60947-1 and EN-60947-5-1 fdimit switches.
- Machines Directives 89/392/EEC, 91/368/EEC, 93/44/EEC, 93/68/EEC de ning main safety and health requirements concerning design and manufacture of the machines and other equipment including safety components in European Union countries.
- Electromegnetic Compatibility Directive 89/336/EEC, amended b@irective 92/31/EEC and Directive 93/68/EEC concerning all electrical devices likely to create electromagnetic disturbances.

Signi cation of CE marking:

CE marking must not be confused with a quality label.

CE marking placed on a product is proof of conformity with the European Devices concerning the product.

CE marking is part of an administrative procedure and guarantees free movement of the product within the European Community.

Standards

International Standards

IEC 947-1 Low-voltage switchgear and controlgear - Part 1: General Rules (CEI EN 60947-1).

IEC 947-5-1 Low-voltage switchgear and controlgear - Part 5: Control circuit devices and switching elements - Section 1: Electromechanical control circ

cuit devices (CEI EN 60947-5-1) - Chapter 3: Special requirements for control switches with positive opening operation.

IEC 204-1 Electrical equipment on industrial machines - Part 1: General requirements (CEI EN 60204-1).

IEC 204-2 Electrical equipment on industrial machines - Part 2: Item designation and examples of drawings, diagrams, tables and instructions

IEC 529 Degrees of protection provided by enclosure (IP code) (CEI EN 60529).

GENERAL TECHNICAL DATA

Specifications, Directives and Standards



European Standards

EN 50005 Low-voltage switchgear and controlgear for industrial use - Terminal marking and distinctive number: General rules (CEI 17-17).

EN 50013 Low-voltage switchgear and controlgear for industrial use - Terminal marking and distinctive number for particular control switches (CEI 17-

17).

EN 50041 Low-voltage switchgear and controlgear for industrial use - Control switches - Position switches 42,5 x 80 - Dimensions and characteristics.

EN 50047 Low-voltage switchgear and controlgear for industrial use - Control switches - Position switches 30 x 55 - Dimensions and characteristics.

EN 60947-1 Low-voltage switchgear and controlgear for industrial use - Part 1: General rules (CEI EN 60947-1).

EN 60947-5-1 Low-voltage switchgear and controlgear for industrial use - Part 5: Control circuit devices and switching elements - Section 1:

Electromechanical control circuit devices (CEI EN 60947-5-1) - Chapter 3: Special requirements for control switches with positive opening

operation.

EN 60529 Degrees of protection provided by enclosures (IP code). **EN 61058-1** Switches for appliances. Part. 1: general requirements.

· Harmonised European Standards

These standards are common to all European Union and EFTA (European Free Trade Association) countries. They were prepared (prEN project) and written (EN nal text) by the European standardisation committees CEN or CENELEC. Harmonised European standards were drawn up to allow de nition of the rules and technical means to be used to satisfy the main safety requirements on machines and thus guarantee conformity with the Machines Directive. Compliance with a harmonised European standard is presumption of conformity with the relevant Directive.

European standards relating to machine safety are divided into groups (A, B and C types).

Type A standards: basic standards: setting out design principles and the general aspects valid for all machine types.

EN 292-1 Safety of machinery - Basic concepts, general principles for design - Part 1: Basic terminology, methodology. EN 262-2 and EN 292-2/A\$afety of machinery - Basic concepts, general principles for design - Part 2: Technical principles and specifications.

EN 1050 Safety of machinery - Principles for risk assessment.

Type B standards: group standards: **B1:** dealing with speci c safety aspects.

EN 60204-1 Safety of machinery - Electrical equipment of machines - Part 1: General requirements

EN 954-1 Safety of machinery - Safety-related parts of control systems - Part 1: General principles for design.

B2: dealing with components and devices determining safety.

EN 1088 Safety of machinery - Interlocking devices associated with guards - Principles for design and selection

Type C standards: speci c standards or standards per machine family giving detailed safety speci cations applicable to a machine or to a group of

machines

EN 81-1 Safety rules for the construction and installation of lifts - Part 1: Electric lifts.

American Standards

UL 508 Standard for safety. Industrial control equipment.CSA - C22.2 No. 14-95 Industrial control equipment. Industrial products.

LIMIT SWITCHES

Plastic or Metal Casing Terminolgy



Class II materials, according to IEC 536, are designed with double insulation. This measure consists in doubling the functional insulation with an additional layer of insulation so as to eliminate the risk of electric shock and thus not having to protect elsewhere. No conductive part of "double insulated" material should be connected to a protective conductor.

Positive Opening Operation ⊕

A control switch, with one or more break-contact elements, has a positive opening operation when the switch actuator ensures full contact opening of the break-contact. For the part of travel that separates the contacts, there must be a positive drive, with no resilient member (e.g. springs), between the moving contacts and the point of the actuator to which the actuating force is applied.

The positive opening operation does not deal with N.O. contacts.

Control switches with positive opening operation may be provided with either snap action or slow action contact elements. To use several contacts on the same control switch with positive opening operation, they must be electrically separated from each other, if not, only one may be used. Every control switch with positive opening operation must be indelibly marked on the outside with the symbol: \bigoplus .

Snap Action

Snap action contacts are characterised by a release position that is distinct from the operating position (di erential travel). Snap breaking of moving contacts is independent of the switch actuator's speed and contributes to regular electric performance even for slow switch actuator speeds

Slow Action


Slow action contacts are characterised by a release position that is the same as the operating position. The switch actuator's speed directly conditions the travel speed of contacts.

Contact shape according to IEC 947-5-1.

Change-over contact elements with 4 terminals must be indelibly marked with the corresponding Za or Zb symbol as in the diagrams below.



Contacts with the same polarity



The 2 moving contacts are electrically separated

Utilization Category

AC-15: switching of electromagnetic loads of electromagnets using an alternating current (>72 VA). DC-13: switching of electromagnets using a direct current.

Terminals

Limit switches with metal casings must have a terminal, for a protective conductor, that is placed inside the casing very close to the cable inlet and must be indelibly marked.

Minimum Actuation Force/Torque

The minimum amount of force/torque that is to be applied to the switch actuator to produce a change in contact position.


Minimum Force/Torque to achieve Positive Opening Operation

The minimum amount of force/torque that is to be applied to the switch actuator to ensure positive opening operation of the N.C contact.

LIMIT SWITCHES

Plastic or Metal Casing Travel and Operation Diagrams





P_o Free position:

position of the switch actuator when no external force is exerted on it.

P_A Operating position:

position of the switch actuator, under the e ect of force F1, when the contacts leave their initial free position

P_P Positive opening position:

position of the switch actuator from which positive opening is ensured.

L Max. travel position:

maximum acceptable travel position of the switch actuator under the e ect of a force F1.

P_R Release position:

position of the switch actuator when the contacts return to their initial free position.

C Pre-travel:

distance between the free position P_0 and the operating position $P_{\!\scriptscriptstyle A}$

C_P Positive opening travel:

minimum travel of the switch actuator, from the free position, to ensure positive opening operation of the normally closed contact.

C₂ Over-travel:

distance between the operating position $P_{\!A}$ and the max. travel position L.

G Max. travel:

distance between the free position P_0 and the max. travel position L.

C₃ Differential travel (C1-C4):

travel di $\,$ erence of the switch actuator between the operating position P_A and the release position P_R .

C₁ Release travel:

distance between the release position ${\rm P}_{\rm R}$ and the free position ${\rm P}_{\rm O}$.

Diagram for snap action contacts:





Diagram for non-overlapping slow action contacts:



Note: for slow action contacts, $C_3 = 0$, $C_{1.1} = \text{pre-travel}$ of contact 21-22, $C_{1.2} = \text{pre-travel}$ of contact 13-14

LIMIT SWITCHES

Plastic or Metal Casing Travel and Operation Diagrams



SUMMARY LIMIT SWITCHES

Snap action 1NO+1NC	13 21 Zb	00
111011110	14 22 ⊖	

Slow action break before make 1NO+1NC 14 22 Θ 01

Slow action make before break 1NO+1NC $_{14}^{13}$ $_{22}^{21}$ $_{\Theta}$ $_{O2}^{2}$

Simultaneous $\begin{vmatrix} 13 & 23 \\ 13 & 23 \end{vmatrix}$ Slow action $\begin{vmatrix} 13 & 23 \\ 13 & 24 \end{vmatrix}$ Zb 04

 $\begin{array}{c|c} \text{Snap action} & \begin{array}{c|c} & 11 & & 21 \\ \hline & 2NC & & & \\ & 12 & & 22 \end{array} & \begin{array}{c} 2b \\ \ominus \end{array} & \begin{array}{c} 05 \end{array}$


CE10....P













CE70 SERIES LIMIT SWITCHES

Pre-wired Metal Casing IP67-30mm width



Description Pre-wired

Pre-wired
Metal Casing IP67



General Technical Data

			Plastic Casing	Metal Casing		
Standards			Devices conform with international IEC 947-5-1			
		and European EN	60 947-5-1 standards			
Certi cations - Approvals			UL (upo	UL (upon request)		
Air temperature near the device			•			
during operation		°C	– 25 .	+ 70		
- for storage		°C	- 40 + 70			
Mounting positions			All positions are authorised			
Protection against electrical shocks (acc. to	IEC 536)		Class II	Class I		
Degree of protection (according to IEC 529 ar	nd EN 60 529)		IP	IP 67		
Degree of protection (according to UL50)			Type 1 enclosure	Type 4 - 4X - 6 enclosure		
			("indoor use only")	("outdoor use - raintight -		
				watertight corrosion resistant")		
EL CLES						
Electrical Data						
Rated insulation voltage Ui						
- according to IEC 947-1 and EN 60-947-1			400 V (degree of pollution 3)			
- according to UL 508 and CSA C22-2 n° 14			B 300, R 300			
Rated impulse withstand voltage Uimp		kV	4			
(according to IEC 947-1 and EN 60 947-1)	to IEC 947-1 and EN 60 947-1)					
	onventional free air thermal current I _{th} A		5			
(according to IEC 947-5-1) θ < 40 °C						
Short-circuit protection		Α	6			
U _e < 500 V a.c gG (gl) type fuses						
Rated operational current						
I _e / AC-15 (according to IEC 947-5-1)	24 V - 50/60 Hz	Α	5.0			
	120 V - 50/60 Hz	Α		.0		
	240 V - 50/60 Hz	Α	1.5			
$I_{ m e}$ / DC-13 (according to IEC 947-5-1)	24 V - d.c.	Α	1.1			
	125 V - d.c.	Α		22		
-	250 V - d.c.	Α	0.1			
Switching frequency	Сус	les/h		500		
Load factor		-		.5		
Resistance between contacts		$m\Omega$	25			
Mechanical durability			10 Millions	of Cycles		

CE70 SERIES LIMIT SWITCHES

Pre-wired Metal Casing IP67-30mm width



IM_ Nylon Roller Lever


Operating Head

Conformity / (N.C. contact with positive opening operation):

Max actuation speed [m/s]: 1.5

Min. force [N] or torque [Nm]: actuation / positive opening operation: 0.08/0.28

Weight (kg): 0.230



Part Number	Contact Block	Туре	Travel Diagram
CE70.00.IM	Snap Action Contacts (1NO + 1NC)	00	0 14° 26° 58° 74° 21 22
CE70.01.IM	Non overlapping Slow Action Contacts (1NO + 1NC)	01	0 27° 49° 74° 21.22 13.14 45°

FM_ Adjustable Lever with Nylon Roller


Operating Head

Conformity / (N.C. contact with positive opening operation):

Max actuation speed [m/s]: 1.5

Min. force [N] or torque [Nm]: actuation / positive opening operation: 0.08/0.28

Weight (kg): 0.240



Part Number	Contact Block	Туре	Travel Diagram
CE70.00.FM	Snap Action Contacts (1NO + 1NC)	00	0 14°26° 58° 74° 21.42
CE70.01.FM	Non overlapping Slow Action Contacts (1NO + 1NC)	01	0 27° 49° 74° 21-22 13-14 45°