

Compact Mechanical Tachometers
Deumo 1, 2 & 3

A range of three Mechanical Tachometers are designed to cover speed ranges suitable for most general purpose contact speed measurement of rpm or linear speed in metres per minute. Direct reading - no calculation or reading conversion needed, the clear dial & fine pointer provide very good readability on this very long scaled instrument.



Deumo 1 illustrated



Top left - Shows red pointer lock button
 Bottom left - Shows range change selector
 Right - Shows Tachometer & kit
 Supplied complete with 2 x rpm cones, linear speed disc & carrycase

- Three measuring ranges on each model
- Direct rpm & metres/min reading
- Clear reading - very long scale dial.
- Very wide speed range
- Reading Hold- Pointer Lock feature
- Hand held portable
- Self powered - no batteries required

Common features
 Range selector - 3 position switch
 Accuracy - +/- 0.5% fsd
 Memory - Mechanical pointer lock
Accessories
 2 x rpm cone
 1 x female cone
 1 x Metric disc
 Carrycase & instructions

Speed Ranges	DEUMO 1	DEUMO 2	DEUMO 3
i. . 40 - 500 rpm	24 - 300 rpm	16 - 200 rpm	
ii. . 400 - 5000 rpm	240 - 3000 rpm	160 - 2000 rpm	
iii. . 4000 - 50000 rpm	2400 - 30,000 rpm	1600 - 20,000 rpm	