

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 2214C Page 1 of 1 Pages	Issue: 3 Issue Date: 5/19/2005 Effective Date: 8/1/2005
---	--

- A. Construction** Diameters (In)
- 1) Component 1 4 X 1 PAIR
 - a) Conductor 22 (7/30) AWG TC
 - b) Insulation 0.010" Wall, Nom. PVC 0.050
 - (1) Color Code Alpha Wire Company Color Code A

Pair	Color	Pair	Color	Pair	Color
1	BLACK-RED	3	BLACK-GREEN		
2	BLACK-WHITE	4	BLACK-BLUE		

- c) Pair 2/Cond Cabled Together
 - (1) Twists: 8.0 Twists/foot (min)
- 2) Cable Assembly 4 Components Cabled
 - a) Twists: 4.0 Twists/foot (min)
- 3) Shield: Alum/Mylar Tape, 25% Overlap, Min.
 - a) Foil Direction Foil Facing Out
 - b) Drain Wire 22 (7/30) AWG TC
- 4) Jacket 0.032" Wall, Nom.,PVC 0.266 (0.281 Max.)
 - a) Color(s) SLATE
 - b) Print ALPHA WIRE-* P/N 2214C 4PR 22 AWG
SHIELDED 75C (UL) TYPE CM OR AWM 2576 --- LLXXXXXX
CSA TYPE CMG FT4 ROHS
* = Factory Code

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

- 1) UL AWM/STYLE 2576 80°C / 150 V_{RMS}
CM 75°C
VW-1
- 2) CSA International CMG 60°C
FT4
- 3) EU Directive 2002/95/EC(RoHS):
All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
- 4) California Proposition 65: The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

C. Physical & Mechanical Properties

- 1) Temperature Range -20 to 80°C
- 2) Bend Radius 10X Cable Diameter
- 3) Pull Tension 49 Lbs, Maximum

D. Electrical Properties

- (For Engineering purposes only)
- 1) Voltage Rating 150 V_{RMS}
 - 2) Mutual Capacitance 38 pf/ft @1 kHz, Nominal
 - 3) Ground Capacitance 68 pf/ft @1 kHz, Nominal
 - 4) Characteristic Impedance 59 Ω
 - 5) Inductance 0.18 μH/ft, Nominal
 - 6) Conductor DCR 16.5 Ω/1000ft @20°C, Nominal
 - 7) OA Shield DCR 11.8 Ω/1000ft @20°C, Nominal

E. Other

- 1) Packaging
 - a) 1000 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.
Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 2214C
Page 2 of 1 Pages

Issue: 3
Issue Date: 5/19/2005
Effective Date: 8/1/2005

- b) 500 FT
- c) 100 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.
Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.