

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 5199/60C
Page 1 of 1 Pages

Issue: 10
Issue Date: 1/29/2008
Effective Date: 3/1/2008

A. Construction

Diameters (In)

- | | | |
|----------------|-----------------------------------|-------|
| 1) Component 1 | 60 X 1 COND | |
| a) Conductor | 22 (7/30) AWG TC | |
| b) Insulation | 0.010" Wall, Nom. PVC, Semi Rigid | 0.050 |
| (1) Color Code | Alpha Wire Company Color Code E | |

Cond	Color	Cond	Color	Cond	Color
1	BLACK	21	WHITE/BLACK/RED	41	WHITE/ORANGE/YELLOW
2	BROWN	22	WHITE/BLACK/ORANGE	42	WHITE/ORANGE/GREEN
3	RED	23	WHITE/BLACK/YELLOW	43	WHITE/ORANGE/BLUE
4	ORANGE	24	WHITE/BLACK/GREEN	44	WHITE/ORANGE/VIOLET
5	YELLOW	25	WHITE/BLACK/BLUE	45	WHITE/ORANGE/SLATE
6	GREEN	26	WHITE/BLACK/VIOLET	46	WHITE/YELLOW/GREEN
7	BLUE	27	WHITE/BLACK/SLATE	47	WHITE/YELLOW/BLUE
8	VIOLET	28	WHITE/BROWN/RED	48	WHITE/YELLOW/VIOLET
9	SLATE	29	WHITE/BROWN/ORANGE	49	WHITE/YELLOW/SLATE
10	WHITE	30	WHITE/BROWN/YELLOW	50	WHITE/GREEN/BLUE
11	WHITE/BLACK	31	WHITE/BROWN/GREEN	51	WHITE/GREEN/VIOLET
12	WHITE/BROWN	32	WHITE/BROWN/BLUE	52	WHITE/GREEN/SLATE
13	WHITE/RED	33	WHITE/BROWN/VIOLET	53	WHITE/BLUE/VIOLET
14	WHITE/ORANGE	34	WHITE/BROWN/SLATE	54	WHITE/BLUE/SLATE
15	WHITE/YELLOW	35	WHITE/RED/ORANGE	55	WHITE/VIOLET/SLATE
16	WHITE/GREEN	36	WHITE/RED/YELLOW	56	WHITE/BLACK/BROWN/RED
17	WHITE/BLUE	37	WHITE/RED/GREEN	57	WHITE/BLACK/BROWN/ORANGE
18	WHITE/VIOLET	38	WHITE/RED/BLUE	58	WHITE/BLACK/BROWN/YELLOW
19	WHITE/SLATE	39	WHITE/RED/VIOLET	59	WHITE/BLACK/BROWN/GREEN
20	WHITE/BLACK/BROWN	40	WHITE/RED/SLATE	60	WHITE/BLACK/BROWN/BLUE

- | | | |
|-------------------|--|--------------------|
| 2) Cable Assembly | 60 Components Cabled | |
| a) Twists: | 2.3 Twists/foot (min) | |
| b) Core Wrap | Nonwoven Polyester Tape, 25% Overlap, Min. | |
| 3) Shield: | Alum/Mylar Tape, 25% Overlap, Min. | |
| a) Foil Direction | Foil Facing In | |
| b) Drain Wire | 22 (7/30) AWG TC | |
| 4) Jacket | 0.032" Wall, Nom.,PVC | 0.522 (0.549 Max.) |
| a) Color(s) | Slate, Black, Yellow, Orange, Blue, Green, Red, Sand Beige, White | |
| b) Ripcord | 1 End 810 Denier Nylon | |
| c) Print | ALPHA WIRE-* P/N 5199/60C 60C 22 AWG
XTRAGUARD 1 XTREME PERFORMANCE FOR XTREME
ENVIRONMENTS - SHIELDED 105C (UL) TYPE CM OR AWM
2464 VW-1 --- LLXXXXXX CSA 105C TYPE CMG FT4
CE ROHS <SEQ FOOTAGE>
* = Factory Code | |

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

- | | | |
|-----------------------------------|-----------------|------------------|
| 1) UL | | |
| a) Component 1 | AWM/STYLE 10002 | 105°C / 300 VRMS |
| b) Overall | AWM/STYLE 2464 | 80°C / 300 VRMS |
| | CM | 105°C |
| | VW-1 | |
| 2) CSA International | CMG | 105°C |
| | FT4 | |
| 3) EU Directive 2002/95/EC(RoHS): | | |

All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.

- | | |
|-------------------------------|---|
| 4) California Proposition 65: | The outer surface materials used in the manufacture of this part meet the |
|-------------------------------|---|

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 5199/60C
Page 2 of 1 Pages

Issue: 10
Issue Date: 1/29/2008
Effective Date: 3/1/2008

- requirements of California Proposition 65.
LVD 73/23/EEC Amendment 93/68/EEC
- 5) CE:
- C. Physical & Mechanical Properties**
- 1) Temperature Range -20 to 105°C
 - 2) Bend Radius 10X Cable Diameter
 - 3) Pull Tension 335 Lbs, Maximum
 - 4) Sunlight Resistance Yes
- D. Electrical Properties** (For Engineering purposes only)
- 1) Voltage Rating 300 VRMS
 - 2) Capacitance 36 pf/ft @1 kHz, Nominal Conductor to Conductor
 - 3) Ground Capacitance 65 pf/ft @1 kHz, Nominal
 - 4) Inductance 0.18 μH/ft, Nominal
 - 5) Conductor DCR 16.7 Ω/1000ft @20°C, Nominal
 - 6) OA Shield DCR 9.3 Ω/1000ft @20°C, Nominal
- E. Other**
- 1) Packaging
 - a) 1000 FT
 - b) 500 FT
 - c) 100 FT
 - d) Bulk(Made-to-order)

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.