



# ClimaSys forced vent. IP54, 850m3/h, 230V, with outlet grille and filter G2

Local distributor code: 388829152

NSYCVF850M230PF

EAN Code: 3606480151347

#### **Overview**

Lead time Usually Ships within 4 Weeks

#### Main

Range	ClimaSys	
Product name	ClimaSys CV	
Product or component type	Fan	
Type of filter	Standard	
Flow rate	Free flow rate with standard filter: 838 m3/h at 50 Hz Free flow rate with standard filter: 803 m3/h at 60 Hz	
[Us] rated supply voltage	207244 V	
Input voltage	230 V 50/60 Hz	

# Complementary

Absorbed power	150 W 50 Hz
	195 W 60 Hz
[In] rated current	0.65 A 50 Hz
	0.85 A 60 Hz
Noise level < at	7576 dB
Bearing type	Ball
Height	External: 336 mm
Width	External: 316 mm
Depth	External : 162 mm
cut-out dimensions	291 x 291 mm
Product weight	4.1 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient air temperature for operation	-1560 °C
Ambient air temperature for storage	-4070 °C
Maximum pressure	170 Pa flow rate 0 m³/h
Connections - terminals	Terminal block
IP degree of protection	IP54

Device composition	axial motor     protective grille: on the front and rear surfaces     filter: front of axial motor     outlet grille: front     cut-out template	
Condition of use	Outside temperature must be 5 °C lower than inside temperature Flow rates depends on the work point, see ProClima software Overfrequent filter replacement should be avoided Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23.000 cm
Package 1 Width	32.000 cm
Package 1 Length	34.000 cm
Package 1 Weight	4.386 kg
Unit Type of Package 2	P12
Number of Units in Package 2	24
Package 2 Height	110.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	116.000 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Image of product in real life situation

