



Safety position switch, 1N/O+1N/C, insulated material, +actuator ZB, screw connection

Part no. LS-S11-ZB
106876
EL Number 4356197
(Norway)

General specifications		
Product name		Eaton Moeller® series LS Safety position switch
Part no.		LS-S11-ZB
EAN		4015081066391
Product Length/Depth		95 millimetre
Product height		30 millimetre
Product width		30 millimetre
Product weight		0.08 kilogram
Compliances		CE Marked
Certifications		EN 60947-5 CSA-C22.2 No. 14 IEC 60947-5 CE UL 508 CSA Class No.: 3211-03 UL Category Control No.: NKCR IEC/EN 60947-5 UL IEC/EN 60947 CSA Std. C22.2 No. 14 CSA CSA File No.: 012528 UL File No.: E29184
Product Tradename		LS
Product Type		Safety position switch
Product Sub Type		None
Features & Functions		
Electric connection type		Cable entry metrical
Enclosure material		Plastic Insulated material
Features		Forced opening
Material		Plastic housing
Switch function type		Slow-action switch
General information		
Connection type		Screw terminal
Degree of protection		NEMA Other IP66
Lifespan		1,500,000 mechanical Operations
Operating frequency		1800 Operations/h
Overvoltage category		III
Pollution degree		3
Product category		Safety position switches
Rated impulse withstand voltage (Uimp)		4000 V AC
Repetition accuracy		0.15 mm (Contacts/switching capacity)
Suitable for		Safety functions
Type		Safety position switch Position switch
Ambient conditions, mechanical		
Mounting position		Horizontal As required Vertical
Shock resistance		25 g, Standard-action contact, Mechanical, Half-sinusoidal shock 20 ms
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C

Ambient operating temperature - max		70 °C
Climatic proofing		Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Terminal capacities		
Terminal capacity (flexible with ferrule)		2 x (0.5 - 1.5) mm² 1 x (0.5 - 1.5) mm²
Terminal capacity (solid)		1 x (0.5 - 1.5) mm² 2 x (0.5 - 1.5) mm²
Screw size		PH1, Terminal screw
Tightening torque		0.4 Nm, Screw terminals
Electrical rating		
Rated conditional short-circuit current (Iq)		1 kA
Rated insulation voltage (Ui)		400 V
Rated operational current (Ie) at AC-15, 220 V, 230 V, 240 V		6 A
Rated operational current (Ie) at AC-15, 24 V		10 A
Rated operational current (Ie) at AC-15, 380 V, 400 V, 415 V		4 A
Rated operational current (Ie) at DC-13, 110 V		0.6 A
Rated operational current (Ie) at DC-13, 125 V		0.8 A
Rated operational current (Ie) at DC-13, 220 V, 230 V		0.3 A
Rated operational current (Ie) at DC-13, 24 V		3 A
Short-circuit protection rating		Max. 6 A gG/gL, Fuse, Contacts
Supply frequency		Max. 400 Hz, Contacts
Actuator		
Actuating force at beginning/end of stroke		10 N/5 N (plug-in/pull-out)
Actuator type		Other
Contacts		
Number of contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		1
Number of contacts (normally open contacts)		1
Safety		
Explosion safety category for gas		None
Explosion safety category for dust		None
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		0.17 W
Rated operational current for specified heat dissipation (In)		6 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.

10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Sensors (EG000026) / End switch (EC000030)			
Electric engineering, automation, process control engineering / Sensor technology, safety-related sensor technology / Safety-related mechanical switch (sensor technology) / Safety position switch (Type 1) (ecl@ss13-27-27-26-01 [AKE640018])			
Width sensor		mm	30
Diameter sensor		mm	0
Height of sensor		mm	96
Length of sensor		mm	33.35
Rated operation current Ie at AC-15, 24 V		A	10
Rated operation current Ie at AC-15, 125 V		A	6
Rated operation current Ie at AC-15, 230 V		A	6
Rated operation current Ie at DC-13, 24 V		A	3
Rated operation current Ie at DC-13, 125 V		A	0.8
Rated operation current Ie at DC-13, 230 V		A	0.3
Switching function			Slow-action switch
Switching function latching			No
Output electronic			No
Forced opening			Yes
Number of safety auxiliary contacts			1
Number of contacts as normally closed contact			1
Number of contacts as normally open contact			1
Number of contacts as change-over contact			0
Type of interface			None
Type of interface for safety communication			None
Construction type housing			Cuboid
Housing material			Plastic
Coating housing			Other
Type of control element			Other
Alignment of the control element			Other
Type of electric connection			Cable entry metrical
With status indication			No
Suitable for safety functions			Yes
Explosion safety category for gas			None
Explosion safety category for dust			None
Ambient temperature during operating		°C	-25 - 70
Degree of protection (IP)			IP66
Degree of protection (NEMA)			Other