

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/in/products/2904958>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety relay for emergency stop, safety doors, and light grids up to SIL 3, Cat. 4, PL e, 1 or 2-channel operation, automatic start, 2 enabling current paths (1-channel), $U_S = 24\text{ V DC}$, fixed screw terminal block

Your advantages

- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061
- Low housing width of just 6.8 mm
- 2 channel control
- 2 single-channel enabling current paths
- Automatic activation

Commercial data

Item number	2904958
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNA
Product key	DNA171
Catalog page	Page 219 (C-6-2019)
GTIN	4046356904889
Weight per piece (including packing)	87 g
Weight per piece (excluding packing)	68.188 g
Customs tariff number	85371098
Country of origin	DE

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/in/products/2904958>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Safety relays
Product family	PSRmini
Application	Emergency stop
	Safety door
	Light grid
	Solenoid switch
	Transponder
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

Data management status

Article revision	07
------------------	----

Times

Typical response time	< 175 ms
Typ. starting time with U_s	< 250 ms (when controlled via A1)
Typical release time	< 20 ms (when controlled via A1 or S12 and S22.)
Restart time	1 s (Boot time, after switching on the supply voltage)
Recovery time	< 500 ms

Electrical properties

Maximum power dissipation for nominal condition	3 W ($U_s = 26.4$ V, $I_L^2 = 36$ A ² , $P_{\text{Total max}} = 1.2$ W + 1.8 W)
Nominal operating mode	100% operating factor

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V AC
	250 V AC
Rated surge voltage/insulation	See section "Insulation coordination"

Supply

Designation	A1/A2
Rated control circuit supply voltage U_s	20.4 V DC ... 26.4 V DC
Rated control circuit supply voltage U_s	24 V DC -15 % / +10 %
Rated control supply current I_s	typ. 40 mA
Power consumption at U_s	typ. 0.96 W
Inrush current	4.5 A ($\Delta t < 120$ μ s at U_s)
Filter time	1 ms (at A1 in the event of voltage dips at U_s)
Protective circuit	Surge protection; Suppressor diode

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/in/products/2904958>

Serial protection against polarity reversal

Input data

Digital: Sensor circuit (S12, S22)

Description of the input	safety-related sensor inputs
Input voltage range "0" signal	0 V DC ... 5 V DC (for safe Off; at S12 and S22)
Input voltage range "1" signal	20.4 V DC ... 26.4 V DC
Input current range "0" signal	0 mA ... 2 mA (for safe Off; at S12 and S22)
Inrush current	< 20 mA (typ. with U_S)
Filter time	max. 1.5 ms (Test pulse width of low test pulses) Test pulse rate = 5 x Test pulse width
Concurrency	∞
Max. permissible overall conductor resistance	150 Ω
Protective circuit	Suppressor diode
Voltage at input/start and feedback circuit	24 V DC -15 % / +10 %
Current consumption	< 5 mA (with U_S/I_x to S12) < 5 mA (with U_S/I_x to S22)

Output data

Relay: Enabling current path (13/14, 23/24)

Output description	safety-related N/O contacts (1-channel)
Number of outputs	2 (undelayed)
Contact switching type	2 enabling current paths
Contact material	AgSnO ₂
Switching voltage	min. 12 V AC/DC max. 250 V AC/DC
Switching capacity	min. 60 mW
Inrush current	min. 3 mA max. 6 A
Switching capacity in accordance with IEC 60947-5-1	2 A (AC15) 4 A (DC13)
Limiting continuous current	max. 6 A
Sq. Total current	72 A ² (observe derating)
Switching frequency	max. 0.1 Hz
Mechanical service life	10x 10 ⁶ cycles
Output fuse	6 A gL/gG (N/O contact) 4 A gL/gG (for low-demand applications)

Connection data

Connection technology

pluggable	no
-----------	----

Conductor connection

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/in/products/2904958>

Connection method	Screw connection
Conductor cross section rigid	0.2 mm² ... 2.5 mm²
Conductor cross section flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section AWG	26 ... 12
Stripping length	12 mm
Screw thread	M3
Tightening torque	0.5 Nm ... 0.6 Nm

Signaling

Status display	2 x LED (green)
Operating voltage display	1 x green LED

Dimensions

Width	6.8 mm
Height	93.1 mm
Depth	102.5 mm

Material specifications

Color (Housing)	yellow (RAL 1018)
Housing material	PBT

Characteristics

Safety data	
Stop category	0

Safety data: EN ISO 13849

Category	4
Performance level (PL)	e (4 A DC13; 2 A AC15; 8760 switching cycles/year)

Safety data: IEC 61508 - High demand

Safety Integrity Level (SIL)	3
------------------------------	---

Safety data: IEC 61508 - Low demand

Safety Integrity Level (SIL)	3
------------------------------	---

Safety data: EN IEC 62061

Safety Integrity Level (SIL)	3
------------------------------	---

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-40 °C ... 55 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 2000 m (Above sea level)

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/in/products/2904958>

Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)
Shock	15g
Vibration (operation)	10 Hz ... 150 Hz, 2g

Approvals

CE

Certificate	CE-compliant
-------------	--------------

Standards and regulations

Air clearances and creepage distances between the power circuits

Standards/regulations	EN 60947-1
-----------------------	------------

Mounting

Mounting type	DIN rail mounting
Assembly note	See derating curve
Mounting position	vertical or horizontal


PSR-MS60-2NO-24DC-SC - Safety relays

2904958

<https://www.phoenixcontact.com/in/products/2904958>



Drawings




PSR-MS60-2NO-24DC-SC - Safety relays

2904958

<https://www.phoenixcontact.com/in/products/2904958>

Block diagram



Key:

1 = Voltage limitation

2 = Channel 1


3 = Control circuit channel 1

4 = Start channel 1 and 2

5 = Control circuit channel 2

K1, K2 = Force-guided elementary relays

Block diagram



Block diagram

PSR-MS60-2NO-24DC-SC - Safety relays





2904958


<https://www.phoenixcontact.com/in/products/2904958>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2904958>

**Functional Safety**
Approval ID: 44-205-13755202

**cULus Listed**
Approval ID: E140324

**Functional Safety**
Approval ID: 44-780-13755207

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/in/products/2904958>

Classifications

ECLASS

ECLASS-11.0	27371819
ECLASS-13.0	27371819
ECLASS-12.0	27371819

ETIM

ETIM 9.0	EC001449
----------	----------

UNSPSC

UNSPSC 21.0	39122200
-------------	----------

PSR-MS60-2NO-24DC-SC - Safety relays



2904958
<https://www.phoenixcontact.com/in/products/2904958>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	56d78635-8cd2-4cb8-8997-bfc8194eeaff

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in