

GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

Request Samples



Check Inventory



25.0 x 25.0 x 4.0mm

RoHS Compliant

MSL Level = N/A


Features

- Multiband Active GNSS
 - GPS : L1
 - GLONASS : G1
 - BeiDou : B1
 - Galileo : E1
 - QZSS : L1
 - SBAS : L1
- RHCP Polarization
- Small Size of 25.0 x 25.0 x 4.0 mm
- Light Weight


Applications

- IoT / M2M
- Unmanned Aerial Vehicle (UAV)
- Fleet Management and Asset Tracking
- Transportation
- Precision Agriculture
- Geolocation and Tracking

Product Image



GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

Request Samples



Check Inventory




25.0 x 25.0 x 4.0mm

RoHS Compliant


MSL Level = N/A

GNSS Frequency Bands Covered

GPS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	
GLONASS	G1 1598.06-1609.31MHz	G2 1242.93-1251.68MHz	G3 1202.025MHz	
Galileo	E1 1575.42MHz	E5a 1176.45MHz	E5b 1201.5MHz	E6 1278.75MHz
BeiDou	B1 1561MHz	B2 1207.14MHz	B3 1268.52MHz	
QZSS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	L6 1278.75MHz
IRNSS/NAVIC			L5 1176.45MHz	
SBAS	L1/E1/B1 1575.42MHz		L5/B2a/E5a 1176.45MHz	



GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

Request Samples



Check Inventory



25.0 x 25.0 x 4.0mm

RoHS Compliant

MSL Level = N/A

Electrical Specification

Parameters	Typ.	Units	Note
Antenna			
Frequency	GPS: L1 GLONASS: G1 Beidou: B1 Galileo: E1 QZSS: L1 SBAS: L1/E1/B1	-	
VSWR	< 2.0	-	
Polarization	RHCP	-	(Right Hand Circular Polarization)
Nominal Impedance	50	Ω	
Peak Gain	> 4.0	dBic	L1 (1575.42 MHz)/G1 (1602MHz)
Efficiency	> 75	%	L1 (1575.42 MHz)/G1 (1602MHz)
Axial Ratio	< 5.0		L1 (1575.42 MHz)/G1 (1602MHz)

Note: With 60 × 60 mm Ground Plate

Mechanical Specification

Parameter	Specification
Antenna Dimension	25.0 x 25.0 x 4.0mm
Mounting Type	Through hole

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +110°C
RoHS Compliance	Yes



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 04-23-24

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

Request Samples



Check Inventory




25.0 x 25.0 x 4.0mm
RoHS Compliant
MSL Level = N/A

Ordering Information

Part Number	Description
AANI-PP-0055	GNSS L1 Ceramic Patch Antenna
AANI-PP-0055-EVB	GNSS L1 Ceramic Patch Antenna EVB

GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

Request Samples



Check Inventory






25.0 x 25.0 x 4.0mm

RoHS Compliant

MSL Level = N/A

Product Dimensions




Unit: inches [mm]



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 04-23-24

ABRACON IS
ISO9001-2015
CERTIFIED



AANI-PP-0055

Request Samples



Check Inventory




25.0 x 25.0 x 4.0mm

RoHS Compliant


MSL Level = N/A

PCB Footprint

TOP VIEW




BOTTOM VIEW



Tolerance : ± 0.20

Unit : mm

GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

[Request Samples](#)



[Check Inventory](#)





25.0 x 25.0 x 4.0mm

RoHS Compliant

MSL Level = N/A

Measurement Setup





AANI-PP-0055

Request Samples



Check Inventory






25.0 x 25.0 x 4.0mm

RoHS Compliant

MSL Level = N/A

Reflection Characteristics – Return Loss & VSWR





AANI-PP-0055

Request Samples



Check Inventory





25.0 x 25.0 x 4.0mm

RoHS Compliant

MSL Level = N/A

Radiation Characteristics – Peak Gain





AANI-PP-0055

Request Samples



Check Inventory




25.0 x 25.0 x 4.0mm


RoHS Compliant

MSL Level = N/A

Radiation Characteristics – Total Efficiency (%)



GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

Request Samples



Check Inventory







25.0 x 25.0 x 4.0mm

RoHS Compliant

MSL Level = N/A

Radiation Characteristics – 3D & 2D Pattern

1575MHz




5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 04-23-24

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

Request Samples



Check Inventory






25.0 x 25.0 x 4.0mm


RoHS Compliant

MSL Level = N/A


1602MHz




XY plane




XZ plane



YZ plane



GNSS L1 Ceramic Patch Antenna



AANI-PP-0055

Request Samples



Check Inventory



25.0 x 25.0 x 4.0mm

RoHS Compliant

MSL Level = N/A

Packaging

1. 50 pcs per tray
2. 300 pcs per inner box
3. 1200 pcs per carton

Dimension of the carton: 390 x 388 x 206 mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 04-23-24

ABRACON IS
ISO9001-2015
CERTIFIED