

DIGITAL MULTIMETERS

3000 SERIES



3292B-BT &
3293B-BT only

MODELS MTX 3292B & 3292B-BT, 3293B & 3293B-BT

Portable multimeter measuring resistance, capacitance, temperature, duty cycle, pulse counts and frequency



(Android App available on Google Play for Models 3292B-BT & 3293B-BT)



SCAN TO
LEARN
MORE

FEATURES

- Easy-to-read 320 x 240 pixel color matrix graphical screen with black background
- Trace, cursors and zoom on recordings
- Programmable storage rate
- Stores up to 30,000 measurements (MTX 3293B)
- On screen connection indicator
- USB or Bluetooth® Class II communication available as an option
- NiMH AA rechargeable battery
- No downtime: instrument operates while charging

PRODUCT INCLUDES

MTX 3292B & MTX 3292B-BT, MTX 3293B & MTX 3293B-BT

Soft carrying case, set of (2) color-coded (red/black) safety leads, set of (2) color-coded (red/black) test probes, printed quick start guide, (4) NiMH 2400 mA·h 1.5 V rechargeable batteries (installed), optical USB cable, USB Type A charger, USB charging cable and USB drive with SX-DMM software.



CAT. #

DESCRIPTION

2154.03	DMM Model MTX 3292B (ASYC IV, TRMS, 100,000-cts, USB, Color Graphical Display)
2154.04	DMM Model MTX 3293B (ASYC IV, TRMS, 100,000-cts, USB, Color Graphical Display)
2154.05	DMM Model MTX 3292B-BT (ASYC IV, TRMS, 100,000-cts, Bluetooth®, USB, Color Graphical Display)
2154.06	DMM Model MTX 3293B-BT (ASYC IV, TRMS, 100,000-cts, Bluetooth®, USB, Color Graphical Display)

MODELS	MTX 3292B, 3292B-BT		MTX 3293B, 3293B-BT
ELECTRICAL			
DC, AC & AC+DC Voltages	1000 V		
Voltage DC Accuracy	± 0.03 %	± 0.02 %	
AC & AC+DC Bandwidth	100 kHz	200 kHz	
DC, AC & AC+DC Current	10 A / (10 to 20) A (30 s max)		
Current DC Accuracy	± 0.01 %		
Frequency	5 MHz		
Resistance	1 Ω to 100 MΩ		
Audible Continuity	< 20 Ω		
Diode Test	Diode 0 to 2.6 V < 1 mA + Zener Diode or LED 0 to 20 V < 11 mA		
Capacitance	10 mF		
Temperature Pt 100 / 1000	(-328 to 1472) °F (-200 to 800) °C		
Temperature K / J TC	(-40 to 2192) °F (-40 to 1200) °C		
OTHER FUNCTIONS			
MIN / MAX / PEAK	SURV time / date-stamped MAX / MIN / AVG or PEAK ± on all functions		
Relative Mode (ΔRel)	Relative value REF-delta unit or on 3 displays + main measurement		
PWM Filter	4 th order 300 Hz low-pass filter for measuring variable speed drives with asynchronous motors		
V / A-Output Clamp Function for Direct Reading	Programmable ratio		
Secondary Measurements	3 measurements + main measurement		
SPEC Mode	Display of measurement tolerance: Smin, Smax		
GRAPH	Trends of main measurements < 60 s + Zoom + Cursor		
Center Zero	Automatic trend bargraph		
Memory	10,000 measurements	30,000 measurements	
GENERAL			
Display	Color graphical display (70 x 52) with backlighting on four-line 100,000-count display		
Communication	USB optical connector or Bluetooth® Class II (optional) & SX-DMM software (included)		
Power Supply	Charger or (4) AA batteries or NiMH batteries (included)		
Environment	Storage: (-4 to 158) °F (-20 to 70) °C Operation: (32 to 104) °F (0 to 40) °C		
Dimensions	(7.72 x 3.54 x 1.85) in (196 x 90 x 47.1) mm		
Weight	20 oz (570 g)		

Consult factory for NIST Calibration prices.



Vol. 24 Rev.00 06/2024

Technical Assistance (800) 343-1391
© 2024 Chauvin Arnoux®, Inc. d.b.a. AEMC® Instruments. All Rights Reserved.

www.aemc.com

59

DIGITAL MULTIMETERS

3000 SERIES

FUNCTIONAL DISPLAYS

The TRMS measurements of AC voltages and currents are also accurate on non-linear signals

MTX 3292B & MTX 3293B COLOR MATRIX GRAPHICAL SCREENS




SETUP MENU

Configuration of measurements




MEASUREMENT

Configuration of the measurement parameters



MEM

Storing of the measurements recording mode



HOLD

Management and hold of the display



MTX 3290 & MTX 3291 BACKLIT LCD SCREENS




MAX/MIN AVG

Displays maximum, minimum and average values



PEAK MODE

Displays Peak + value



AREL MODE

Displays relative values with respect to referenced measured value