

**ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION**

Part Number: 6369
Page 1 of 1 Pages

Issue: 3
Issue Date: 5/23/2005
Effective Date: 8/1/2005

A. Construction

Diameters (In)

- 1) Component 1 12 X 1 PAIR
 - a) Conductor 24 (7/32) AWG TC
 - b) Insulation 0.010" Wall, Nom. PVC, Semi Rigid 0.044
 - (1) Color Code Alpha Wire Company Color Code M

| Pair | Color | Pair | Color | Pair | Color |
|------|-----------------------------|------|---------------------------|------|-----------------------------|
| 1 | BLUE/WHITE - WHITE/BLUE | 5 | SLATE/WHITE - WHITE/SLATE | 9 | BROWN/RED - RED/BROWN |
| 2 | ORANGE/WHITE - WHITE/ORANGE | 6 | BLUE/RED - RED/BLUE | 10 | SLATE/RED - RED/SLATE |
| 3 | GREEN/WHITE - WHITE/GREEN | 7 | ORANGE/RED - RED/ORANGE | 11 | BLUE/BLACK - BLACK/BLUE |
| 4 | BROWN/WHITE - WHITE/BROWN | 8 | GREEN/RED - RED/GREEN | 12 | ORANGE/BLACK - BLACK/ORANGE |

- c) Pair 2/Cond Cabled Together
- (1) Twists: 9.6 Twists/foot (min)
- 2) Component 2 1 X 1 COND
 - a) Conductor 24 (7/32) AWG TC
 - b) Insulation 0.010" Wall, Nom. PVC, Semi Rigid 0.044
 - (1) Color(s)

| Cond | Color | Cond | Color | Cond | Color |
|------|-------------|------|-------|------|-------|
| 1 | GREEN/BLACK | | | | |

- 3) Cable Assembly 13 Components Cabled
- a) Twists: 2.7 Twists/foot (min)
- 4) Shield: Alum/Mylar Tape, 25% Overlap, Min.
- a) Foil Direction Foil Facing Out
- b) Drain Wire 24 (7/32) AWG TC
- c) Braid TC, 65% Coverage, Min.
- 5) Jacket 0.032" Wall, Nom., PVC 0.389 (0.410 Max.)
- a) Color(s) SLATE
- b) Print ALPHA WIRE-* P/N 6369 12PR/1C 24 AWG

SHIELDED 75C (UL) TYPE CM OR AWM 2464 --- LLXXXXXX
CSA TYPE CMG FT4 ROHS

* = Factory Code

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

- 1) UL AWM/STYLE 2464 80°C / 300 VRMS
CM 75°C
VW-1
- 2) CSA International CMG 60°C
FT4
- 3) EU Directive 2002/95/EC(RoHS):

All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.

- 4) California Proposition 65: The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

C. Physical & Mechanical Properties

- 1) Temperature Range -20 to 80°C
- 2) Bend Radius 10X Cable Diameter
- 3) Pull Tension 97 Lbs, Maximum

D. Electrical Properties

- 1) Voltage Rating (For Engineering purposes only) 300 VRMS

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

**ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION**

Part Number: 6369
Page 2 of 1 Pages

Issue: 3
Issue Date: 5/23/2005
Effective Date: 8/1/2005

- 2) Component 1
 - a) Characteristic Impedance 75 Ω
 - b) Mutual Capacitance 30 pf/ft @1 kHz, Nominal
 - c) Ground Capacitance 50 pf/ft @1 kHz, Nominal
 - d) Conductor DCR 26 Ω /1000ft @20°C, Nominal
 - e) OA Shield DCR 3.4 Ω /1000ft @20°C, Nominal
- 3) Component 2
 - a) Ground Capacitance 90 pf/ft @1 kHz, Nominal
 - b) Conductor DCR 26 Ω /1000ft @20°C, Nominal

E. Other

- 1) Packaging
 - a) 1000 FT
 - b) 500 FT
 - c) 100 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.