

## Molded Precision Current Sense Shunt Resistor

with TCR down to ±25ppm/°C, Tightest Tolerance of ±0.5%, Excellent long-term stability, AEC-Q200 Qualified

## FEATURES

- Resistance values: 10 m $\Omega$  to 100 m $\Omega$
- Tolerance: to ±0.5%
- Temperature coefficient of resistance (TCR): to ±25 ppm/°C (-55°C to + 125°C, +20°C)
- Load life stability: ±0.2% typical, at +70°C, 2000 h (rated power)
- Thermal EMF: <3uV/°C
- Nickel Chrome Resistive Element
- AEC-Q200 qualified



## **KEY APPLICATIONS**

- Automatic Test Equipment (ATE)
- Test & Measurement systems
- Industrial
- Weighing system
- Switching and linear power supplies
- Precision current-sensing
- Battery Management Systems
- Power amplifiers
- Medical
- Automotive

FIGURE 1 – POWER DERATING CURVE										
	120									
Rated Power %	100	×	65°C				$\prec$	- 70°C (P70°	C Rate	ed temp.)
	80			_						
	60							$\mathbf{\lambda}$	170	)°C
	40									
	20						1			
	0									
	-	75 - 5	0 - 25	0	25	50	75	100	125	150 175
Ambient Temperature °C										

TABLE 1 – SPECIFICATIONS					
PARAMETER	CSM2512RS				
Resistance Range	10 mΩ to 100 mΩ				
Power Rating at 70°C	1 W				
Tolerance	±0.5%, ±1%, ±2%				
Temperature Coefficient Max. (-55°C to +125°C, +20°C Ref.)	± 25ppm/°C				
Operating Temperature Range	-65°C to +170°C				
Packaging	Tape & Reel 4000pcs/reel				

For any questions, contact foil@vpgsensors.com



## FIGURE 2 - DIMENSIONS in mm Recommended Land Pattern L W н D В С Α 6.40±0.2 3.2±0.2 0.8±0.1 0.8±0.2 3.6±0.1 3.6±0.1 2.0±0.1

TABLE 2 - PERFOR	RMANCE SPECIFICATIONS			
Test Item	Test Method	Standard	Typical	Maximum
Short-time overload	5x rated power for 5s, measured $24\pm 2h$ after test	MIL-STD-202 Method 201	±0.1%	±0.3%
High temp. storage	+170°C, 1000h, no load, measured $24\pm 2h$ after test	MIL-STD-202 Method 108	±0.2%	±0.5%
Moisture resistance	T=24h/cycle, no load, 7a and 7b not required, measured 24±2h after test	MIL-STD-202 Method 106	±0.02%	±0.05%
Load life	+70°C, 2000h, rated power, measured 24±2h after test	MIL-STD-202 Method 108	±0.2%	±0.5%
Resistance to soldering heat	+260°C±5°C, 10s±1s, measured 24±2h after test	MIL-STD-202 Method 210	±0.05%	±0.3%
Thermal shock	– 55°C~+ 125°C, 1000 cycles measured 24±2h after test	JESD22 Method JA-104	±0.1%	±0.5%
High temp. & high humidity	+85°C, 85%RH, 10% of rated power, 1000h, measured 24 $\pm$ 2h after test	MIL-STD-202 Method 103	±0.05%	±0.3%
Solderability	+235°C±5°C, 2s±0.5s	J-STD-202	95% covered	



For any questions, contact foil@vpgsensors.com

The document and the products described herein are subject to change from time to time without notice and are also subject to specific disclaimers. Please visit https://vpgsensors.com/disclaimer for more information.