

**KERN MH-CH**  
Hanging balance

**2**  
Years  
Warranty

**24**  
Hours  
Delivery

STANDARD



**Three in one: Balance,  
Thermometer, Clock**

KERN MH

Hand strap

**Data hold function**  
The display is "frozen" automatically for approx. 7 sec, as soon as the weighing value remains unchanged

**Hook**  
stainless steel, can be hinged



**Ready for use**  
Batteries size AA (2 x 1.5 V) inclusive.  
AUTO-OFF function after 5 min to preserve the battery. Operation time approx. 250 h

Model	Read-out d	Weighing-range Max
KERN	g	kg
MH 5K5	5	5
MH 10K10	10	10

Casing WxDxH 70x25x100 mm (with hook 140 mm). Net weight approx. 150 g.  
LCD display with digit height 12 mm.  
**52** Temperature display -10 ... +40°C, division 1°C.

Catalogue 2003

**Practical and  
always at hand**

STANDARD



KERN CH

**Data hold function**  
The display can be "frozen" via the MODE key for approx. 5 sec

**Tape measure**  
extractable (length 100 cm)

**Hook**  
stainless steel



**Ready for use**  
Block-battery (9 V) inclusive.  
AUTO-OFF function after 3 min to preserve the battery

Model	Read-out d	Weighing-range Max
KERN	g	kg
CH 15K20	20	15
CH 50K50	50	50
CH 50K100	100	50

Casing WxDxH 90x30x175 mm (with hook 270 mm). Net weight approx. 250 g.  
LCD display with digit height 11 mm.

INDUSTRIAL BALANCES