

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 86125CY
Page 2 of 2 Pages

Issue: 9
Issue Date: 7/7/2009
Effective Date: 7/21/2009

- E. Electrical Properties** (For Engineering purposes only)
- 1) Voltage Rating 300 V_{RMS}
 - 2) Capacitance 28 pf/ft @1 kHz, Nominal Conductor to Conductor
 - 3) Ground Capacitance 50 pf/ft @1 kHz, Nominal
 - 4) Inductance 0.2 μH/ft, Nominal
 - 5) Conductor DCR 42 Ω/1000ft @20°C, Nominal
 - 6) OA Shield DCR 2.8 Ω/1000ft @20°C, Nominal
- F. Other**
- 1) Packaging
 - a) 1000 FT
 - b) 500 FT
 - c) 100 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.