

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 86606CY
Page 1 of 2 Pages

Issue: 10
Issue Date: 7/7/2009
Effective Date: 7/21/2009

A. Construction

Diameters (In)

- 1) Component 1 6 X 1 PAIR
 - a) Conductor 24 (10/34) AWG TC
 - b) Insulation 0.010" Wall, Nom. PVC, Semi Rigid 0.044
 - (1) Color Code Alpha Wire Company Color Code A

Pair	Color	Pair	Color	Pair	Color
1	BLACK-RED	3	BLACK-GREEN	5	BLACK-BROWN
2	BLACK-WHITE	4	BLACK-BLUE	6	BLACK-YELLOW

- c) Pair 2/Cond Cabled Together
 - (1) Twists: 9.6 Twists/foot (min)
- 2) Cable Assembly 6 Components Cabled
 - a) Twists: 4.8 Twists/foot (min)
 - b) Core Wrap Nonwoven Polyester Tape, 25% Overlap, Min.
- 3) Shield: Flex Alum/Mylar Tape, 25% Overlap, Min.
 - a) Foil Direction Foil Facing Out
 - b) Drain Wire 26 (7/34) AWG TC
 - c) Braid TC, 85% Coverage, Min.
- 4) Jacket 0.040" Wall, Nom., PVC 0.337+/- 0.017
 - a) Color(s) SLATE
 - b) Jacket Separator Tissue Tape, 25% Overlap, Min.
 - c) Print ALPHA WIRE-* P/N 86606CY 6PR 24 AWG
XTRAGUARD CONTINUOUS FLEX DATA CABLE
(UL) 105C TYPE CM --- C(UL) CMG OR AWM 2661
105C 300V --- LLXXXXXX CSA AWM I/II A/B FT4 105C
300V CE ROHS <SEQ FOOTAGE>
* = Factory Code

[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]

B. Industry Approvals

- 1) UL
 - a) Component 1 AWM/STYLE 10002 105°C / 300 V_{RMS}
 - b) Overall AWM/STYLE 2661 105°C / 300 V_{RMS}
CM 105°C
- 2) CSA International AWM I/II A/B 105°C / 300 V_{RMS}
C(UL) TYPE CMG 105°C
FT4
- 3) CE: LVD 73/23/EEC Amendment 93/68/EEC

C. Environmental Approvals

- 1) EU Directive 2002/95/EC(RoHS): All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
- 2) California Proposition 65: The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

D. Physical & Mechanical Properties

- 1) Temperature Range -10 to 105°C(static), +5 to 105°C (dynamic)
- 2) Bend Radius 10X Cable Diameter(static), 15X Cable Diameter(dynamic)
- 3) Pull Tension 46 Lbs, Maximum
- 4) Sunlight Resistance Yes

E. Electrical Properties

- (For Engineering purposes only)
- 1) Voltage Rating 300 V_{RMS}
- 2) Mutual Capacitance 23.1 pf/ft @1 kHz, Nominal
- 3) Ground Capacitance 42 pf/ft @1 kHz, Nominal

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability. Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE COMPANY
CUSTOMER PRODUCT SPECIFICATION

Part Number: 86606CY
Page 2 of 2 Pages

Issue: 10
Issue Date: 7/7/2009
Effective Date: 7/21/2009

- 4) Characteristic Impedance 82 Ω
- 5) Inductance 0.19 μ H/ft, Nominal
- 6) Conductor DCR 29 Ω /1000ft @20°C, Nominal
- 7) OA Shield DCR 2.9 Ω /1000ft @20°C, Nominal

F. Other

- 1) Packaging
 - a) 1000 FT
 - b) 500 FT
 - c) 100 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.