



RoHS Compliant

Product Features

- Low hold current, Solid state, Radial leaded product ideal for up to 277VAC

Operating (Hold Current) Range

50mA - 2A

Temperature Range

-20°C to 85°C

Maximum Operating Voltage

277V AC

Maximum Interrupt Voltage

305V AC

Agency Approval

TUV (Std. EN/IEC 62319-1-1 and EN/IEC 62319-1, Cert. R50102173) UL Recognized Component (Std. UL1434, File E305051)

> LEAD FREE = HALOGEN FREE = HF



Flectrical Characteristics (23°C)

UK CE & SUL

	5	Current Curre	Trip		Max. Int. Voltage	Max Current	Typical Power	Max Time to Trip		Resistance Tolerance		Agency Approvals	
	Part Number (Bulk)		Current					Current	Time	Rmin	R1max	-10	Δ
			IT, A	Vmax, Vac	VI-max, Vac	Imax, A	Pd, W	Α	Sec	Ohms	Ohms	c PU °us	ΤÜV
Α	0ZRV0005FF1E	0.05	0.20	277	305	1.0	0.70	0.25	18.00	8.00	26.00	Υ	Υ
В	0ZRV0008FF1E	0.08	0.26	277	305	1.2	0.80	0.40	18.00	4.50	18.00		Υ
С	0ZRV0012FF1E	0.12	0.30	277	305	1.2	1.00	0.60	18.00	3.00	12.00		Υ
D	0ZRV0016FF1E	0.16	0.37	277	305	1.6	1.40	0.80	18.00	2.30	8.00		Υ
Е	0ZRV0025FF1B	0.25	0.56	277	305	2.5	1.50	1.25	18.50	1.30	4.30	Υ	Υ
F	0ZRV0033FF1A	0.33	0.74	277	305	3.3	1.70	1.65	21.00	0.94	3.10	Υ	Υ
G	0ZRV0040FF1A	0.40	0.90	277	305	4.0	2.00	2.00	24.00	0.81	2.70	Υ	Υ
Н	0ZRV0055FF1A	0.55	1.25	277	305	5.5	2.40	2.75	26.00	0.63	2.10	Υ	Υ
ı	0ZRV0075FF1A	0.75	1.50	277	305	7.5	2.60	3.75	18.00	0.43	1.40	Υ	Υ
J	0ZRV0100FF1A	1.00	2.00	277	305	10.0	2.90	5.00	21.00	0.32	1.10	Υ	Υ
K	0ZRV0125FF1A	1.25	2.50	277	305	12.5	3.30	6.25	23.00	0.24	0.80	Υ	Υ
L	0ZRV0150FF1A	1.50	3.00	277	305	15.0	3.70	7.50	23.00	0.14	0.48	Υ	Υ
М	0ZRV0200FF1A	2.00	4.00	277	305	20.0	4.50	10.00	28.00	0.09	0.29	Υ	Υ

ΙH Hold Current- The maximum current at which the device will not trip in still air at 23°C.

ΙT Trip current- The minimum current at which the device will trip in still air at 23°C. Vmax Maximum voltage device can withstand at its rated current without suffering damage.

Maximum fault current device can withstand at rated voltage (Vmax) without damage.

Typical power dissipated by device when in tripped state in 23°C still air environment.

Rmin Minimum device resistance at 23°C in initial un-soldered state.

R1max Maximum device resistance at 23°C, 1 hour after initial device trip, or after being soldered to PCB in end application



Specifications subject to change without notice

Type 0ZRV Series

PTC's – Basic Theory of Operation / "Tripped" Resistance Explanation

A Bel PTC consists of a block of polymeric material containing conductive carbon granules which is sandwiched between two conductive metal plates. When this polymer block reaches approximately 125C, either due to current passing through it via conductive chains of carbon particles or due to an external heat source; it swells volumetrically. This expansion breaks apart a majority of the chains of carbon granules that run randomly between the two conductive plates. This behavior results in a sharp increase in resistance across the two plates which all but eliminates current flow through the device, allowing just enough residual current flow to maintain the block's internal temperature at 125C. Once this "tripped" state current is cut off, the polymer brick cools and shrinks to its original size, thereby allowing its broken carbon chains to reestablish themselves and permit the part to return to its low resistance state. Once cooled to room ambient, the PTC will once again exhibit a resistance less than its "R1max" rating.

At currents below the device IHOLD rating, AND at temperatures below 100C, the PTC maintains a resistance value below its R1 MAX rating.

The catalog data for each device specifies a "Typical Power" value. This is the power required to exactly match the heat lost by the tripped device to its ambient surroundings at 23C. By Ohm's Law, power can be stated as: $W = E^2/R$. Thus the approximate resistance of a "Tripped" PTC can be determined by: $R = E^2/W$, where "E" is the voltage appearing across the PTC (usually the supply's open circuit voltage), and "W" is the Typical Power value for the particular PTC.

Since the PPTC acts to maintain a constant internal temperature, its apparent resistance will change based upon applied voltage and, to a lesser degree, ambient conditions. Consider the following example....


A PTC with a Typical Power of 1 watt protecting a circuit using a 60V supply will demonstrate an apparent, tripped resistance "R" of:

 $R = 60^2/1 = 3,600 \text{ ohms}$

This same tripped device when used to protect a 12V circuit would now present an apparent resistance of: $R = 12^2/1 = 144$ ohms

The value for Typical Power is "typical" because any physical factors that affect heat loss (such as ambient temperature or air convection) will somewhat alter the level of power that the PTC needs to maintain its internal temperature. In short, PTCs do not exhibit a constant, quantifiable tripped resistance value.

Average Time Current Characteristic Curve at 23°C



The Average Time Current Characteristic Curve and Temperature Rerating Curve are affected by a number of variables and these curves are provided for guidance only.



Specifications subject to change without notice

Bel Fuse Inc. 300 Executive Drive, Suite 300, West Orange, NJ 07052 USA

Rev. 0ZRV May2024

Type 0ZRV Series

Physical Specifications

Lead material:

Tin plated copper, size / diameter as shown in Drawings and Table under Product Dimensions.

Soldering characteristics

MIL-STD-202, Method 208H.


Insulating coating

Flame retardant epoxy, meets UL-94-V-0 requirements.

PTC Marking

"bel" or "b", , IH code and "RV .

Product Dimensions




All dimensions in mm. С D Part Number Fig. Typical Max Max Min Max Typical 0ZRV0005FF 7.40 12.70 5.10 7.60 3.80 1.60 0ZRV0008FF 2 7.40 12.20 5.10 7.60 3.80 1.60 0ZRV0012FF 8.10 12.80 5.10 7.60 3.80 1.60 2 0ZRV0016FF 7.60 7.40 14.20 5.10 3.80 1.60 2 0ZRV0025FF 3 8.90 15.20 5.10 7.60 3.80 1.80 0ZRV0033FF 12.60 15.50 5.10 7.60 3.80 1.80 3 0ZRV0040FF 3 12.60 15.50 5.10 7.60 3.80 1.80 0ZRV0055FF 7.60 12.60 16.50 5.10 4.10 1.90 4 0ZRV0075FF 15.80 20.00 5.10 7.60 4.80 1.90 4 0ZRV0100FF 16.30 21.70 10.20 7.60 5.10 1.90 4 7.60 5.30 0ZRV0125FF 5 18.80 24.50 10.20 1.90 0ZRV0150FF 5 23.80 28.30 10.20 7.60 5.30 1.90 0ZRV0200FF 25.20 30.60 10.20 7.60 6.10 1.90

Temperature Derating Table

	Temperature Derating								
I Hold Value	-20	0	23	30	40	50	60	70	85
0ZRV	146%	124%	100%	92%	79%	67%	55%	43%	25%

Thermal Derating Curve



Cautionary Notes

- Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.
- These Polymer PTC (PPTC) devices are intended for protection against occasional overcurrent/overtemperature fault conditions and may not be suitable for use in applications where repeated and/or prolonged fault conditions are anticipated.
- 3. Avoid contact of PTC device with chemical solvent. Prolonged contact may adversely impact the PTC performance.
- If potting is mandated, avoid rigid potting compounds as they will encase the PTC and prevent it from volumetrically expanding to properly respond to a trip event.



Specifications subject to change without notice

Rev. 0ZRV May2024


Type 0ZRV Series

Environmental Specifications

Temperature cycling	JESD22 Method JA-104
Biased humidity	MIL-STD-202 Method 103
Operational life	MIL-STD-202 Method 108
Terminal strength	AEC-Q200-004
Resistance to solvents	MIL-STD-202 Method 215
Mechanical shock	MIL-STD-202 Method 213
Vibration	MIL-STD-202 Method 204
Resistance to soldering heat	MIL-STD-202 Method 210
Thermal shock	MIL-STD-202 Method 107
Solderability	ANSI/J-STD-002

Soldering Parameters


- Columnia Latamotoro					
Lead-free Wave Soldering Profile					
Wave Solder Parameter					
Average ramp-up rate	200°C / second				
Heating rate during preheat	typical 1 - 2°C / second Max 4°C / second				
Final preheat temperature	within 125°C of soldering temperature				
Peak temperature Tp	260°C				
Time within +0°C / -5°C of actual peak temperature	10 seconds				
Ramp-down rate	5°C / second max.				



Standard Packaging

Part Number	Bulk				
Part Number	Pcs/Box	P/N Code			
0ZRV0005FF					
-	3000	1E			
0ZRV0016FF					
0ZRV0025FF	1500	1B			
0ZRV0033FF					
-	1000	1A			
0ZRV0200FF					

P/N Explanation and Ordering Information





Specifications subject to change without notice

Bel Fuse Inc. 300 Executive Drive, Suite 300, West Orange, NJ 07052 USA

Rev. 0ZRV May2024