

Vishay Dale



# Power Metal Strip<sup>®</sup> Resistors, Low Value (down to 0.001 $\Omega$ ), Surface Mount, 4-Terminal



### **FEATURES**





- Ideal for all types of precision current sensing, voltage division and pulse applications including switching and linear power supplies, instruments, power amplifiers
- Proprietary processing technique produces extremely low resistance values (down to 0.001 Ω)
- RoHS\*
  COMPLIANT
  GREEN
  (5-2008)\*\*


- All welded construction
- · Solderable terminations
- Solid metal Nickel-Chrome or Manganese-Copper alloy resistive element with low TCR (< 20 ppm/°C)</li>
- Very low inductance 0.5 nH to 5 nH
- Excellent frequency response to 50 MHz
- Compliant to RoHS directive 2002/95/EC

STANDARD ELECTRICAL SPECIFICATIONS					
GLOBAL MODEL	POWER RATING P <sub>70°C</sub> W	RESISTANCE RANGE $\Omega$			
WODEL		± 0.5 %	± 1.0 %		
WSK2512	1.0	0.003 to 0.025	0.001 to 0.025		

#### Note

· Part Marking: DALE, Value, Tolerance; due to resistor size limitations some resistance values will be marked with only the resistance value

TECHNICAL SPECIFICATIONS					
PARAMETER	UNIT	WSK2512			
Temperature Coefficient	ppm/°C	0.001 $\Omega$ to 0.0029 $\Omega$ = ± 250 0.003 $\Omega$ to 0.0049 $\Omega$ = ± 75 0.005 $\Omega$ to 0.025 $\Omega$ = ± 35			
Operating Temperature Range	°C	- 65 to + 170			
Maximum Working Voltage V (P x R) <sup>1/2</sup>		$(P \times R)^{1/2}$			
Weight/1000 pieces	g	63.6			



<sup>\*</sup> Pb containing terminations are not RoHS compliant, exemptions may apply


<sup>\*\*</sup> Please see document "Vishay Material Category Policy": <a href="www.vishay.com/doc?99902">www.vishay.com/doc?99902</a>



## Power Metal Strip® Resistors, Low Value (down to 0.001 $\Omega$ ), Surface Mount, 4-Terminal


Vishay Dale

### **DIMENSIONS**



	DIMENSIONS in inches [millimeters]						
MODEL	$ \begin{array}{c} \textbf{RESISTANCE} \\ \textbf{RANGE} \ \Omega \end{array} $	L	w	н	Т	Α	В
WSK2512 -	0.001 to 0.0049	$0.250 \pm 0.010$ [6.35 ± 0.254]	$0.125 \pm 0.010$ [3.18 $\pm$ 0.254]	$0.025 \pm 0.010$ [0.635 ± 0.254]	0.087 ± 0.010 [2.21 ± 0.254]	$0.030 \pm 0.010$ [0.762 ± 0.254]	$0.020 \pm 0.010$ [0.508 ± 0.254]
	0.005 to 0.025	$0.250 \pm 0.010$ [6.35 ± 0.254]	$0.125 \pm 0.010$ [3.18 ± 0.254]	$0.025 \pm 0.010$ [0.635 ± 0.254]	$0.047 \pm 0.010$ [1.19 $\pm$ 0.254]	$0.030 \pm 0.010$ [0.762 ± 0.254]	$0.020 \pm 0.010$ [0.508 ± 0.254]

MODEL	SOLDER PAD DIMENSIONS in inches [millimeters]					
MODEL	а	b	С	d	е	I
WSK2512	0.125 [3.18]	0.130 [3.30]	0.030 [0.76]	0.020 [0.51]	0.055 [1.40]	0.065 [1.65]



PERFORMANCE						
TEST	CONDITIONS OF TEST	TEST LIMITS				
Thermal Shock	- 55 °C to + 150 °C, 1000 cycles, 15 min at each extreme	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$				
Short Time Overload	5 x power for 5 s	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$				
Low Temperature Storage	- 65 °C for 24 h	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$				
High Temperature Exposure	1000 h at + 170 °C	$\pm (1.0 \% + 0.0005 \Omega) \Delta R$				
Bias Humidity	+ 85 °C, 85 % RH, 10 % Bias, 1000 h	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$				
Mechanical Shock	100 g's for 6 ms, 5 pulses	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$				
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$				
Load Life	1000 h at rated power, + 70 °C, 1.5 h "ON", 0.5 h "OFF"	$\pm (1.0 \% + 0.0005 \Omega) \Delta R$				
Resistance to Solder Heat	+ 260 °C Solder, 10 s to 12 s dwell, 25 mm/s emergence	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$				
Moisture Resistance	MIL-STD-202 Method 106, 0 % power, 7a and 7b not required	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$				

PACKAGING						
MODEL	REEL					
	TAPE WIDTH	DIAMETER	RIECES/REEL	CODE		
WSK2512	12 mm/Embossed Plastic	178 mm/7"	2000	R86		

### Note

<sup>•</sup> Embossed carrier tape per EIA-481-1A



Vishay

### **Disclaimer**

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com