



 Revision Date:
 07/07/2006

 Issue date:
 11/07/2006

Version:

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product type: Liquid flux

Product name: X33S-07i Item No. : MB2049

Region: Europe
Company Name & Address
Henkel Loctite Adhesives Ltd.
Multicore Solders
Technologies House, Wood Lane End
Hemel Hempstead, Herts HP2 4RQ, UK

Tel: +44 (0) 1442 278000 Fax: +44 (0) 1442 278071

Emergency Tel: +44 (0) 1442 278000

2. COMPOSITION/INFORMATION ON INGREDIENTS

Hazardous components CAS No.	EINECS-No.	%	Classification
Propan-2-ol 67-63-0	200-661-7	80 - 100	F;R11 R67 Xi;R36
Adipic acid 124-04-9	204-673-3	1 - 5	Xi;R36

Additional Information:

For the explanation of the listed risk phrases refer to Section 16.

3. HAZARDS IDENTIFICATION

Highly flammable. Irritating to eyes. Vapours may cause drowsiness and dizziness.

4. FIRST AID MEASURES

Inhalation: Move to fresh air. If symptoms persist, seek medical advice.

Eye contact: Flush eyes with plenty of water for at least 15 minutes. If irritation persists seek medical attention.

Ingestion: Do not induce vomiting. Seek medical attention immediately.

Skin contact: Rinse off with plenty of water. If irritation persists, seek medical advice.

5. FIRE-FIGHTING MEASURES

Item No.: MB2049 Product name: X33S-07i

1 of 5

Extinguishing media: Water spray (fog), foam, dry chemical or carbon dioxide.

Special fire fighting procedures: Fire fighters should wear positive pressure breathing apparatus.

Unusual fire or explosion hazards: Vapours may form explosive mixtures with air.

Hazardous combustion products: Thermal decomposition can lead to release of irritating gases and vapours.

6. ACCIDENTAL RELEASE MEASURES

Environmental precautions: Prevent further leakage or spillage if safe to do so. Do not let product enter drains.

Clean-up methods: Evacuate personnel to safe areas. Remove all sources of ignition. Wear suitable protective clothing,

gloves and eye/face protection. Soak up with inert absorbent. Keep in suitable, closed containers for

disposal.

7. HANDLING AND STORAGE

Handling: Use only in well-ventilated areas. Keep away from sources of ignition - No smoking. Avoid contact with

eyes, skin and clothing.

Storage: Keep containers tightly closed in a cool, well-ventilated place. Store away from sources of heat or

ignition. Take measures to prevent the build up of electrostatic charge.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Hazardous components CAS No.	ACGIH TLV	Austria	Belgium	Czech
Propan-2-ol 67-63-0	200 ppm TWA 400 ppm STEL	200 ppm MAK 2000 mg/m³ STEL 500 mg/m³ MAK 800 ppm STEL	1248 mg/m³ VLE 400 ppm VLE 500 ppm VLE 997 mg/m³ VLE	500 mg/m³ TWA
Adipic acid 124-04-9	5 mg/m³ TWA		5 mg/m³ VLE	

Hazardous components CAS No.	Estonia	Greece	Finland	France	Hungary
Propan-2-ol	600 mg/m ³ STEL	500 ppm STEL	200 ppm TWA	400 ppm VLE	2000 mg/m ³ STEL
67-63-0	250 ppm STEL	1225 mg/m³ STEL	250 ppm STEL	980 mg/m³ VLE	500 mg/m ³ TWA
	350 mg/m ³ TWA 150 ppm TWA	980 mg/m ³ TWA 400 ppm TWA	500 mg/m³ TWA 620 mg/m³ STEL		

Hazardous components CAS No.	Germany	Ireland	Netherlands	Norway	Portugal
Propan-2-ol 67-63-0	1000 mg/m³ Peak 200 ppm MAK 400 ppm Peak 500 mg/m³ MAK	1225 mg/m³ STEL 400 ppm TWA 500 ppm STEL 980 mg/m³ TWA	250 ppm MAC 650 mg/m³ MAC	100 ppm TWA 245 mg/m³ TWA	400 ppm TWA
Adipic acid 124-04-9		5 mg/m³ TWA	5 mg/m³ MAC		5 mg/m³ TWA

Hazardous components	Poland	Spain	Sweden	UK EH40
CAS No.				
Propan-2-ol		1250 mg/m ³ VLA-EC	150 ppm LLV	400 ppm TWA
67-63-0	900 mg/m ³ NDS	400 ppm VLA-ED	250 ppm STV	999 mg/m³ TWA
		500 ppm VLA-EC	350 mg/m³ LLV	500 ppm STEL
		998 mg/m³ VLA-ED	600 mg/m ³ STV	1250 mg/m ³ STEL
Adipic acid	10 mg/m3 NDSCh	5 mg/m³ VLA-ED		
124-04-9	5 mg/m ³ NDS			

Engineering controls: Ensure adequate ventilation, especially in confined areas. Where reasonably practicable this should be

achieved by the use of local exhaust ventilation and good general extraction.

Respiratory protection: In case of insufficient ventilation, wear suitable respiratory equipment.

Skin protection: For hand protection, use rubber or plastic gloves.

Eye/face protection: Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of

splashing.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state: liquid

Colour: colourless
Odour: alcoholic

pH: not determined

Vapour pressure: 6.6 kPa at 25°C (77°F)

Boiling point/range: 82°C (178°F)

Melting point/range: not determined

Specific gravity: 0.794

Vapour density: heavier than air

Flash point: 14°C (57°F)

Autoignition temperature: 398°C (750°F)

Flammable limits in air - lower %: 2.0
Flammable limits in air - upper %: 12.0

Evaporation rate: not determined

Solubility in water: soluble

Partition coefficient (n-octanol/water): not determined

VOC content: 95 - 100%

10. STABILITY AND REACTIVITY

Stability: Stable under recommended storage conditions.

Hazardous polymersation: Will not occur.

Hazardous decomposition products: Thermal decomposition can lead to release of irritating gases and vapours.

Incompatability: Incompatible with oxidising agents. Dissolves aluminium and zinc slowly with formation of hydrogen.

Conditions to avoid: Keep away from open flames, hot surfaces and sources of ignition.

11. TOXICOLOGICAL INFORMATION

Hazardous components CAS No.	LD50s & LC50s	
Propan-2-ol	Dermal LD50 (Rabbit) = 12800 mg/kg	
67-63-0	Dermal LD50 (Rat) = 12800 mg/kg	
	Oral LD50 (Rat) = 4396 mg/kg	
	Inhalation LC50 (Rat) = 72.6 mg/L	

Inhalation: Inhalation of vapours in high concentration may cause irritation of respiratory system. Symptoms of

overexposure may be headache, dizziness, tiredness, nausea and vomiting.

Skin: Prolonged skin contact may cause skin irritation and/or dermatitis.

Eyes: Contact with eyes will cause irritation.

Ingestion: May cause irritation to the digestive tract. May cause nausea, vomiting and abdominal pain. Ingestion

of large quantities may cause liver or kidney damage.

12. ECOLOGICAL INFORMATION

Mobility: No data available.

Bioaccumulation: No data available.

Ecotoxicity: Biodegradable product of low ecotoxicity.

Isopropyl alcohol:

LC50/96h/Fathead minnows = 1000 mg/l

EC50/24h/Daphnia = 9714 mg/l

Persistence and degradability: Isopropyl alcohol:

BOD5 = 28% (fresh water), 13% (salt water) BOD20 = 78% (fresh water), 72% (salt water)

WGK Water Classification (VwVwS): Class 1

13. DISPOSAL CONSIDERATIONS

Product

Disposal methods: Dispose of this material and its container as a hazardous or special waste. Incineration under

controlled conditions is recommended.

European Waste Catalogue: 14 06 03 - other solvents and solvent mixtures.

Packaging

Disposal Methods: Dispose of as unused product. Do not incinerate closed containers.

14. TRANSPORT INFORMATION

ICAO/IATA (Air):

Identification number: UN1219

Proper shipping name: Isopropanol solution

Hazard class or division: 3
Packing group: |

IMO/IMDG (Sea)

Identification number: UN1219

Proper shipping name: Isopropanol solution

Hazard class or division: 3
Packing group:

EmS: F-E, S-D

ADR/RID (Road/Rail)

UN Number UN1219

Proper shipping name: Isopropanol solution

Hazard class or division 3
Packing group II

15. REGULATORY INFORMATION

Indication of danger: Xi - Irritant.

F - Highly flammable.







Risk Phrases:

R11 - Highly flammable.

R36 - Irritating to eyes.

R67 - Vapours may cause drowsiness and dizziness.

Safety Phrases: S16 - Keep away from sources of ignition - No smoking.

S26 - In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S51 - Use only in well ventilated areas.

Additional Labelling: None

UK National regulations: The Health & Safety at Work etc. Act

The Control of Substances Hazardous to Health Regulations 2002 L5: General Approved Code of Practice to the COSHH Regulations HS(G)97: A Step by Step Guide to the COSHH Regulations

HS(G)193: COSHH essentials: Easy steps to control chemicals (G)51: The Storage of Highly Flammable Liquids in Containers(G)140: The Safe Use and Handling of Highly Flammable Liquids:

The Spraying of Highly Flammable Liquids

16. OTHER INFORMATION

Supercedes Sheet Dated: 09/06/2004

Prepared by: Barry Chase Senior Specialist

Senior Specialist

Product Safety & Regulatory Affairs - Europe

MSDS data Revised: 26/04/2006

The information in this safety data sheet was obtained from reputable sources and to the best of our knowledge is accurate and current at the mentioned date. Neither Loctite nor its subsidiary companies accept any liability arising out of the use of the information provided here or the use, application or processing of the product(s) described herein. Attention of users is drawn to the possible hazards from improper use of the product(s). This safety data sheet was prepared in accordance with Commission Directive 2004/73/EC adapting to technical progress for the 29th time Council Directive 67/548/EEC, and Commission Directive 1999/45/EC.

Explanation of Section 2 R - Phrases

R11 - Highly flammable.

R36 - Irritating to eyes.

R67 - Vapours may cause drowsiness and dizziness.