

APPROVAL SHEET

RFANT Series – 1005 – RoHS Compliance

MULTILAYER CERAMIC ANTENNA

Halogens Free Product

2400 ~ 2500 MHz Working Frequency

P/N: RFANT1005040A1T

*Contents in this sheet are subject to change without prior notice.

FEATURES


1. Surface Mounted Devices with a small dimension of $1.0 \times 0.5 \times 0.35 \text{ mm}^3$ meet future miniaturization trend.
2. High stability in Temperature / Humidity Change
3. LTCC process

APPLICATIONS

1. 2400~2500 MHz Working Frequency
2. Bluetooth, Wireless, Home RF

CONSTRUCTION

TOP View




PIN	Connection
P1	Feeding
P2	GND_1
P3	GND_2
P4	Feeding


DIMENSIONS

Figure	Symbol	Dimension (mm)
<p>Top view</p> <p>Side view</p> <p>Bottom view</p>	L	1.00 ± 0.10
	W	0.50 ± 0.10
	T	0.35 ± 0.10
	A	0.10 ± 0.10
	B	0.30 ± 0.10
	C	0.20 ± 0.10
	D	0.50 ± 0.10
	E	0.125 ± 0.10


ELECTRICAL CHARACTERISTICS

RFANT1005040A1T	Specification
Working Frequency Range	2400 ~ 2500 MHz
Return Loss	-7 dB
Peak Gain	1 dBi (Typical)
VSWR	2.6 max.
Polarization	Linear Vertical
Radiation Pattern	Directional
Impedance	50Ω
Moisture sensitivity levels	MSL is LEVEL 1 (Refer to : IPC/JEDEC J-STD-020)
HBM ESD	Pass 1KV on all pins (Base on AEC-Q200-002)
MM ESD	Pass 200V (Base on EIA/JESD22-A115)
Operating & Storage Condition (Component)	
Operation Temperature Range: -40 ~ +85 °C	
Storage Temperature Range: -40 ~ +85 °C	
Storage Condition before Soldering (Included packaging material)	
Storage Temperature Range: +5 ~ +40 °C	
Humidity: 30 to 70% relative humidity	



TEST BOARD



Antenna on Test Board (Thickness: 0.8mm)



RADIATION PATTERN



	ZX plane		ZY plane		XY plane	
Frequency [MHz]	Max Value [dB]	Average [dB]	Max Value [dB]	Average [dB]	Max Value [dB]	Average [dB]
2400	-2.15 dB	-4.93 dB	0.13 dB	-2.31 dB	-0.88 dB	-4.60 dB
2450	-2.12 dB	-4.91 dB	0.21 dB	-2.06 dB	-0.12 dB	-4.10 dB
2500	-3.59 dB	-6.68 dB	-1.40 dB	-3.63 dB	-2.05 dB	-5.89 dB

RELIABILITY TEST

Test item	Test condition / Test method	Specification
Solderability JIS C 0050-4.6 JESD22-B102D	*Solder bath temperature : $235 \pm 5^{\circ}\text{C}$ *Immersion time : 2 ± 0.5 sec Solder : Sn3Ag0.5Cu for lead-free	At least 95% of a surface of each terminal electrode must be covered by fresh solder.
Resistance to soldering heat JIS C 0050-5.4	*Preheating temperature : $120\sim 150^{\circ}\text{C}$, 1 minute. *Solder temperature : $270\pm 5^{\circ}\text{C}$ *Immersion time : 10 ± 1 sec Solder : Sn3Ag0.5Cu for lead-free Measurement to be made after keeping at room temperature for 24 ± 2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within $-40 \sim 85^{\circ}\text{C}$. Loss of metallization on the edges of each electrode shall not exceed 25%.
Drop Test JIS C 0044 Customer's specification.	*Height : 75 cm *Test Surface : Rigid surface of concrete or steel. *Times : 6 surfaces for each units ; 2 times for each side.	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within $-40 \sim 85^{\circ}\text{C}$.
Vibration JIS C 0040	*Frequency : $10\text{Hz}\sim 55\text{Hz}\sim 10\text{Hz}(1\text{min})$ *Total amplitude : 1.5mm *Test times : 6hrs.(Two hrs each in three mutually perpendicular directions)	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within $-40 \sim 85^{\circ}\text{C}$.
Adhesive Strength of Termination JIS C 0051- 7.4.3	*Pressurizing force: 2N for 5 sec	No remarkable damage or removal of the termination.
Bending test JIS C 0051- 7.4.1	The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm/s per second until the deflection becomes 1mm and then pressure shall be maintained for 5 ± 1 sec. Measurement to be made after keeping at room temperature for 24 ± 2 hours	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within $-40 \sim 85^{\circ}\text{C}$.

Temperature cycle JIS C 0025	1. 30±3 minutes at -40°C±3°C, 2. 10~15 minutes at room temperature, 3. 30±3 minutes at +85°C±3°C, 4. 10~15 minutes at room temperature, Total 100 continuous cycles Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
High temperature JIS C 0021	*Temperature : 85°C±2°C *Test duration : 1000+24/-0 hours Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Humidity (steady conditions) JIS C 0022	*Humidity : 90% to 95% R.H. *Temperature : 40±2°C *Time : 1000+24/-0 hrs. Measurement to be made after keeping at room temperature for 24±2 hrs ※ 500hrs measuring the first data then 1000hrs data	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Low temperature JIS C 0020	*Temperature : -40°C±2°C *Test duration : 1000+24/-0 hours Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.

SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,
 This product could sustain by reflow process three times, and the temperature below 260°C.





Fig 2. Infrared soldering profile

ORDERING CODE

RF	ANT	100504	0	A	1	T
Walsin RF device	Product code ANT : Antenna	Dimension code Per 2 digits of Length, Width, Thickness : e.g. : 100504 = Length 10, Width 05, Thickness 04	Unit of dimension 0 : 0.1 mm 1 : 1.0 mm	Application A: 2400~2500 MHz	Specification Design Code	Packing T : Reeled

Minimum Ordering Quantity: 4000 pcs per reel.


PACKAGING



Paper Tape specifications (unit :mm)

Index	Ao	B0	ΦD	T	W
Dimension (mm)	0.63± 0.10	1.12± 0.10	1.55 ± 0.05	0.43± 0.10	8.00 ± 0.10
Index	E	F	Po	P1	P2
Dimension (mm)	1.75 ± 0.10	3.50 ± 0.05	4.00 ± 0.10	2.00 ± 0.05	2.00 ± 0.05

Reel dimensions



Index	A	B	C
Dimension (mm)	Φ178.0	Φ60.0	Φ13.0

Taping Quantity: 4000 pieces per 7" reel

CAUTION OF HANDLING

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection.
- (2) Storage environment condition.
 - Products should be storage in the warehouse on the following conditions.
 - Temperature : +5 to +40℃
 - Humidity : 30 to 70% relative humidity
 - Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
 - Products should be storage on the palette for the prevention of the influence from humidity, dust and so on.
 - Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
 - Products should be storage under the airtight packaged condition.