



Switches > Toggle Switches



Configuration (Pole-Throw): **Single Pole - Double Throw**

Bushing Thread Size: **10-48**

Switch Contact Plating Material: **Gold**

Process Sealed: **No**

Toggle Style: **Baton Standard**

Features

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On

Body Features

Bushing Thread Size	10-48
Product Orientation	Vertical
Bushing Style	Threaded
Case Color	Red

Contact Features

Switch Contact Plating Material	Gold
---------------------------------	------

Housing Features

Process Sealed	No
----------------	----

Product Type Features

Toggle Style	Baton Standard
Switch Type	Toggle
Sealed Device	Yes
Switch Connection Type	Wire Wrap

Electrical Characteristics

Contact Current Rating	.4 A
Operating Voltage	20 VDC



Mechanical Attachment

Product Mount Type	Panel
--------------------	-------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Dimensions

Toggle Length	7.37 mm[.29 in]
---------------	-----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought

TE Part #5746613-1
08 DIP PLUG CONN-W/COVER

TE Part #87667-2
MOD IV RECP LP

TE Part #1-2176093-3
RP 2A 0.25W 12K4 0.1% 25PPM 1K RL

TE Part #NB17372001
RP-4800-NO.2-0-STK

TE Part #321866
BODY SOLIS RING 1/0 1/4

Documents

Product Drawings

TMS1T3B1M5RE

English

CAD Files

Customer View Model

ENG_CVM_CVM_2267079-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2267079-1_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2267079-1_A1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Subminiature Switches

English