




MULTI-BEAM

TE Internal #: 6450160-3
PCB Mount Receptacle, Right Angle, Board-to-Board, 26 Position,
2.54 mm [.1 in] Centerline, Fully Shrouded, Gold, Through Hole -
Solder

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



EU RoHS Compliance: **Compliant**
EU ELV Compliance: **Compliant**
PCB Connector Assembly Type: **PCB Mount Receptacle**
PCB Mount Orientation: **Right Angle**
Connector System: **Board-to-Board**

Features

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Type Features

Mixed & Hybrid Header	Yes
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Columns	8
Number of Loaded Positions	26
Number of Signal Positions	24



Number of Power Positions	2
PCB Mount Orientation	Right Angle
Number of Positions	26
Number of Rows	4

Electrical Characteristics

Operating Voltage	60 VDC
-------------------	--------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 2.54 µm[50 – 100 µin]
Contact Mating Area Plating Material Thickness	.076 µm[3 µin]
PCB Contact Termination Area Plating Material Thickness	2.54 – 5.08 µm[100 – 200 µin]
Contact Layout	Matrix
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Receptacle
Contact Current Rating (Max)	42 A

Termination Features

Termination Post & Tail Length	3.43 mm[.135 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention	Without
Mating Alignment Type	Guide Post
PCB Mount Retention Type	Hold-Down
PCB Mount Alignment Type	Hold-Down
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

--	--



Housing Material	High Temperature Thermoplastic Glass-Filled
------------------	---

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Connector Width	20.83 mm[.82 in]
-----------------	------------------

PCB Thickness (Recommended)	2.11 – 2.62 mm[.083 – .103 in]
-----------------------------	--------------------------------

Connector Height	11.94 mm[.47 in]
------------------	------------------

Connector Length	48.9 mm[1.925 in]
------------------	-------------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
-----------------------------	----------------

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	High Temperature Part - Not Glow Wire
------------------	---------------------------------------

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	55
--------------------	----

Packaging Method	Tray
------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
--	---

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 6450330-1
MBXL R/A HDR 1P+24S+1P

TE Part # 6600330-4
MBXL VERT HDR 1P+24S+1P

TE Part # 1600236-4
PAN MT PLUG, MBXL, 1P+24S+1P

TE Part # 1600820-1
STL W/GUIDES, MBXL, 1P+24S+1P

TE Part # 2-6450830-6
MBXL R/A HDR 1P + 24S + 1P

TE Part # 6450500-5
MBXL VERT HDR 1P+24S+1P

Customers Also Bought


TE Part #5102321-9
A/L UNIV HDR 40P VERT LG LAT

TE Part #4-644759-0
10P MTA156 HDR ASSY STR LF

TE Part #1892714-2
MBXL R/A HDR 2P

TE Part #2834167-3
RELEASABLE SLIM CONTACT






TE Part #1551573-5

Shield Finger, Loose Piece



TE Part #7-2834006-2

2P MRPK CONN_RD/BK



TE Part #5039304024

DR-25-1/2-0-SP



TE Part #31256

TERMINAL,DG R 16-14 1/4



TE Part #NB14724001

VERSAFIT-5/8-0-FSP



TE Part #NB17744001

VERSAFIT-1-1/4-0-SP

Documents

Product Drawings

MBXL R/A RCPT 1P+24S+1P

English

CAD Files

Customer View Model

ENG_CVM_CVM_6450160-3_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6450160-3_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6450160-3_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

POWER_CONNECTORS_CATALOG_SEC01_BOARD_TO_BOARD

English

MULTI-BEAM XL Cable Plug Assemblies Datasheet 6-1773442-7

English

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

6450160-3

PCB Mount Receptacle, Right Angle, Board-to-Board, 26 Position, 2.54 mm [.1 in]
Centerline, Fully Shrouded, Gold, Through Hole - Solder



Application Specification

English