




MTA 156

TE Internal #: 3-641437-4
Connector Assembly, Plug, Wire-to-Wire, 4 Position, 3.96 mm [.156 in] Centerline, Wire & Cable, UL 94V-2, MTA 156, Rectangular Power Connectors

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



EU RoHS Compliance: **Compliant**
EU ELV Compliance: **Compliant**
Rectangular Power Connector Type: **Connector Assembly**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Wire**

Features

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Type Features

Compatible With Discrete Wire Type	Solid, Stranded
Rectangular Power Connector Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Power Positions	4
Number of Signal Positions	0
Number of Rows	1



Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Cable Exit Angle	90°
------------------	-----

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	50 µm[1.27 µin]
Contact Layout	Inline
Contact Mating Area Plating Material	Tin
Contact Base Material	Copper Alloy
Wire Contact Termination Area Plating Thickness	2.03 µm[80 µin]
Contact Mating Area Plating Material Finish	Matte
Contact Current Rating (Max)	7 A
Contact Retention Within Housing	With
Contact Type	Pin
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.03 µm[80 µin]

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Strain Relief	With
Panel Mount Feature	Without
Mating Retention Type	Latch
PCB Mount Retention	Without
Contact Retention Type Within Housing	Locking Lance
Mating Retention	With
Mating Alignment Type	Polarization
Mating Alignment	With
PCB Mount Alignment	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Wire & Cable IDC Installation Type	Closed End
------------------------------------	------------



Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	White
Housing Material	Nylon - GF

Dimensions

Compatible Insulation Diameter Range	2.41 mm[.095 in]
Product Length	19.81 mm
Connector Height	12.37 mm
Wire Size	.3 – .4 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	LR 7189, Certified
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	1500
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC
Free






Solder Process Capability


Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME	 TE Part # 3-640602-4 04P MTA156 CONN ASSY 24AWG LF	 TE Part # 643067-4 04P MTA156 CMOLDED COVER	 TE Part # 3-640429-4 04P MTA156 CONN ASSY 24AWG WHT
 TE Part # 3-640427-4 04P MTA156 CONN ASSY 20AWG YEL	 TE Part # 3-640600-4 04P MTA156 CONN ASSY 20AWG LF	 TE Part # 3-640428-4 04P MTA156 CONN ASSY 22AWG RED	 TE Part # 3-640426-4 04P MTA156 CONN ASSY 18AWG ORA
 TE Part # 640643-4 04P MTA156 COVER F/T	 TE Part # 3-640599-4 04P MTA156 CONN ASSY 18AWG ORA	 TE Part # 3-640601-4 04P MTA156 CONN ASSY 22AWG LF	 TE Part # 643071-4 04P MTA156 FD-THRU COVER



TE Part # 3-640430-4
04P MTA156 CONN ASSY 26AWG BLU



TE Part # CAT-103156-WBHS
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156




TE Part # 770598-4
04P SL156 HSG W/O LCK RAMP



TE Part # 640551-4
04P MTA156 COVER



TE Part # 3-644860-4
04P MTA156 CONN ASSY 18AWG LF



TE Part # 58082-1
MTA 156 CRIMP HEAD PRODUCTION POSTED


Also in the Series | MTA 156



Connector Caps & Covers(89)




Connector Contacts(4)



Connector Hardware(2)




Insertion & Extraction Tools(1)



PCB Headers & Receptacles(677)



Rectangular Power Connectors(331)



Standard Rectangular Connectors(336)

Customers Also Bought



TE Part #1-2834074-3
3P PLUG, MINIATURE WATERPROOF CONN,WHITE




TE Part #3-641436-2
02P MTA156 CON ASSY LF



TE Part #3-641437-2
02P MTA156 PSTD CONN ASSY RED



TE Part #350561-7
UMNL PIN 24-18 .0126 AU/NI/BR



TE Part #1-2273009-1
M8 x 1.0 Angled socket Pigtail



TE Part #1534686-1
MAG MATE CONT WITH SOLDER PIN



TE Part #1534685-1
MAG MATE CONT .300 SOLDER POST



TE Part #1534684-1
MAG MATE CONT .300 SOLDER POST



TE Part #62438-1
MAG-MATE POST 25-27 013 TPBR



TE Part #601967-2
POSITIONER M22520/1-02

Documents

Product Drawings

04P MTA156 PSTD CONN ASSY RED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-641437-4_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-641437-4_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-641437-4_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English

UL

English

3-641437-4

Connector Assembly, Plug, Wire-to-Wire, 4 Position, 3.96 mm [.156 in] Centerline,
Wire & Cable, UL 94V-2, MTA 156, Rectangular Power Connectors

