

Electrical / Optical Characteristics at Ta = 25°C





Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	IV	25	40	60	mcd	IF = 20mA
Viewing Angle	2θ1/2		70		deg	
Peak Emission Wavelength	λp		570		nm	
Dominant Wavelength	λD	567	570	573	nm	
Spectral Line Half-Width	Δλ		30		nm	
Forward Voltage	VF	1.8	2.1	2.4	V	VR=5V
Reverse Current	Ir	-	-	10	uA	

▲ Luminous intensity (IV) ±10%, Forward Voltage (VF) ±0.1V, Wavelength (λd) ±0.5nm

Absolute Maximum Ratings: (Ta = 25°C)


Parameter	Symbol	Rating	Unit
Power Dissipation	Pd	85	mW
Peak Forward Current (Duty 1/10 @ 1KHZ)	IF (Peak)	100	mA
Recommended Operating Current	IF (Rec)	30	mA
Electrostatic Discharge	ESD _{HBM}	2000	V
Operating Temperature Range	T _{OPR}	-40 to +85	°C
Storage Temperature Range	T _{STG}	-40 to +100	
Lead Soldering Temperature Range (1.6 mm (1/16 inch) from body)	Reflow Soldering : 260°C for 5 sec. Hand Soldering : 350°C for 3 sec.		

Green (AlInGaP λP=570nm)



Single Color LED

multicompPRO



Relative Intensity VS. wavelength



Soldering Iron

Temperature at tip of iron : 350°C Max.


Soldering Time: 3 sec. ± 1 sec. (one time only)

If temperature is higher, time should be shorter


Soldering



Reflow Temp./Time(SMD)



Diagram



Dimensions : Millimetres

Part Number Table

Description	Part Number
Single Color LED, Green, 3mm	L514XGD

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO