



Miniature circuit breaker (MCB), 2 A, 2p, characteristic: B

Part no. FAZ-B2/2
278722
EL Number 1691015
(Norway)

General specifications		
Product name		Eaton Moeller series xEffect - FAZ MCB
Part no.		FAZ-B2/2
EAN		4015082787226
Product Length/Depth		80 millimetre
Product height		75.5 millimetre
Product width		36 millimetre
Product weight		0.226 kilogram
Compliances		RoHS conform UL CSA09 (with supplementary protector only)
Certifications		UL 1077 CSA (Class No. 3215-30) UL (File No. E177451) CSA (File No. 204453) IEC 61373 IEC/EN 60898 North America (UL recognized, CSA certified) CE marking UL (Category Control Number QVNU2, QVNU8) EN45545-2 CSA-C22.2 No. 235 IEC/EN 60947-2
Product Tradename		xEffect - FAZ
Product Type		MCB
Product Sub Type		None
Delivery program		
Application		xEffect - Switchgear for industrial and advanced commercial applications Switchgear for industrial and advanced commercial applications Branch circuits, not as BCPD
Number of poles		Two-pole
Number of poles (total)		2
Number of poles (protected)		2
Tripping characteristic		B
Release characteristic		B
Amperage Rating		2 A
Type		Miniature circuit breaker FAZ
Technical Data - Electrical		
Voltage type		AC
Voltage rating		240 V AC / 415 V AC
Voltage rating (IEC/EN 60898-1)		415 V AC
Voltage rating (UL)		480Y/277 V
Voltage rating (UL CSA 13)		480 Y/277 V AC; 96 V DC
Rated operational voltage (Ue) - max		400 V
Operational voltage (IEC/EN 60947-2) - max		440 V AC
Rated insulation voltage (Ui)		440 V
Rated impulse withstand voltage (Uimp)		4 kV
Frequency rating - min		50 Hz
Frequency rating - max		60 Hz
Rated switching capacity (IEC/EN 60947-2) at max voltage rating		10 kA
Rated switching capacity (IEC/EN 60947-2)		15 kA
Rated switching capacity (IEC/EN 60898-1)		10 kA
Breaking capacity		10 kA (UL1077)
Rated service short-circuit breaking capacity (IEC/EN 60898-1)		7.5 kA

Rated service short-circuit breaking capacity (IEC/EN 60947-2)		7.5 kA
Rated short-circuit breaking capacity (EN 60898) at 230 V		10 kA
Rated short-circuit breaking capacity (EN 60898) at 400 V		10 kA
Rated short-circuit breaking capacity (IEC 60947-2) at 230 V		15 kA
Rated short-circuit breaking capacity (IEC 60947-2) at 400 V		15 kA
Overvoltage category		III
Pollution degree		2
Technical Data - Mechanical		
Width in number of modular spacings		2
Built-in depth		70.5 mm
Degree of protection		IP20 IP20 (IEC) UL/CSA Type: -
Connectable conductor cross section (solid-core) - min		1 mm ²
Connectable conductor cross section (solid-core) - max		25 mm ²
Connectable conductor cross section (multi-wired) - min		1 mm ²
Connectable conductor cross section (multi-wired) - max		25 mm ²
Design verification as per IEC/EN 61439 - technical data		
Rated operational current for specified heat dissipation (I _n)		2 A
Heat dissipation per pole, current-dependent		0 W
Equipment heat dissipation, current-dependent		2.8 W
Static heat dissipation, non-current-dependent		0 W
Heat dissipation capacity		0 W
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		75 °C
Design verification as per IEC/EN 61439		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
Additional information		
Current limiting class		3
Features		Additional equipment possible
Special features		Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
Used with		Miniature circuit breaker FAZ

Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Miniature circuit breaker (MCB) (EC000042)			
Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Miniature circuit breaker (MCB) (ecI@ss13-27-14-19-01 [AAB905019])			
Built-in depth		mm	70.5
Release characteristic			B
Number of poles (total)			2
Number of protected poles			2
Rated current		A	2
Rated voltage		V	400
Rated insulation voltage Ui		V	440
Rated impulse withstand voltage Uimp		kV	4
Rated short-circuit breaking capacity Icn according to EN 60898 at 230 V		kA	10
Voltage type			AC
Rated short-circuit breaking capacity Icn according to EN 60898 at 400 V		kA	10
Rated short-circuit breaking capacity Icu according to IEC 60947-2 at 230 V		kA	15
Rated short-circuit breaking capacity Icu according to IEC 60947-2 at 400 V		kA	15
Frequency		Hz	50 - 60
Power loss		W	2.8
Current limiting class			3
Flush-mounted installation			No
Concurrently switching neutral conductor			No
Over voltage category			3
Pollution degree			2
Additional equipment possible			Yes
Width in number of modular spacings			2
Degree of protection (IP)			IP20
Ambient temperature during operating		°C	-25 - 75
Connectable conductor cross section multi-wired		mm²	1 - 25
Connectable conductor cross section solid-core		mm²	1 - 25
Explosion-proof			No