




Part No. 1003893FT BT Tunable FPC 2.4 GHz Embedded Antenna

2.4 GHz

Supports: Wi-Fi applications, Bluetooth, Zigbee, WLAN



KYOCERA AVX WLAN antennas deliver on the key needs of device designers for higher functionality and performance in smaller/thinner designs. These innovative antennas provide compelling advantages for 2.4 GHz enabled devices.

Real-World Performance and Implementation

Antennas may look alike on the outside, but the important difference is inside. Other antennas may contain simple PIFA or monopole designs that interact with their surroundings, complicating layout or changing performance with use position. KYOCERA AVX antennas utilize patented Isolated Magnetic Dipole (IMD) technology to deliver a unique size and performance combination. This antenna is also offered in PCB form under PN# 1003893PT.

The 1003893FT is offered in many standard cable lengths ranging up to 200 mm. Ordering part number guide is located at end of document for selection ease.

BT Tunable FPC 2.4 GHz Embedded Antenna

2.400 - 2.485 GHz

KEY BENEFITS

Stay-in-Tune

KYOCERA AVX antenna technology provides superior RF field containment, resulting in less interaction with surrounding components.

Quicker Time-to-Market

By optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily mot

Environmental Compliance

Products are the latest RoHS version compliant

APPLICATIONS

Embedded design
Gateway, Access Point
Handheld
Healthcare M2M, Industrial devices
Smart Grid

Smart Home • OBD-II

Electrical Specifications

Typical Performance using 100 mm cable tested on PC-ABS

Frequency	2.400 – 2.485 GHz
Peak Gain	3.3 dBi
Average Efficiency	87%
VSWR Match	1.5:1 max
Feed Point Impedance	50 ohms unbalanced
Polarization	Linear
Power Handling	0.5 Watt CW

Mechanical Specifications

Ordering Part #	1003893FT-AA10L0100
Dimensions (mm)	40.0 x 8.0 x 0.2
Weight (grams)	0.7
Cable/Connector (mm)	Length: 100, Diameter: 1.13, Color: Black; U.FL compatible connector
Mounting	using 3M468 Adhesive
Packaging	PE bags


^{*}Additional variations with different cable lengths, colors and connectors are available.



2.4 GHz KYOCERA AVX Embedded Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Test Setup and Antenna Assembly


Measured in free space with PC/ABS loading and 100 mm cable






Typical VSWR and Efficiency Plots


Measured in free space with PC/ABS loading and 100 mm cable





Antenna Radiation Patterns

Measured with PC/ABS loading and 100 mm cable Typical Performance @ 2440 MHZ






2.4 GHz KYOCERA AVX Embedded Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Antenna Tuning Options

Typical Performance using 100 mm cable tested on PC-ABS



Ref Default: P1 ~ P8 Open

Options for Tuning: "2.4GHz (Lower)"

<u>MODE</u>	<u>T1</u>	<u>T2</u>	<u>T3</u>	<u>T4</u>
PADS	Connect:	Connect:	Connect:	Connect:
	P1+P5	P1+P2+P5+P6	P3+P7	P3+P4+P7+P8
Outcome:	~20 MHz	~40 MHz	~20 MHz	~50 MHz
(Ref: Default)	Shift low	Shift low	Shift low	Shift low

Antenna Tuning Procedure

This antenna has unique features enabling limited range RF tuning by adding a solder bridge in the designated area. Ease of tuning for any application on the fly with a soldering iron. Tuning optional if required.





Filled Gap

^{*}This antenna has unique features enabling limited range RF tuning by leaving P1 ~ P8 connected by "solder bridge". Refer to detailed tuning options below.

DATASHEET | Part No. 1003893FT

2.4 GHz KYOCERA AVX Embedded Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.


Mechanical Dimensions


For references only, in mm.

Part Number	A (mm)	B (mm)	C (mm)	D (mm)	Connector
1003893FT-AA10L0100	40.0 ± 0.3	8.0 ± 0.3	0.2	100.0 ± 3.0	U.FL compatible


^{*}Height "C" of 0.2 mm includes FPC + adhesive thicknesses

*Connector shown in photo below is "Face Down"





Bottom View





DATASHEET | Part No. 1003893FT

2.4 GHz KYOCERA AVX Embedded Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

Ordering Part Numbers

Typical antenna dimensions (mm)

Part Number	A (mm)	B (mm)	C (mm)	D (mm)	Connector
1003893FT-AA10L0025	40.0 ± 0.3	8.0 ± 0.3	0.2	25.0 ± 3.0	U.FL compatible
1003893FT-AA10L0050	40.0 ± 0.3	8.0 ± 0.3	0.2	50.0 ± 3.0	U.FL compatible
1003893FT-AA10L0075	40.0 ± 0.3	8.0 ± 0.3	0.2	75.0 ± 3.0	U.FL compatible
1003893FT-AA10L0100	40.0 ± 0.3	8.0 ± 0.3	0.2	100.0 ± 3.0	U.FL compatible
1003893FT-AA10L0150	40.0 ± 0.3	8.0 ± 0.3	0.2	150.0 ± 4.0	U.FL compatible
1003893FT-AA10L0200	40.0 ± 0.3	8.0 ± 0.3	0.2	200.0 ± 4.0	U.FL compatible

^{*}Height "C" of 0.2 mm includes FPC + adhesive thicknesses

^{*}Connector shown in photo below is "Face Down"