


NOVEX LITE™

Nitrile Synthetic Rubber Glove

Features

- Construction:** Lightweight unlined nitrile synthetic rubber glove.
- Performance:** Made from tough nitrile rubber providing outstanding physical strength. Protection is provided against a wide range of chemicals including strong detergents and oils as well as certain solvents.
- Comfort:** Anatomically shaped ensuring maximum comfort and minimum hand fatigue.
- Good Grip:** Overall textured finish provides a good grip in wet and dry handling applications.



Typical Handling Applications

- Oil & Chemical Processing
- Automotive Industry
- Agriculture
- Metal Fabrication
- Food Processing
- Electronics
- Laboratory

Specifications

Size	7	8	9	10	CEEN388
Code	954	955	956	957	2001
Length	33cm	33cm	33cm	33cm	



NITRI-TECH II™

Nitrile Synthetic Rubber Glove - Flock Lined or Unlined

Features

- Performance:** Offers very good abrasion and puncture resistance as well as protection against a wide range of chemicals including strong detergents, oils and certain solvents.
- Comfort:** Anatomically shaped ensuring comfort and reducing hand fatigue.
- Good Grip:** Slip resistant pattern on palm of glove ensuring good grip in both wet and dry conditions.
- Flock Lined Versions:** Soft cotton flock lining absorbs perspiration keeping hands cool. Easier to put on and take off.
- Unlined Versions:** Flock and lint free.
- Sanitised:** Contains a fungicidal and bacteriostatic agent.
- Anti-Static Properties:** Meets the surface resistivity requirements of EN1149 part 1: 1995.



Typical Handling Applications

- Printing Industry
- Agriculture
- Manufacturing & Assembly
- Cleaning & Janitorial
- Food Process & Packing
- Local Authorities
- Automotive Industry

Specifications

Size	7	8	9	10	CEEN388
Green Flock Lined	924	925	926	927	4101
Blue Flock Lined	944	945	946	947	4101
Green Unlined	904	905	906	907	3101
Length	31cm	31cm	31cm	31cm	

