



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Connector Product Type: **Housing**
Operating Voltage: **600 VDC**
Connector System: **Wire-to-Wire**
Number of Positions: **4**
Sealable: **No**

Features

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Mechanical Attachment

Mating Retention Type	Threaded Coupling
Thread Size	5/8-24 UNEF-2A
Polarization Code	A
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Panel Mount Feature	Without

Housing Features

Body Orientation	Straight
Housing Color	Black



Housing Material	Nylon - GF
Circular Connector Shell Size	11

Configuration Features

Reverse Numbering	Without
Number of Positions	4
Number of Power Positions	0
Number of Signal Positions	4

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Reverse Gender	Yes
Contact Type	Pin
Contact Protection	With

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Power & Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-66107-1
III+ PIN,26-24,TIN,LP

TE Part # 1-66358-6
III+ SKT,18-14,TIN ,STRIP

TE Part # 788088-2
TYPE III+ SOCKET ASSEMBLY,.062

TE Part # 796094-2
SLD CPC PLUG ASY,11-4,STD SEX



TE Part # 66428-4
III+ SKT,30-26,30AU/FL,LP



TE Part # 66104-9
III+ SKT,24-20,30AU/FL,STRIP



TE Part # 66106-7
III+ PIN,26-24,15AU/FL,STRIP



TE Part # 66098-9
III+ PIN,18-16,30AU/FL,STRIP



TE Part # 66429-3
III+ PIN,30-26,15AU/FL,LP



TE Part # 58495-1
PRO CRIMPER ASSY MULTIMATE



TE Part # 66566-4
III+ PIN,24-20,30AU/FL,LP



TE Part # 1-796407-1
CPC PSTD RCPT,11-4,R/A LF



TE Part # 66563-8
III+ SKT,24-20,30AU/FL,STRIP



TE Part # 213841-8
PWRBAND PIN CNT ASSY,8-10,L.P.



TE Part # 201611-1
CONTACT PIN ASSY.



TE Part # 213841-4
PWRBAND PIN CNT ASSY,8-10,L.P.



TE Part # 213811-1
COUPLING RING,SZ 11,CPC



TE Part # 213845-1
POWERBAND CONT ASSY,SILVER PLT



TE Part # 164159-3
M-SRS PIN ASSY 3+



TE Part # 212618-2
PIN CONT ASSY,SZ 16,TYPE II


Also in the Series | AMP CPC




Connector Backshells(1)



Connector Caps & Covers(16)



Connector Contacts(6)



Connector Seals & Cavity Plugs(35)



Connector Strain Relief(60)



Insertion & Extraction Tools(1)




Power Contacts(6)

Customers Also Bought



TE Part #211400-1
CPC PLUG ASSEMBLY SIZE 13-7




TE Part #206358-5
CABLE CLAMP ASY, SIZE 11



TE Part #211768-1
CPC PLUG ASSEMBLY SIZE 17-9



TE Part #206061-1
RECPT, SZ 11-4, CPC



TE Part #1-206062-7
CABLE CLAMP KIT, BULK PKG



TE Part #206044-1
CPC PLUG ASSEMBLY SIZE 17-14



TE Part #206430-1
RECPT, SZ 11-4, CPC



TE Part #206070-8
CABLE CLAMP KIT #17



TE Part #1-66103-8
III+ PIN,24-20,TIN,LP



TE Part #66103-4
III+ PIN,24-20,30AU/FL,LP

Documents

Product Drawings

CPC PLUG ASSY, 11-4, REV SEX

English

CAD Files

Customer View Model

ENG_CVM_CVM_206429-1_J.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_206429-1_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_206429-1_J.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English