


Ferrite Power Inductor, Shielded Drum Core



LINKS TO ADDITIONAL RESOURCES


[Product Page](#)

ELECTRICAL SPECIFICATIONS

Operating temperature:

-40 °C to +105 °C (temperature rise included)

Resistance to solder heat:

255 °C for 10 s (2 times max. through reflow)

FEATURES

- 7.8 mm x 7.8 mm x 5.0 mm max. SMD package
- Shielded drum core ferrite construction to reduce leakage flux
- Inductance range: 1.0 μ H to 470 μ H
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

APPLICATIONS

- DC/DC power supplies
- Noise suppression and filtering

STANDARD ELECTRICAL SPECIFICATIONS

PART NUMBER	L ₀ INDUCTANCE (μ H)	INDUCTANCE TOLERANCE (%)	DCR MAX. (m Ω)	HEAT RATING CURRENT DC TYP. (A) ⁽¹⁾
IFDC3030EZER1R0N	1.0	30	13	9.00
IFDC3030EZER1R5N	1.5	30	14.5	7.60
IFDC3030EZER2R2M	2.2	20	18	6.50
IFDC3030EZER3R3M	3.3	20	24	5.60
IFDC3030EZER3R6M	3.6	20	26	5.00
IFDC3030EZER4R7M	4.7	20	30	4.40
IFDC3030EZER6R8M	6.8	20	41	3.00
IFDC3030EZER8R2M	8.2	20	48	2.90
IFDC3030EZER100M	10	20	49	1.84
IFDC3030EZER120M	12	20	58	1.71
IFDC3030EZER150M	15	20	81	1.47
IFDC3030EZER180M	18	20	91	1.31
IFDC3030EZER220M	22	20	110	1.23
IFDC3030EZER270M	27	20	150	1.12
IFDC3030EZER330M	33	20	170	0.96
IFDC3030EZER390M	39	20	230	0.91
IFDC3030EZER470M	47	20	260	0.88
IFDC3030EZER560M	56	20	350	0.75
IFDC3030EZER680M	68	20	380	0.69
IFDC3030EZER820M	82	20	430	0.61
IFDC3030EZER101M	100	20	610	0.60
IFDC3030EZER121M	120	20	660	0.52
IFDC3030EZER151M	150	20	880	0.46
IFDC3030EZER181M	180	20	980	0.42
IFDC3030EZER221M	220	20	1170	0.36
IFDC3030EZER271M	270	20	1640	0.34
IFDC3030EZER331M	330	20	1860	0.32
IFDC3030EZER391M	390	20	2850	0.29
IFDC3030EZER471M	470	20	3010	0.36


Notes

- All test data is referenced to 25 °C ambient
- Test condition: 100 kHz, 0.3 V for 8.2 μ H and below, and 1 kHz, 0.3 V for 10 μ H and above
- Storage condition: -40 °C to +105 °C (on board); and -10 °C to +40 °C and < 70 % RH (in component packaging)

⁽¹⁾ DC current (A) that will cause an approximate Δ T of 40 °C or cause L₀ to drop by 35 %, whichever is lower



DIMENSIONS in inches [millimeters]



DESCRIPTION

IFDC3030EZ	2.2 μH	± 20 %	ER	e3
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

I F D C	3 0 3 0 E Z	E R	2 R 2	M
PRODUCT FAMILY	SIZE	PACKAGE CODE	INDUCTANCE VALUE	INDUCTANCE TOLERANCE
		ER = tape and reel	2R2 = 2.2 μ H	M = ± 20 % N = ± 30 %



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.